

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0191600002](#)
Status: **Active**
Overview: [Splices](#)
Description: Closed-End Insulated Splice for 10-16 AWG Wire

Documents:
[Drawing \(PDF\)](#) [Packaging Specification PK-19408-109-001 \(PDF\)](#)
[Product Specification PS-19902-013-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	LR18689
UL	E32244
General	
Product Family	Splices
Series	19160
Crimp Quality Equipment	Yes
Overview	Splices
Product Name	Closed-End Insulated
UPC	800753110144
Physical	
Barrel Type	Closed
Color - Resin	Natural
Flammability	94V-2
Insulation	Nylon (PA)
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.041/g
Packaging Type	Carton
Temperature Range - Operating	105°C
Wire Insulation Diameter	9.65mm max.
Wire Size AWG	10, 12, 14, 16
Electrical	
Voltage - Maximum	600V
Material Info	
Engineering Number	NC-1610
Reference - Drawing Numbers	
Packaging Specification	PK-19408-109-001
Product Specification	PS-19902-013-001
Sales Drawing	PS-19160-005-001, SD-19160-001-001



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant	China RoHS
REACH SVHC Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free Status Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[19160](#) Series

Application Tooling | [FAQ](#)
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
AT-200 Hand Held Pneumatic Tool, Without Crimp Dies	192790001
Hand Crimp Tool	640010600
Crimp Head for the AT-200 Pneumatic Hand Tool	640050600
Crimp Head for the AT-200 Pneumatic Hand Tool, Crimp from Top	640053500

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19160-0002](#)