

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0191640033

Status:

Active

Overview:

Perma-Seal Terminals

Description:

Perma-Seal Ring Tongue Terminal for 14-16 AWG Wire, Stud Size 8 (M4)

Documents:

3D Model

Product Specification PS-19902-011-001 (PDF)

Drawing (PDF)

Product Specification PS-19902-013-001 (PDF)

3D Model (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR18689

UL

E32244

General

Product Family

Ring and Spade Terminals

Series

19164

Crimp Quality Equipment

Yes

Overview

Perma-Seal Terminals

Product Name

Perma-Seal

Type

Ring

UPC

800753113213

Physical

Barrel Type

Closed

Insulation

NiAc

Material - Plating Mating

Tin

Net Weight

1.034/g

Packaging Type

Bag

Stud Size

8 (M4)

Wire Insulation Diameter

5.97mm

Wire Size AWG

14, 16

Wire Size mm²

1.23-1.94

Material Info

Engineering Number

SB-237-08

Reference - Drawing Numbers

Product Specification

PS-19902-011-001, PS-19902-013-001

Sales Drawing

SD-19164-026-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2021)4569-DC (8

July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19164 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
PremiumGrade	640017400
Hand Crimp Tool for Industrial Terminals, 10-22 AWG (see ATS)	
Power Crimp Tool	640057400
Head for Terminals 10-22 AWG Wire	
ServiceGrade Hand	640160041
Crimp Tool for Field Repair only, for production use our PremiumGrade Tool	

This document was generated on 12/14/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19164-0033](#)