


TP5KP Series





Agency Approvals

AGENCY	AGENCY FILE NUMBER
71 2	E230531


Maximum Ratings and Thermal Characteristics (T_x=25°C unless otherwise noted)

Parameter	Symbol	Value	Unit
Peak Pulse Power Dissipation by 10/1000µs Test Waveform (Fig.2) (Note 1)	P _{PPM}	5	kW
Steady State Power Dissipation on Infinite Heat Sink at $T_L = 75^{\circ}\text{C}$	P _D	8.0	W
Peak Forward Surge Current, 8.3ms Single Half Sine Wave Unidirectional Only (Note 2)	I _{FSM}	400	А
Maximum Instantaneous Forward Voltage at 100A for Unidirectional Only (Note 3)	V _F	3.5	V
Operating Junction Temperature Range	T	-55 to 150	°C
Storage Temperature Range	T _{STG}	-55 to 175	°C
Typical Thermal Resistance Junction to Lead	R _{eJL}	8.0	°C/W
Typical Thermal Resistance Junction to Ambient	R _{eJA}	40	°C/W

Notes:

- 1. Non-repetitive current pulse per Fig. 4 and derated above T₁ (initial) =25°C per Fig. 3.
- Measured on 8.3ms single half sine wave or equivalent square wave, duty cycle=4 per minute maximum.

Functional Diagram



Description

The TP5KP Series is designed specifically to protect sensitive electronic equipment from voltage transients induced by lightning and other transient voltage events.

Features

- Hi reliability application and automotive grade AEC Q101 qualified
- Glass passivated chip junction in P600 package
- 5 kW peak pulse capability at 10/1000µs waveform, repetition rate (duty cycles):0.01%
- Fast response time: typically less than 1.0ps from 0 Volts to V_{BB} min
- Excellent clamping capability
- Typical failure mode is short from over-specified voltage or current
- Whisker test is conducted based on JEDEC JESD201A per its table 4a and 4c
- IEC-61000-4-2 ESD 30kV(Air), 30kV (Contact)
- EFT protection of data lines in accordance with IEC 61000-4-4

- Low incremental surge resistance
- Typical I_R less than 2μA when V_{BR} min>12V
- High temperature to reflow soldering guaranteed: 260°C/10sec / 0.375", (9.5mm) lead length, 5 lbs., (2.3kg) tension
- V_{BR} @ $T_J = V_{BR}$ @25°C \times (1+ α T \times (T_J - 25)) (α T:Temperature Coefficient, typical value is 0.1%)
- UL Recognized compound meeting flammability rating V-0
- Matte tin lead-free plated
- Halogen free and RoHS compliant
- Pb-free E3 means 2nd level interconnect is Pb-free and the terminal finish material is tin(Sn) (IPC/ JEDEC J-STD-609A.01)

Applications


TVS Components are ideal for the protection of I/O interfaces, $V_{\rm cc}$ bus and other vulnerable circuits used in telecom, computer, industrial and consumer electronic applications.




Electrical Characteristics (T_a=25°C unless otherwise noted)

Part Number (Uni)			er Number Stand off Voltage V _B	Breakdown Voltage V _{BR} (Volts) @ I _T		Test Current I _T	Maximum Clamping Voltage V _C @ I _{PP}	Maximum Peak Pulse Current I _{pp}	Maximum Reverse Leakage I _R @ V _R	Agency Recognition
(31)	(3.)	(Volts)	MIN	MAX	(mA)	(V)	(A)	(μ A)		
TP5KP11A	TP5KP11CA	11.0	12.20	13.50	5	18.2	280.2	2	X	
TP5KP12A	TP5KP12CA	12.0	13.30	14.70	5	19.9	256.3	2	X	
TP5KP13A	TP5KP13CA	13.0	14.40	15.90	5	21.5	237.2	2	X	
TP5KP14A	TP5KP14CA	14.0	15.60	17.20	5	23.2	219.8	2	X	
TP5KP15A	TP5KP15CA	15.0	16.70	18.50	5	24.4	209.0	2	X	
TP5KP16A	TP5KP16CA	16.0	17.80	19.70	5	26.0	196.2	2	X	
TP5KP17A	TP5KP17CA	17.0	18.90	20.90	5	27.6	184.8	2	X	
TP5KP18A	TP5KP18CA	18.0	20.00	22.10	5	29.2	174.7	2	X	
TP5KP20A	TP5KP20CA	20.0	22.20	24.50	5	32.4	157.4	2	X	
TP5KP22A	TP5KP22CA	22.0	24.00	26.90	5	35.5	143.7	2	X	
TP5KP24A	TP5KP24CA	24.0	26.70	29.50	5	38.9	131.1	2	X	
TP5KP26A	TP5KP26CA	26.0	28.90	31.90	5	42.1	121.1	2	X	
TP5KP28A	TP5KP28CA	28.0	31.10	34.40	5	45.4	112.3	2	X	
TP5KP30A	TP5KP30CA	30.0	33.30	36.80	5	48.4	105.4	2	X	
TP5KP33A	TP5KP33CA	33.0	36.70	40.60	5	53.3	95.7	2	X	
TP5KP36A	TP5KP36CA	36.0	40.00	44.20	5	58.1	87.8	2	X	
TP5KP40A	TP5KP40CA	40.0	44.40	49.10	5	64.5	79.1	2	X	
TP5KP43A	TP5KP43CA	43.0	47.80	52.80	5	69.4	73.5	2	X	
TP5KP45A	TP5KP45CA	45.0	50.00	55.30	5	72.7	70.2	2	X	
TP5KP48A	TP5KP48CA	48.0	53.30	58.90	5	77.4	65.9	2	X	
TP5KP51A	TP5KP51CA	51.0	56.70	62.70	5	82.4	61.9	2	X	
TP5KP54A	TP5KP54CA	54.0	60.00	66.30	5	87.1	58.6	2	X	
TP5KP58A	TP5KP58CA	58.0	64.40	71.20	5	93.6	54.5	2	X	
TP5KP60A	TP5KP60CA	60.0	66.70	73.70	5	96.8	52.7	2	X	

I-V Curve Characteristics





- $\mathbf{P}_{_{\mathbf{PPM}}}$ Peak Pulse Power Dissipation Max power dissipation
- **V_s Stand-off Voltage** -- Maximum voltage that can be applied to the TVS without operation
- V_{ss} Breakdown Voltage Maximum voltage that flows though the TVS at a specified test current (I_x)
- V_c Clamping Voltage Peak voltage measured across the TVS at a specified lppm (peak impulse current)
- Reverse Leakage Current Current measured at V₈
- Forward Voltage Drop for Uni-directional



Ratings and Characteristic Curves (T_A=25°C unless otherwise noted)

Figure 1 - TVS Transients Clamping Waveform




Figure 2 - Peak Pulse Power Rating Curve




Figure 3 - Peak Pulse Power Derating Curve




Figure 4 - Pulse Waveform




Figure 5 - Typical Junction Capacitance




Figure 6 - Typical Transient Thermal Impedance






Figure 7 - Maximum Non-Repetitive Peak Forward Surge Current Uni-Directional Only






Figure 8 - Peak Forward Voltage Drop vs Peak Forward Current (Typical Values)



Soldering Parameters

Reflow Co	ndition	Lead–free assembly	
	-Temperature Min (T _{s(min)})	150°C	
Pre Heat	-Temperature Max (T _{s(max)})	200°C	
	-Time (min to max) (t _s)	60 – 180 secs	
Average ra to peak	mp up rate (Liquidus Temp (T _A)	3°C/second max	
$T_{S(max)}$ to T_A	- Ramp-up Rate	3°C/second max	
Reflow	-Temperature (T _A) (Liquidus)	217°C	
nellow	-Time (min to max) (t _s)	60 – 150 seconds	
Peak Temp	erature (T _P)	260 ^{+0/-5} °C	
Time withi Temperatu	n 5°C of actual peak re (t _p)	20 - 40 seconds	
Ramp-dow	n Rate	6°C/second max	
Time 25°C	to peak Temperature (T _P)	8 minutes Max.	
Do not exc	eed	260°C	



Flow/Wave Soldering (Solder Dipping)

Peak Temperature :	265°C	
Dipping Time :	10 seconds	
Soldering :	1 time	

Physical Specifications


Weight	0.07oz., 2.1g		
Case P600 molded plastic body over pass junction.			
Polarity	Color band denotes the cathode except Bipolar.		
Terminal	Matte Tin axial leads, solderable per JESD22-B102.		

Environmental Specifications

High Temp. Storage	JESD22-A103
HTRB	JESD22-A108
Temperature Cycling	JESD22-A104
нзткв	JESD22-A101
RSH	JESD22-B106




Dimensions




Dimonoiono	Incl	hes	Millimeters		
Dimensions	Min	Max	Min	Max	
А	1.000	-	25.40	-	
В	0.340	0.360	8.60	9.10	
С	0.048	0.054	1.22	1.36	
D	0.340	0.360	8.60	9.10	

Part Numbering System




Part Marking System



Packing Options

Part Number	Component Package	Quantity	Packaging Option	Packaging Specification
TP5KPxxxXX	P600	800	Tape & Reel	EIA STD RS-296

Tape and Reel Specification



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

 TP5KP17A
 TP5KP33A
 TP5KP33CA
 TP5KP24A
 TP5KP26CA
 TP5KP15A
 TP5KP43CA
 TP5KP51CA

 TP5KP18CA
 TP5KP30A
 TP5KP24CA
 TP5KP48CA
 TP5KP45A
 TP5KP28A
 TP5KP45CA
 TP5KP13CA
 TP5KP13CA
 TP5KP11CA
 TP5KP36A
 TP5KP40CA
 TP5KP22CA
 TP5KP12CA
 TP5KP15CA
 TP5KP17CA

 TP5KP13CA
 TP5KP54CA
 TP5KP20A
 TP5KP51A
 TP5KP54A
 TP5KP11A
 TP5KP30CA
 TP5KP20CA
 TP5KP28CA

 TP5KP36CA
 TP5KP58CA
 TP5KP12A
 TP5KP16CA
 TP5KP18A
 TP5KP26A
 TP5KP43A
 TP5KP58A
 TP5KP60CA

 TP5KP14A
 TP5KP16A
 TP5KP60A
 TP5KP22A
 TP5KP48A