

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0346900201

Status:

Active

Overview:

Stac64 Single, Multi-Pocket and Hybrid Header System

Description:

Stac64 Vertical Header Assembly, 20 Circuits, Polarization B, Gray, Tray

Documents:

- 3D Model

3D Model (PDF)

Drawing (PDF)

Product Specification PS-34729-020-001 (PDF)

Application Specification 347290200-AS-CH-000 (PDF)
- Application Specification AS-34729-020-001 (PDF)

Packaging Specification PK-31300-892-001 (PDF)

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

General


Product Family	PCB Headers
Series	34690
Application	Automotive, Power, Wire-to-Board
Comments	Polarization B
Overview	Stac64 Single, Multi-Pocket and Hybrid Header System
Product Name	Stac64
UPC	800756894232

Physical

Breakaway	No
Circuits (Loaded)	20
Circuits (maximum)	20
Color - Resin	Gray
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	7.555/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	3.33mm
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.57mm
Packaging Type	Tray
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +100°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	10.0A
-------------------------------	-------



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

34690 Series

Mates With

34729 2.54mm (.100") Pitch Stac64 Right
Angle Receptacle, 31408 USCAR 2.54mm
(.100") Pitch Receptacle

Voltage - Maximum	500V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	040
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Application Specification	347290200-AS-CH-000, AS-34729-020-001
Packaging Specification	PK-31300-892-001
Product Specification	PS-34729-020-001
Sales Drawing	346900000-000

This document was generated on 12/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[34690-0201](#)