




STEVAL-IFS006V2

Smart inductive proximity switch with the SPT01-335DEE

Data brief

Features

- Metal body detection using the eddy current effect on the HF losses of a coil
- Flexibility
 - MCU firmware can be modified based on application requirements
 - sensitivity and hysteresis adjustment
- In-circuit programming and debugging capabilities
- Analog and digital temperature compensation
- PNP (high-side) sensor functionality configuration
- Complete Transil protection of the output and power supply lines
- Overload and short-circuit protection
- Indicator status LED
- Compact design
- Supply voltage: 7 V to 32 V DC
- Temperature range: $-25\text{ }^{\circ}\text{C}$ to $+85\text{ }^{\circ}\text{C}$
- RoHS compliant



STEVAL-IFS006V2

Description


The STEVAL-IFS006V2 demonstration board is an inductive proximity switch application based on the principle of metal body detection using the eddy current effect on the HF losses of a coil.

The design consists of a single transistor HF oscillator, an ST7LITEUS5 microcontroller, an intelligent TDE1708DFT power switch, and a SPT01-335DEE triple Transil™ array.

The STEVAL-IFS006V2 represents a very simple, compact and cost-effective solution for an inductive proximity switch with wide temperature range, supply voltage variation and noise immunity in industrial environments.

1 Schematic diagram

Figure 1. Circuit schematic



IFS006v2_schematic_1

2 Revision history

Table 1. Document revision history

Date	Revision	Changes
04-Nov-2009	1	Initial release.

Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

UNLESS EXPRESSLY APPROVED IN WRITING BY AN AUTHORIZED ST REPRESENTATIVE, ST PRODUCTS ARE NOT RECOMMENDED, AUTHORIZED OR WARRANTED FOR USE IN MILITARY, AIR CRAFT, SPACE, LIFE SAVING, OR LIFE SUSTAINING APPLICATIONS, NOR IN PRODUCTS OR SYSTEMS WHERE FAILURE OR MALFUNCTION MAY RESULT IN PERSONAL INJURY, DEATH, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE. ST PRODUCTS WHICH ARE NOT SPECIFIED AS "AUTOMOTIVE GRADE" MAY ONLY BE USED IN AUTOMOTIVE APPLICATIONS AT USER'S OWN RISK.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2009 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Philippines - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[STMicroelectronics:](#)

[STEVAL-IFS006V2](#)