


# OA80 Series



AC Fan - 115V, 230V, Dual Voltage  
80 x 38mm(3.15" x 1.5")



|                       |                                                |                                                                                                                                                                                                                                                                                                                                        |  |
|-----------------------|------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|
| Frame                 | Diecast Aluminum                               | <u>Operating Temperature</u><br>Ball Bearing<br>-20C ~ +80C<br>Sleeve Bearing<br>-10C ~ +50C<br><br><u>Life Expectancy</u><br>Ball Bearing<br>60,000 hours (L10 at 40C)<br>Sleeve Bearing<br>30,000 hours (L10 at 40C)<br><br><u>Dual Voltage</u><br>Connection via 4x leads.<br>Fans can be configured for<br>115V or 230V operation. |  |
| Impeller              | PBT, UL94V-O plastic                           |                                                                                                                                                                                                                                                                                                                                        |  |
| Connection            | 2x Lead Wires 22 AWG or terminals              |                                                                                                                                                                                                                                                                                                                                        |  |
| Motor                 | Shaded pole, impedance protected               |                                                                                                                                                                                                                                                                                                                                        |  |
| Bearing System        | Dual ball or Sleeve                            |                                                                                                                                                                                                                                                                                                                                        |  |
| Insulation Resistance | >100M ohm between lead-wire and frame (500VDC) |                                                                                                                                                                                                                                                                                                                                        |  |
| Dielectric Strength   | 1 min at 1500 VAC, 50/60Hz                     | m0                                                                                                                                                                                                                                                                                                                                     |  |

| Model Number      | Speed (RPM) | Airflow (CFM) | Noise (dB) | Volts AC | Voltage Range | Watts | Max. Static Pressure ("H2O) |
|-------------------|-------------|---------------|------------|----------|---------------|-------|-----------------------------|
| OA80AP-11-1*      | 3000        | 31            | 29         | 115      | 80~130        | 12    | 0.24                        |
| OA80AP-11-2*      | 2300        | 23            | 22         | 115      | 80~130        | 9     | 0.15                        |
| OA80AP-11-3*      | 1600        | 17            | 18         | 115      | 80~130        | 5     | 0.10                        |
| OA80AP-22-1*      | 3000        | 31            | 29         | 230      | 160~260       | 12    | 0.24                        |
| OA80AP-22-2*      | 2300        | 23            | 22         | 230      | 160~260       | 9     | 0.15                        |
| OA80AP-22-3*      | 1600        | 17            | 18         | 230      | 160~260       | 5     | 0.10                        |
| OA80AP-11/22-1W** | 3000        | 31            | 29         | 115/230  | 80~260        | 12    | 0.24                        |
| OA80AP-11/22-2W** | 2300        | 23            | 22         | 115/230  | 80~260        | 9     | 0.15                        |
| OA80AP-11/22-3W** | 1600        | 17            | 18         | 115/230  | 80~260        | 5     | 0.10                        |

\* Indicate "TB" (Terminal Ball Bearing), "WB" (12" Wire Leads, Ball Bearing), "TS" (Terminal, Sleeve Bearing), "WS" (12" Wire Leads, Sleeve Bearing)  
 \*\* Indicate "B" (Ball Bearing) or "S" (Sleeve Bearing)

Alternate 5 blade frame style available (m2)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Orion Fans:

[OA80AP-11-2WS](#) [OA80AP-11-2TS](#) [OA80AP-11-2TB](#) [OA80AP-11-2WB](#) [OA80AP-11-1WB](#) [OA80AP-11-1WS](#)  
[OA80AP-11-3TS](#) [OA80AP-11-3TB](#) [OA80AP-22-2WS](#) [OA80AP-22-2TS](#) [OA80AP-22-2TB](#) [OA80AP-22-2WB](#) [OA80AP-](#)  
[11-1TB](#) [OA80AP-11-1TS](#) [OA80AP-22-1WB](#) [OA80AP-22-1TS](#) [OA80AP-22-1TB](#) [OA80AP-22-3TS](#) [OA80AP-22-3TB](#)  
[OA80AP-22-3WS](#) [OA80AP-22-3WB](#) [OA80AP-11-3WB](#) [OA80AP-11-3WS](#) [OA80AP-22-1WS](#)