






**DIP6-pin type
with wide variation
Low on-resistance**

PhotoMOS®

**HF 1 Form A
(AQV10○, 20○)**



FEATURES

1. **Controls low-level analog signals**
PhotoMOS feature extremely low closed-circuit offset voltage to enable control of low-level analog signals without distortion.
2. **Controlled with low-level input signals**
3. **AC/DC dual use type and DC only type available.**
4. **Wide variation of 40V, 60V, 250V, 400V load voltage**

TYPICAL APPLICATIONS

- High-speed inspection machines
- Telephone equipment
- Data communication equipment
- Computers

RoHS compliant

TYPES

1. DC type (AQV10 series)

Output rating*		Package	Part No.				Packing quantity		
			Through hole terminal		Surface-mount terminal				
Load voltage	Load current		Tube packing style		Tape and reel packing style				
					Picked from the 1/2/3-pin side	Picked from the 4/5/6-pin side			
DC only	40 V	DIP6-pin	AQV101	AQV101A	AQV101AX	AQV101AZ	1 tube contains: 50 pcs. 1 batch contains: 500 pcs.		
	60 V		AQV102	AQV102A	AQV102AX	AQV102AZ			
	250 V		AQV103	AQV103A	AQV103AX	AQV103AZ			
	400 V		AQV104	AQV104A	AQV104AX	AQV104AZ			

*Indicate the peak AC and DC values.

Note: The surface mount terminal indicator "A" and the packing style indicator "X" or "Z" are not marked on the device.

2. AC/DC type (AQV20 series)

Output rating*		Package	Part No.				Packing quantity		
			Through hole terminal		Surface-mount terminal				
Load voltage	Load current		Tube packing style		Tape and reel packing style				
					Picked from the 1/2/3-pin side	Picked from the 4/5/6-pin side			
AC/DC dual use	40 V	DIP6-pin	AQV201	AQV201A	AQV201AX	AQV201AZ	1 tube contains: 50 pcs. 1 batch contains: 500 pcs.		
	60 V		AQV202	AQV202A	AQV202AX	AQV202AZ			
	250 V		AQV203	AQV203A	AQV203AX	AQV203AZ			
	400 V		AQV204	AQV204A	AQV204AX	AQV204AZ			

*Indicate the peak AC and DC values.

Note: The surface mount terminal indicator "A" and the packing style indicator "X" or "Z" are not marked on the device.

HF 1 Form A (AQV10○, 20○)

RATING

1. DC type

1) Absolute maximum ratings (Ambient temperature: 25°C 77°F)

	Item	Symbol	AQV101(A)	AQV102(A)	AQV103(A)	AQV104(A)	Remarks
Input	LED forward current	I _F		50 mA			
	LED reverse voltage	V _R		10 V			
	Peak forward current	I _{FP}		1 A			f = 100 Hz, Duty factor = 0.1%
	Power dissipation	P _{in}		150 mW			
Output	Load voltage (DC)	V _L	40 V	60 V	250 V	400 V	
	Continuous load current (DC)	I _L	0.7 A	0.6 A	0.3 A	0.18 A	
	Peak load current	I _{peak}	1.8 A	1.5 A	0.6 A	0.5 A	100 ms (1 shot)
	Power dissipation	P _{out}		360 mW			
Total power dissipation		P _T		410 mW			
I/O isolation voltage		V _{iso}		1,500 Vrms			
Ambient temperature	Operating	T _{opr}		−40 to +85°C	−40 to +185°F		(Non-icing at low temperatures)
	Storage	T _{stg}		−40 to +100°C	−40 to +212°F		

2) Electrical characteristics (Ambient temperature: 25°C 77°F)

	Item	Symbol	AQV101(A)	AQV102(A)	AQV103(A)	AQV104(A)	Condition	
Input	LED operate current	Typical	I _{Fon}	2.3 mA			I _L = Max.	
		Maximum		5 mA				
	LED turn off current	Minimum	I _{off}	0.8 mA			I _L = Max.	
		Typical		2.2 mA				
Output	LED dropout voltage	Typical	V _F	2.3 V			I _F = 10 mA	
		Maximum		3 V				
	On resistance	Typical	R _{on}	0.3 Ω	0.37 Ω	2.7 Ω	6.3 Ω	I _F = 10 mA I _L = Max. Within 1 s
		Maximum		0.5 Ω	0.7 Ω	4 Ω	8 Ω	
Transfer characteristics	Off state leakage current	Maximum	I _{Leak}	1 μA			I _F = 0 mA, V _L = Max.	
	Turn on time*	Typical	T _{on}	0.23 ms	0.22 ms	0.13 ms	0.09 ms	I _F = 10 mA I _L = Max.
		Maximum		1 ms				
	Turn off time*	Typical	T _{off}	0.07 ms		0.08 ms		I _F = 10 mA I _L = Max.
		Maximum		1 ms				
I/O capacitance	Typical	C _{iso}		1.3 pF			f = 1 MHz V _B = 0 V	
	Maximum			3 pF				
	Initial I/O isolation resistance	Minimum	R _{iso}	1,000 MΩ			500 V DC	

2. AC/DC type


1) Absolute maximum ratings (Ambient temperature: 25°C 77°F)

	Item	Symbol	Type of connection	AQV201(A)	AQV202(A)	AQV203(A)	AQV204(A)	Remarks
Input	LED forward current	I _F		50 mA				
	LED reverse voltage	V _R		10 V				
	Peak forward current	I _{FP}		1 A				f = 100 Hz, Duty factor = 0.1%
	Power dissipation	P _{in}		150 mW				
Output	Load voltage (peak AC)	V _L		40 V	60 V	250 V	400 V	
	Continuous load current	I _L		0.5 A	0.4 A	0.2 A	0.15 A	A connection: Peak AC, DC B, C connection: DC
				0.7 A	0.6 A	0.3 A	0.18 A	
	Peak load current	I _{peak}		1.0 A	0.8 A	0.4 A	0.25 A	A connection 100 ms (1 shot) V _L = DC
I/O	Power dissipation	P _{out}		360 mW				
	Total power dissipation	P _T		410 mW				
	I/O isolation voltage	V _{iso}		1,500 Vrms				
	Ambient temperature	T _{opr}		−40 to +85°C			−40 to +185°F	(Non-icing at low temperatures)
	Storage	T _{stg}		−40 to +100°C			−40 to +212°F	

2) Electrical characteristics (Ambient temperature: 25°C 77°F)

Item			Symbol	Type of connection	AQV201(A)	AQV202(A)	AQV203(A)	AQV204(A)	Condition			
Input	LED operate current	Typical	I _{Fon}	—	2.4 mA			I _L = Max.	I _F = 10 mA			
		Maximum			5 mA							
	LED turn off current	Minimum	I _{Foff}	—	0.8 mA			I _L = Max.				
		Typical			2.2 mA							
Output	LED dropout voltage	Typical	V _F	—	2.3 V			I _L = 10 mA				
		Maximum			3 V							
	On resistance	Typical	R _{on}	A	0.6 Ω	0.74 Ω	5.5 Ω	12.4 Ω	I _F = 10 mA I _L = Max. Within 1 s			
		Maximum			1 Ω	1.4 Ω	8 Ω	16 Ω				
		Typical	R _{on}	B	0.3 Ω	0.37 Ω	2.7 Ω	6.2 Ω	I _F = 10 mA I _L = Max. Within 1 s			
		Maximum			0.5 Ω	0.7 Ω	4 Ω	8 Ω				
Transfer characteristics	Typical	R _{on}	C	—	0.15 Ω	0.18 Ω	1.4 Ω	3.1 Ω	I _F = 10 mA I _L = Max. Within 1 s			
		Maximum			0.25 Ω	0.35 Ω	2 Ω	4 Ω				
	Off state leakage current	Maximum	I _{Leak}	—	1 μA			I _F = 0 mA, V _L = Max.				
	Turn on time*	Typical	T _{on}	—	0.38 ms	0.41 ms	0.21 ms	0.18 ms	I _F = 10 mA I _L = Max.			
	Turn on time*	Maximum			1 ms							
Transfer characteristics	Turn off time*	Typical	T _{off}	—	0.08 ms			0.07 ms	I _F = 10 mA I _L = Max.			
		Maximum			1 ms			f = 1 MHz V _B = 0 V				
	I/O capacitance	Typical	C _{iso}	—	1.3 pF							
	Maximum	—			3 pF							
Transfer characteristics	Initial I/O isolation resistance	Minimum	R _{iso}	—	1,000 MΩ			500 V DC				

*Turn on/Turn off time



3. Recommended operating conditions (Ambient temperature: 25°C 77°F)

Please use under recommended operating conditions to obtain expected characteristics.


Item		Symbol	Min.	Max.	Unit
LED current		I _F	10	30	mA
AQV101(A)	Load voltage (Peak AC)	V _L	—	32	V
	Continuous load current	I _L	—	0.7	A
AQV102(A)	Load voltage (Peak AC)	V _L	—	48	V
	Continuous load current	I _L	—	0.6	A
AQV103(A)	Load voltage (Peak AC)	V _L	—	200	V
	Continuous load current	I _L	—	0.3	A
AQV104(A)	Load voltage (Peak AC)	V _L	—	320	V
	Continuous load current	I _L	—	0.18	A
AQV201(A)	Load voltage (Peak AC)	V _L	—	32	V
	Continuous load current (A connection)	I _L	—	0.5	A
AQV202(A)	Load voltage (Peak AC)	V _L	—	48	V
	Continuous load current (A connection)	I _L	—	0.4	A
AQV203(A)	Load voltage (Peak AC)	V _L	—	200	V
	Continuous load current (A connection)	I _L	—	0.2	A
AQV204(A)	Load voltage (Peak AC)	V _L	—	320	V
	Continuous load current (A connection)	I _L	—	0.15	A

■ These products are not designed for automotive use.


If you are considering to use these products for automotive applications, please contact your local Panasonic Corporation technical representative.

REFERENCE DATA


1.-(1) Load current vs. ambient temperature characteristics (DC type)
Allowable ambient temperature: -40 to +85°C
-40 to +185°F




2.-(2) On resistance vs. ambient temperature characteristics (DC type: AQV103, AQV104)
LED current: 10 mA;
Continuous load current: Max. (DC)




3.-(1) Turn on time vs. ambient temperature characteristics (DC type)
LED current: 10 mA;
Load voltage: Max. (DC);
Continuous load current: Max. (DC)




4.-(2) Turn off time vs. ambient temperature characteristics (AC/DC type)
LED current: 10 mA; Load voltage: Max. (DC);
Continuous load current: Max. (DC)




5.-(1) LED operate/turn off current vs. ambient temperature characteristics (DC type)
Load voltage: Max. (DC);
Continuous load current: Max. (DC)



1.-(2) Load current vs. ambient temperature characteristics (AC/DC type)
Allowable ambient temperature: -40 to +85°C
-40 to +185°F




2.-(1) On resistance vs. ambient temperature characteristics (DC type: AQV101, AQV102)
LED current: 10 mA;
Continuous load current: Max. (DC)




2.-(2) On resistance vs. ambient temperature characteristics (DC type: AQV103, AQV104)
LED current: 10 mA;
Continuous load current: Max. (DC)

2.-(3) On resistance vs. ambient temperature characteristics (AC/DC type: AQV201, AQV202)
Measured portion: between terminals 4 and 6;
LED current: 10 mA;
Continuous load current: Max. (DC)




2.-(4) On resistance vs. ambient temperature characteristics (AC/DC type: AQV203, AQV204)
Measured portion: between terminals 4 and 6;
LED current: 10 mA;
Continuous load current: Max. (DC)




3.-(2) Turn on time vs. ambient temperature characteristics (AC/DC type)
LED current: 10 mA;
Load voltage: Max. (DC);
Continuous load current: Max. (DC)

3.-(3) Turn on time vs. ambient temperature characteristics (DC type)
LED current: 10 mA;
Load voltage: Max. (DC);
Continuous load current: Max. (DC)




4.-(1) Turn off time vs. ambient temperature characteristics (DC type)
LED current: 10 mA;
Load voltage: Max. (DC);
Continuous load current: Max. (DC)




5.-(2) LED operate/turn off current vs. ambient temperature characteristics (AC/DC type)
Load voltage: Max. (DC);
Continuous load current: Max. (DC)


5.-(3) LED operate/turn off current vs. ambient temperature characteristics (DC type)
Load voltage: Max. (DC);
Continuous load current: Max. (DC)




6. LED dropout voltage vs. ambient temperature characteristics
Sample: All types
LED current: 10 to 50 mA




7.-1) Current vs. voltage characteristics of output at MOS portion (DC type)
Ambient temperature: 25°C 77°F




7.-2) Current vs. voltage characteristics of output at MOS portion (AC/DC type)
Measured portion: between terminals 4 and 6;
Ambient temperature: 25°C 77°F




8. Off state leakage current vs. load voltage characteristics
Sample: AQV204;
Measured portion: between terminals 4 and 6;
Ambient temperature: 25°C 77°F




9.-1) Turn on time vs. LED forward current characteristics (DC type)
Load voltage: Max. (DC);
Continuous load current: Max. (DC);
Ambient temperature: 25°C 77°F




9.-2) Turn on time vs. LED forward current characteristics (AC/DC type)
Measured portion: between terminals 4 and 6;
Load voltage: Max. (DC);
Continuous load current: Max. (DC);
Ambient temperature: 25°C 77°F




10.-1) Turn off time vs. LED forward current characteristics (DC type)
Load voltage: Max. (DC);
Continuous load current: Max. (DC);
Ambient temperature: 25°C 77°F




10.-2) Turn off time vs. LED forward current characteristics (AC/DC type)
Measured portion: between terminals 4 and 6;
Load voltage: Max. (DC);
Continuous load current: Max. (DC);
Ambient temperature: 25°C 77°F



11.-1) Output capacitance vs. applied voltage characteristics (DC type)
Frequency: 1 MHz;
Ambient temperature: 25°C 77°F



11.-2) Output capacitance vs. applied voltage characteristics (AC/DC type)
Measured portion: between terminals 4 and 6;
Frequency: 1 MHz;
Ambient temperature: 25°C 77°F



"PhotoMOS®", "PhotoMOS" and "PHOTOMOS" are registered trademarks of Panasonic Corporation.

*Recognized in Japan, the United States, all member states of European Union and other countries.

Please contact

Panasonic Corporation

Electromechanical Control Business Division

■ 1006, Oaza Kadoma, Kadomashi, Osaka 571-8506, Japan
industrial.panasonic.com/ac/e/

Panasonic®

©Panasonic Corporation 2017

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panasonic](#):

[AQV101](#) [AQV201](#) [AQV201A](#) [AQV202A](#) [AQV202](#) [AQV102](#) [AQV102A](#)