






LOC		DIST		REVISIONS						
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD			
		B		RELEASED PER ECO-09-022874	90CT2009	ZMR	MRS			
		C		REVISED PER ECO-12-014021	29SEP2012	TD	AC			
		C1		REVISED PER ECO-14-003229	05MAR2014	PP	SH			
LLOY										



1. MATERIAL:
CAGE ASSEMBLY: 0.25mm THICK NICKEL SILVER ALLOY
GASKET RETENTION PLATE: STAINLESS STEEL
GASKET: PLATED FILLED SILICONE
2. MINIMUM PC BOARD THICKNESS = 1.50mm.
3. PADS AND VIAS CHASSIS GROUND.
4. DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER.
5. MATES WITH SFP MSA COMPLIANT TRANSCEIVERS.
6. INTERPRETATION OF DATUM REFERENCE FRAME IN ACCORDANCE WITH SECT 4.4.1.1 OF ASME Y14.5M-1994.
7. REFERENCE APPLICATION SPEC. 114-13120, HOLE A, FOR RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS.
8. REFERENCE APPLICATION SPEC. 114-13120, HOLE B, FOR RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS.
9. HOLE PATTERN REPEATS FOR EACH PORT. SPACING BETWEEN PORTS IS 14.25mm.
10. PRODUCT COMPLIES WITH SPECIFICATION SFF-8433 IMPROVED PLUGGABLE FORM FACTOR FOR SFP+ GANGED CAGES.



P/N:2007135-1 AS SHOWN




P/N:2007135-3 AS SHOWN

2007135-1/3
MOUNTED PC BOARD
SHOWN THRU RECOMMENDED BEZEL

WITH SPECIAL BOTTOM CAGE	2007135-3
WITH ORIGINAL BOTTOM CAGE	2007135-1
NOTE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. SCHMITT 21JUN2007	TE Connectivity	
DIMENSIONS:		CHK M. SCHMITT 21JUN2007	NAME	
mm		APVD B. WERTZ 21JUN2007	SFP+ 1X4 CAGE ASSEMBLY	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	PRESS FIT, EMI GASKET	
0 PLC ±0.1		108-2364	-	
1 PLC ±0.1		APPLICATION SPEC	-	
2 PLC ±0.1		114-13120	-	
3 PLC ±0.1		WEIGHT	-	
4 PLC ±0.1		Customer Drawing	-	
ANGLES ±1°		SCALE 5:1	SHEET 1 OF 2	
FINISH		REV C1		



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2007135-1](#)