

N-7MG

Electrical Specifications (@25°C)

1. Maximum Power: 600 VA
2. Input Voltage: 230 V, 50 / 60 Hz
3. Output Voltage: 115V $\pm$ 5%
4. Full Secondary Load: 5.22 Amps RMS

Description:

The N-7MG is part of the line of Auto-Transformers that are single winding transformers in which the secondary coil is a fraction of the entire winding for voltage step-down. This causes part of the power to be transferred conductively through the windings, rather than all of the power being transferred by induction.

Safety:

These units are designed with 1500V isolation between the winding and the core. Materials and construction are rated for Class B insulation system.

Dimensions:

Unit: In inches


A	B	C	D	E
4.625 Max	3.937 Max	5.00 Max	3.000 $\pm$ 0.032	3.875 $\pm$ 0.060

Weight: 12.0 lbs

Mounting Holes: .203 x .375



Cord: 6 ft. long, Plug NEMA 6-15P, Socket NEMA 5-15R

Schematic:



RoHS Compliance: As of manufacturing date February 2005, all standard products meet the requirements of 2011/65/EU, known as the RoHS initiative.

* Upon printing, this document is considered "uncontrolled". Please contact Triad Magnetics' website for the most current version.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Triad Magnetics:](#)

[N-7MG](#)