

Part Number: 5T00UP

Audio Cable, 2 Conductor 10 AWG, BC, Unshielded, CM



Product Description

Commercial Audio Cable, Rated-CL2, 2-10 AWG highly flexible stranded bare copper conductors with PVC insulation, PVC jacket with ripcord

Technical Specifications

Product Overview

Environmental Space:	Indoor (Not Riser or Plenum)
----------------------	------------------------------

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
10	65x28	Bare High-Conductivity ETP Copper	2

Conductor Count:	2
Conductor Size:	10 AWG

Insulation

Material	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.02 in

Color Chart

Color
Black
White

Outer Shield Material

Material
Unshielded

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	0.356 in	0.026 in	Yes

Construction and Dimensions

Cabling

Twists
2.67 twist/ft

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
1.03 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor

26 pF/ft

Inductance

Nominal Inductance

0.15 μ H/ft

Current

Max. Recommended Current [A]

27.8 Amps per conductor @ 25°C

Voltage

UL Voltage Rating

150 V RMS

Temperature Range

UL Temp Rating:	75°C
Operating Temp Range:	-20°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	91 lbs/1000ft
Max Recommended Pulling Tension:	260 lbs
Min Bend Radius/Minor Axis:	3.6 in

Standards

NEC/(UL) Specification:	CL2
CPR Euroclass:	Eca

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1685 UL Loading
UL voltage rating:	150 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	6T00UP

Part Number

Variants

Item #	Color	Footnote
5T00UP 0101000	Black	C
5T00UP 0081000	Gray	C
5T00UP 008500	Gray	C

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.