




Product: [7806R](#) 

50 Ohm Wireless Transmission Coax, RF 195, RG58, 19 AWG Solid BC, Foil + 90% TC Braid, PVC Jkt, CMR

Product Description

50 Ohm Wireless Transmission Coax, RF 195, RG58, 19 AWG Solid Bare Copper Conductor, PE Insulation, Duofoil® + 90% Tinned Copper Braid Shield, PVC Jacket, CMR

Technical Specifications

Product Overview

Suitable Applications:	Point-to-point and point-to-multipoint wireless antenna communication; Wireless microphones, Two-Way Radios, Amateur (Ham) Radio, Low Power FM, GPS, RFID (Radio Frequency Identification)
------------------------	--

Construction Details

RG Type:	58
----------	----

Conductor

AWG	Stranding	Nom. Diameter	Material
19	Solid	0.037 in	BC - Bare Copper

Insulation

Material	Nom. Diameter
PE - Polyethylene (Foam)	0.110 in

Outer Shield Material

Layer	Outer Shield Type	Material	Material Trade Name	Coverage
1	Tape	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
2	Braid	Tinned Copper (TC)		90%

Outer Jacket Material

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.195 in

Electrical Characteristics

VSWR

Frequency [MHz]	Max. VSWR
5 - 6000 MHz	1.25:1

Attenuation

Frequency	Nom. Attenuation [dB/100ft]
5 MHz	0.75 dB/100ft
10 MHz	1 dB/100ft
30 MHz	2 dB/100ft
50 MHz	2.5 dB/100ft
150 MHz	4 dB/100ft
220 MHz	4.9 dB/100ft
450 MHz	7.1 dB/100ft
900 MHz	10.3 dB/100ft
1500 MHz	13.7 dB/100ft

1800 MHz	15.2 dB/100ft
2000 MHz	16.1 dB/100ft
2500 MHz	18.3 dB/100ft
3000 MHz	20.5 dB/100ft
4500 MHz	26.5 dB/100ft
5800 MHz	31.2 dB/100ft
6000 MHz	32 dB/100ft

Power Rating

Frequency [MHz]	Max. Power Rating [W]
30 MHz	890 W
50 MHz	694 W
150 MHz	403 W
220 MHz	336 W
450 MHz	231 W
900 MHz	162 W
1,500 MHz	124 W
2,000 MHz	107 W
2,500 MHz	95 W
3,500 MHz	80 W
4,500 MHz	70 W
6,000 MHz	61 W

Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Impedence	Nom. Velocity
7.6 Ohm/1000ft	4.2 Ohm/1000ft	24.3 pF/ft	50 Ohm	77%

Voltage

UL Voltage Rating
300 V (CMR, CMG)

Mechanical Characteristics

Temperature

UL Rating	Operating
60°C	-20°C to +75°C

Bulk Cable Weight:	27 lbs/1000ft
Max. Pull Tension:	40 lbs

Standards and Compliance

Environmental Suitability:	Indoor - Riser, Indoor
Sustainability:	CA Prop 65
Flammability / Fire Resistance:	UL1666 Vertical Shaft, FT4
NEC / UL Compliance:	CMR
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.339 Revision Date: 09-30-2020
----------------------	--

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[7806R 0101000](#) [7806R 010500](#)