

Part Number: 88241

Analog Video, RG59, #23 Solid BCCS, 95% BC Braid, FEP Jacket, CMP



Product Description

23 AWG Solid .023" bare copper-covered steel conductor, plenum, FEP insulation, bare copper braid shield (95% coverage), FEP jacket.

Technical Specifications

Product Overview

Environmental Space:	Indoor/Outdoor
----------------------	----------------

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
23	Solid	BCCS - Bare Copper Covered Steel	0.023 in	1

Conductor Count:	1
Conductor Size:	23 AWG

Insulation

Material	Nominal Diameter
FEP - Fluorinated Ethylene Propylene	0.132 in

Outer Shield Material

Type	Material	Coverage [%]
Braid	BC - Bare Copper	95 %

Outer Jacket Material

Material	Nominal Diameter
FEP - Fluorinated Ethylene Propylene	0.19 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Conductor DCR Conductor Resistance	Nominal Outer Shield DCR	Outer Conductor DCR
49 Ohm/1000ft	49 Ohm/1000ft	2.6 Ohm/1000ft	2.6 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Shield
19.5 pF/ft

Inductance

Nominal Inductance
0.126 µH/ft

Impedance

Nominal Characteristic Impedance
75 Ohm

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.5 dB/100ft
10 MHz	1 dB/100ft
50 MHz	2.3 dB/100ft
100 MHz	3.3 dB/100ft
200 MHz	5.2 dB/100ft
400 MHz	8.4 dB/100ft
700 MHz	11.6 dB/100ft
900 MHz	13.8 dB/100ft
1000 MHz	14.8 dB/100ft

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.45 ns/ft	69.5 %

Voltage

Non-UL Voltage Rating	UL Voltage Rating
1700 V RMS	300 V RMS

Temperature Range

Non-UL Temp Rating:	200°C
Operating Temp Range:	-70°C To +200°C

Mechanical Characteristics

Bulk Cable Weight:	36 lbs/1000ft
Max Recommended Pulling Tension:	62 lbs
Min Bend Radius/Minor Axis:	2.5 in

Standards

NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
CPR Euroclass:	Eca
RG Type:	59/U Type

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	No
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Burial:	Yes
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes

Flammability, LSOH, Toxicity Testing

UL Flammability:	NFPA 262
CSA Flammability:	FT6
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

Part Number

Non-Plenum Number: 8241

Variants

Item #	Color	Footnote
88241 0101000	Black	C
88241 010500	Black	C

Footnote: C - CRATE REEL PUT-UP.

© 2018 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.