

Non EMC DIN-Based VectorPak™ Subracks

Rack Components
& Accessories




Adapter Plates (Z-Rail Type)

Part No.	Description
AS1/2 (Pkg of 2)	Adapter plate for mounting DIN connectors directly onto subrack, 84 tapped holes (2.5mm x 4.5mm pitch) To be used without backplane

Insulation Strips

Mounted between backplane and rear extrusion


Part No.	HP	Width
5250998-84	84	17.00" (431.8mm)




Nut Strips

Threaded mounting holes spaced at 0.2" centers slide into extrusion grooves, can be used to anchor panels, cards or other components. Used on front & rear extrusions on all Vector DIN based metric subracks.

Part No.	HP	Width
5250268-84	84	17" (431.8mm)
5250268-63	63	12.8" (325.1mm)
5250268-42	42	8.6" (218.4mm)
5250268-21	21	4.4" (111.8mm)




Extrusions



All extrusions available in any length


Part No.	HP	A
5250236-84	84	17.00" (431.8)
5250236-63	63	12.80" (325.8)
5250236-42	42	8.60" (218.4)
5250236-21	21	4.40" (11.8)

Pack of 12 8-32 screws, P/N HD94




Part No.	HP	A
5250238-84	84	17.00" (431.8)
5250238-63	63	12.80" (325.8)
5250238-42	42	8.60" (218.4)
5250238-21	21	4.40" (11.8)

Pack of 12 8-32 screws, P/N HD94



Part No.	HP	A
5250237-84	84	17.00" (431.8)
5250237-63	63	12.80" (325.8)
5250237-42	42	8.60" (218.4)
5250237-21	21	4.40" (11.8)


Pack of 12 8-32 screws, P/N HD94





Part No.	HP	A
5250229-84	84	17.00" (431.8)
5250229-63	63	12.80" (325.8)
5250229-42	42	8.60" (218.4)
5250229-21	21	4.40" (11.8)

Pack of 12 8-32 screws, P/N HD94









REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
ALL	A	PROD. REL.	05/01/86	
	B	INCORP ECO 3157	05/20/86	
	C	ECO 4283, ADD 5250238A	06/21/95	

TABULATION			
PART NO.	7	"A"	"B"
5250238-03		0.800	3
5250238-04		1.000	4
5250238-05		1.200	5
5250238-06		1.400	6
5250238-07		1.600	7
5250238-08		1.800	8
5250238-09		2.000	9
5250238-10		2.200	10
5250238-11		2.400	11
5250238-12		2.600	12
5250238-13		2.800	13
5250238-14		3.000	14
5250238-15		3.200	15
5250238-16		3.400	16
5250238-17		3.600	17
5250238-18		3.800	18
5250238-19		4.000	19
5250238-20		4.200	20
5250238-21		4.400	21

TABULATION			
PART NO.	7	"A"	"B"
5250238-22		4.600	22
5250238-23		4.800	23
5250238-24		5.000	24
5250238-25		5.200	25
5250238-26		5.400	26
5250238-27		5.600	27
5250238-28		5.800	28
5250238-29		6.000	29
5250238-30		6.200	30
5250238-31		6.400	31
5250238-31		6.600	32
5250238-33		6.800	33
5250238-34		7.000	34
5250238-35		7.200	35
5250238-36		7.400	36
5250238-37		7.600	37
5250238-38		7.800	38
5250238-39		8.000	39
5250238-40		8.200	40
5250238-41		8.400	41
5250238-42		8.600	42

TABULATION		
PART NO. 7	"A"	"B"
5250238-43	8.800	43
5250238-44	9.000	44
5250238-45	9.200	45
5250238-46	9.400	46
5250238-47	9.600	47
5250238-48	9.800	48
5250238-49	10.000	49
5250238-50	10.200	50
5250238-51	10.400	51
5250238-52	10.600	52
5250238-53	10.800	53
5250238-54	11.000	54
5250238-55	11.200	55
5250238-56	11.400	56
5250238-57	11.600	57
5250238-58	11.800	58
5250238-59	12.000	59
5250238-60	12.200	60
5250238-61	12.400	61
5250238-62	12.600	62
5250238-63	12.800	63

TABULATION		
PART NO. 7	"A"	"B"
5250238-64	13.000	64
5250238-65	13.200	65
5250238-66	13.400	66
5250238-67	13.600	67
5250238-68	13.800	68
5250238-69	14.000	69
5250238-70	14.200	70
5250238-71	14.400	71
5250238-72	14.600	72
5250238-73	14.800	73
5250238-74	15.000	74
5250238-75	15.200	75
5250238-76	15.400	76
5250238-77	15.600	77
5250238-78	15.800	78
5250238-79	16.000	79
5250238-80	16.200	80
5250238-81	16.400	81
5250238-82	16.600	82
5250238-83	16.800	83
5250238-84	17.000	84


5250238A FINISH: GOLD IRRIDITE

- A
7. DASH NO(S). INDICATE RACK SPACE IN "HP" UNITS (HOLE PITCH OF .200)
 6. FINISH: SATIN ETCH, 7 MIN., CHEM FILM, CLEAR, CLASS 1A, IAW MIL-C-5541
 5. DEGREASE
 4. REMOVE ALL BURRS & SHARP EDGES
 3. FINE GRAIN FINISH ON SURFACES INDICATED ONLY
 2. ENDS TO BE SQUARE WITHIN: .0025 PER INCH OF WIDTH
 1. MAT'L: MAKE FROM P/N # 5280234

NOTES: UNLESS OTHERWISE SPECIFIED.

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS
DRAWING IS THE SOLE PROPERTY OF
VECTOR ELECTRONICS & TECH., INC. ANY
REPRODUCTION IN PART OR AS A WHOLE
WITHOUT THE WRITTEN PERMISSION OF
VECTOR ELECTRONICS & TECH., INC. IS
PROHIBITED.

UNLESS OTHERWISE SPECIFIED:		NAME	DATE	VECTOR ELECTRONICS & TECHNOLOGY, INC		11115 VANOWEN ST., NORTH HOLLYWOOD, CA 91605		
DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL ± ANGULAR: ±.5° TWO PLACE DECIMAL ±.XX THREE PLACE DECIMAL ±.005 INTERPRET GEOMETRIC TOLERANCING PER:		DRAWN	TRUSHAR	01/12/09	EXTRUSION REAR VME CARD CAGE			
		CHECKED						
		ENG APPR.						
		MFG APPR.						
		Q.A.						
MATERIAL	1	THIRD ANGLE PROJECTION			SIZE DWG. NO.		REV	
FINISH	6				B5250238		C	
DO NOT SCALE DRAWING					SCALE: 1:1		WEIGHT:	SHEET 1 OF 1





A



TABULATION	
PART NO. 7	"A"
5250229-64	13.000
5250229-65	13.200
5250229-66	13.400
5250229-67	13.600
5250229-68	13.800
5250229-69	14.000
5250229-70	14.200
5250229-71	14.400
5250229-72	14.600
5250229-73	14.800
5250229-74	15.000
5250229-75	15.200
5250229-76	15.400
5250229-77	15.600
5250229-78	15.800
5250229-79	16.000
5250229-80	16.200
5250229-81	16.400
5250229-82	16.600
5250229-83	16.800
5250229-84	17.000

REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
ALL	A	REVISED & REDRAWN		

NOTES: UNLESS OTHERWISE SPECIFIED.

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS
DRAWING IS THE SOLE PROPERTY OF
VECTOR ELECTRONICS & TECH., INC. ANY
REPRODUCTION IN PART OR AS A WHOLE
WITHOUT THE WRITTEN PERMISSION OF
VECTOR ELECTRONICS & TECH., INC. IS
PROHIBITED.

MATERIAL	1
FINISH	6
DO NOT SCALE DRAWING	

THIRD ANGLE PROJECTION

SIZE	DWG. NO.	REV
B	5250229	A
SCALE: 1:1	WEIGHT:	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vector:

[AS1/2](#) [5250268-84](#) [5250998-84](#) [5250236-36](#) [5250236-42](#)