



Product: <u>9407</u> ⊠

High Perform Instr, 1 Pr #22 Str TC, PVC Ins E2, PVC Jkt, PLTC-ER

Product Description

High Performance Instrumentation, 1 Pair 22AWG (7x30) Tinned Copper, PVC Insulation E2 Color Code, PVC Outer Jacket, PLTC-ER

Technical Specifications

Product Overview

Suitable Applications: Instrumentation, Sensors, Valva			ensors, Valves, Posi	
Constru	Construction Details			
Conducto	r			
Element	Number of Ele	ement AW	G Stranding	Material
Pair(s)	1	22	7x30	TC - Tinned Copper
Insulation				
Element	Materia	al	Thickness [in.	Color Code
Pair(s)	PVC - Polyviny	l Chloride	0.017	Black, Red
Outer Jacket Material Material Thickness Nom. Diameter Ripcord				
PVC - Pol	lyvinyl Chloride	0.037 in	0.198 in	Yes
Cable Diameter (Nominal): 0.198 in				

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Characteristic Impedence	Max. Current
Pair(s)	15.0 Ohm/1000ft	26 pF/ft	90 Ohm	5.8 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
300 V (PLTC, CMG), 150 V (ITC)

Mechanical Characteristics

Temperature

UL Rating	Operating
105°C	-30°C to +105°C
Table Notes	s:

Bend Radius

Stationary Min.	Installation Min	n.
2 in	2 in	
Max. Pull Tension	ո։	18
Bulk Cable Weigl	nt:	17 lbs

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Sunlight Resistance
Flammability / Fire Resistance:	UL1685 UL Loading, FT4, T-29-520, 1202
NEC / UL Compliance:	Article 725, Article 727, Article 800, CMG, ITC-ER, PLTC-ER
AWM Compliance:	2464
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.373 Revision Date: 09-30-2020

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Belden Wire & Cable:

9407 060U1000 9407 0602500 9407 060U500