


K-No.: 25151

**125A / 200A Current Sensor**

For the electronic measurement of currents:  
DC, AC, pulsed, mixed ..., with a galvanic isolation  
between the primary circuit (high power)  
and the secondary circuit (electronic circuit)



Date: 20.10.2010

Customer: Standard type

Customers Part no.:

Page 1 of 2

<b>Description</b>	<b>Characteristics</b>	<b>Applications</b>
<ul style="list-style-type: none"> <li>Closed loop (compensation)</li> <li>Current Sensor with magnetic field probe</li> <li>Printed circuit board mounting</li> <li>Casing and materials UL-listed</li> </ul>	<ul style="list-style-type: none"> <li>Excellent accuracy</li> <li>Very low offset current</li> <li>Very low temperature dependency and offset current drift</li> <li>Very low hysteresis of offset current</li> <li>Short response time</li> <li>Wide frequency bandwidth</li> <li>Compact design</li> <li>Reduced offset ripple</li> </ul>	Mainly used for stationary operation in industrial applications: <ul style="list-style-type: none"> <li>AC variabel speed drives and servo motor drives</li> <li>Static converters for DC motor drives</li> <li>Battery supplied applications</li> <li>Switched Mode Power Supplies (SMPS)</li> <li>Power Supplies for welding applications</li> <li>Uninterruptable Power Supllies (UPS)</li> </ul>

**Electrical data – Ratings**

I <sub>PN</sub>	Primary nominal r.m.s. current	125/200	A
R <sub>M</sub>	Measuring resistance V <sub>C</sub> =± 12V	0 ... 250	Ω
	V <sub>C</sub> =± 15V	10...400	Ω
I <sub>SN</sub>	Secondary nominal r.m.s. current	62,5/100	mA

K <sub>N</sub>	Turns ratio	1: 2000
----------------	-------------	---------

**Accuracy – Dynamic performance data**

		min.	typ.	max.	Unit
I <sub>P,max</sub>	Max. measuring range @ V <sub>C</sub> = ±12V, R <sub>M</sub> = 10 Ω (t <sub>max</sub> = 10sec) @ V <sub>C</sub> = ±15V, R <sub>M</sub> = 10 Ω (t <sub>max</sub> = 10sec)	±290			A
X	Accuracy @ I <sub>PN</sub> , T <sub>A</sub> = 25°C	±370			A
ε <sub>L</sub>	Linearity	0.1	0.5		%
I <sub>0</sub>	Offset current @ I <sub>P</sub> =0, T <sub>A</sub> = 25°C	0.02	0.05		mA
t <sub>r</sub>	Response time	0.5			μs
Δt (I <sub>P,max</sub> )	Delay time at di/dt = 100 A/μs	1			μs
f	Frequency bandwidth	DC...100			kHz

**General data**

		min.	typ.	max.	Unit
T <sub>A</sub>	Ambient operating temperature	-40	+85		°C
T <sub>S</sub>	Ambient storage temperature	-40	+90		°C
m	Mass	37			g
V <sub>C</sub>	Supply voltage	±11.4	±12/±15	±15.75	V
I <sub>C</sub>	Current consumption	18			mA
	Constructed and manufactured and tested in accordance with EN 61800-5-1 (Pin 1- 4 to inner hole) Reinforced insulation, Insulation material group 1, Pollution degree 2				
S <sub>clear</sub>	Clearance (component without solder pad)	12			mm
S <sub>creep</sub>	Creepage (component without solder pad)	12			mm
V <sub>sys</sub>	System voltage overvoltage category 3	RMS	600		V
V <sub>work</sub>	Working voltage (table 7 acc. to EN61800-5-1)	RMS	1000		V
U <sub>PD</sub>	Rated discharge voltage	peak value	1225		V

**Maximal continuous and peak currents at defined temperatures**

Supply voltage ±12V:

T <sub>A</sub>	85 °C	85 °C	70 °C	55 °C
I <sub>P</sub>	200 A	250 A	250 A	250 A
I <sub>P,max</sub>	264 A	295 A	306 A	343 A
R <sub>M</sub>	20 Ω	10 Ω	10 Ω	5 Ω

Supply voltage ±15V:

T <sub>A</sub>	85 °C	85 °C	70 °C	55 °C
I <sub>P</sub>	200 A	150 A	230 A	250 A
I <sub>P,max</sub>	333 A	384 A	389 A	433 A
R <sub>M</sub>	20 Ω	10 Ω	10 Ω	5 Ω


Date	Name	Issue	Amendment
20.10.10	Le	81	Mechanical outline – Error correction – distance of fastening bores (41,4 to 40,64) lapidary change.
Hrsg.: KB-E editor	Bearb: Le designer	KB-PM IA: KRe. check	freig.: prs. released

Copying of this document, disclosing it to third parties or using the contents there for any purposes without express written authorization by use illegally forbidden  
Any offenders are liable to pay all relevant damages.

**K-No.:** 25151

**125A / 200A Current Sensor**

For the electronic measurement of currents:  
DC, AC, pulsed, mixed ..., with a galvanic isolation  
between the primary circuit (high power)  
and the secondary circuit (electronic circuit)



**Date:** 20.10.2010

**Customer:** Standard type

**Customers Part no.:**
**Page** 2 **of** 2

**Mechanical outline (mm):**

General tolerances DIN ISO 2768-c





 Toleranz der Stiftabstände  $\pm 0,2\text{mm}$   
(Tolerances grid distance)

 DC = Date Code  
F = Factory

 \* = vorläufig  
(preliminary)

**Connections:**

1...4: 0,6 x 0,88 mm

**Marking:**

**Schematic diagram**


Temperature of the primary conductor should not exceed 110°C

Additional indications are obtainable on request.

This specification is no declaration of warranty acc. BGB §443 dar.

**Hrsg.:** KB-E  
editor

**Bearb.:** Le  
designer

**KB-PM IA:** KRe.  
check

**freig.:** prs.  
released



## Additional Information

Item No.: T60404-N4646-X201

K-No.: 25151

### 125A / 200A Current Sensor

For electronic current measurement:  
DC, AC, pulsed, mixed ..., with a galvanic  
isolation between primary circuit  
(high power) and secondary circuit

Date: 20.10.2010

Customer:

Customers Part No.:

Page 1 of 3

#### Electrical Data (investigate by a type checking)

		min.	typ.	max.	Unit
V <sub>Ctot</sub>	Maximum supply voltage (without function) ±15.75 to ±18 V: for 1s per hour			±18	V
R <sub>S</sub>	Secondary coil resistance @ T <sub>A</sub> =85°C			63	Ω
X <sub>Ti</sub>	Temperature drift of X @ T <sub>A</sub> = -40 ... +85 °C			0.1	%
I <sub>0ges</sub>	Offset current (including I <sub>0</sub> , I <sub>0t</sub> , I <sub>0T</sub> )			0.07	mA
I <sub>0t</sub>	Long term drift Offset current I <sub>0</sub>		0.025		mA
I <sub>0T</sub>	Offset current temperature drift I <sub>0</sub> @ T <sub>A</sub> = -40 ...+85°C		0.025		mA
I <sub>0H</sub>	Hyteresis current @ I <sub>P</sub> =0 (caused by primary current 10 x I <sub>PN</sub> )		0.025	0.05	mA
ΔI <sub>0</sub> /ΔV <sub>C</sub>	Supply voltage rejection ratio			0.01	mA/V
i <sub>loss</sub>	Offset ripple (with 1 MHz- filter first order)			0.1	mA
i <sub>loss</sub>	Offset ripple (with 100 kHz- filter first order)		0.01	0.02	mA
i <sub>loss</sub>	Offset ripple (with 20 kHz- filter first order)		0.003	0.005	mA
C <sub>k</sub>	Maximum possible coupling capacity (primary – secondary)	8			pF

#### Inspection (Measurement after temperature balance of the samples at room temperature)

K <sub>N</sub> (N <sub>1</sub> /N <sub>2</sub> )	(V)	M3011/6	Transformation ratio (I <sub>P</sub> =100A, 40-80 Hz)	1:1990...2010
I <sub>0</sub>	(V)	M3226	Offset current	0.05 mA
V <sub>d</sub>	(V)	M3014:	Test voltage, rms, 1 s pin 1 – 4 vs. hole	1.8 kV
V <sub>e</sub>	(AQL 1/S4)		Partial discharge voltage acc.M3024 (RMS) with V <sub>vor</sub> (RMS)	1300 V 1625 V

#### Type Testing (Pin 1 - 4 to hole)

V <sub>W</sub>	HV transient test according to M3064 (1,2 µs / 50 µs-wave form)	8	kV
V <sub>d</sub>	Testing voltage to M3014	(5 s)	3.6 kV
V <sub>e</sub>	Partial discharge voltage acc.M3024 (RMS) with V <sub>vor</sub> (RMS)	1300 V 1625 V	

Datum	Name	Index	Änderung
20.10.10	Le	81	Date updated.
Hrsg.: KB-E editor	Bearb: Le designer		KB-PM IA: KRe. check
			freig.: prs. released

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Zu widerhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder GM-Eintragung vorbehalten

Copying of this document, disclosing it to third parties or using the contents there for any purposes without express written authorization by use illegally forbidden.  
Any offenders are liable to pay all relevant damages.

K-No.: 25151

**125A / 200A Current Sensor**


For electronic current measurement:  
DC, AC, pulsed, mixed ..., with a galvanic  
isolation between primary circuit  
(high power) and secondary circuit

Date: 20.10.2010


Customer:

Customers Part No.:

Page 2 of 3

**Limit curve of measurable current  $\hat{I}_P(R_M)$** @ ambient temperature  $\leq 85^\circ\text{C}$ **Maximum measuring range ( $\mu\text{s-range}$ )**

Output current behaviour of a 3kA current pulse  
@  $V_C = \pm 15V$  und  $R_M = 10\Omega$



Fast increasing currents (higher than the specified  $I_{p,\max}$ ), e.g. in case of a short circuit, can be transmitted because the currents are transformed directly and be limited by diodes only.

The offset ripple can be reduced by an external low pass. Simplest solution is a passive low pass filter of 1st order with

$$f_g = \frac{1}{2p \cdot R_M \cdot C_a}$$

In this case the response time is enlarged.

It is calculated from:

$$t'_r \leq t_r + 2,5R_M C_a$$

**Applicable documents**

Current direction: A positive output current appears at point  $I_S$ , by primary current in direction of the arrow.

Housing and bobbin material UL-listed: Flammability class 94V-0.

Hrsg.: KB-E  
editor

Bearb: Le  
designer

KB-PM IA: KRe.  
check

freig.: prs.  
released



## Additional Information

Item No.: T60404-N4646-X201

K-No.: 25151	<b>125A / 200A Current Sensor</b> For electronic current measurement: DC, AC, pulsed, mixed ..., with a galvanic isolation between primary circuit (high power) and secondary circuit	Date: 20.10.2010
Customer:	Customers Part No.:	Page 3 of 3

### Explanation of several of the terms used in the tablets (in alphabetical order)

$I_{OH}$ :	Zero variation after overloading with a DC of tenfold the rated value ( $R_M = R_{MN}$ )
$I_{ot}$ :	Long term drift of $I_o$ after 100 temperature cycles in the range -40 bis 85 °C.
$t_r$ :	Response time, measured as delay time at $I_P = 0,8 \cdot I_{Pmax}$ between a rectangular current and the output current.
$\Delta t (I_{Pmax})$ :	Delay time between $I_{Pmax}$ and the output current $i_a$ with a primary current rise of $di_1/dt = 100 A/\mu s$ .
$U_{PD}$	Rated discharge voltage (recurring peak voltage separated by the insulation) proved with a sinusoidal voltage $V_e$ $U_{PD} = \sqrt{2} * V_e / 1,5$
$V_{vor}$	Defined voltage is the RMS value of a sinusoidal voltage with peak value of $1,875 * U_{PD}$ required for partial discharge test in IEC 61800-5-1 $V_{vor} = 1,875 * U_{PD} / \sqrt{2}$
$V_{sys}$	System voltage RMS value of rated voltage according to IEC 61800-5-1
$V_{work}$	Working voltage voltage according to IEC 61800-5-1 which occurs by design in a circuit or across insulation
$X_{ges}(I_{PN})$ :	The sum of all possible errors over the temperature range by measuring a current $I_{PN}$ : $X_{ges} = 100 \cdot \left  \frac{I_S(I_{PN})}{K_N \cdot I_{PN}} - 1 \right $
$X$ :	Permissible measurement error in the final inspection at RT, defined by $X = 100 \cdot \left  \frac{I_{SB}}{I_{SN}} - 1 \right $ where $I_{SB}$ is the output DC value of an input DC current of the same magnitude as the (positive) rated current ( $I_o = 0$ )
$X_{Ti}$ :	Temperature drift of the rated value orientated output term. $I_{SN}$ (cf. Notes on $F_i$ ) in a specified temperature range, obtained by: $X_{Ti} = 100 \cdot \left  \frac{I_{SB}(T_{A2}) - I_{SB}(T_{A1})}{I_{SN}} \right $
$\epsilon_L$ :	Linearity fault defined by $\epsilon_L = 100 \cdot \left  \frac{I_P}{I_{PN}} - \frac{I_{Sx}}{I_{SN}} \right $ Where $I_P$ is any input DC and $I_{Sx}$ the corresponding output term. $I_{SN}$ : see notes of $F_i$ ( $I_o = 0$ ).

This "Additional information" is no declaration of warranty according BGB §443.

Hrsg.: KB-E	Bearb: Le			KB-PM IA: KRe. check	freig.: prs. released
-------------	-----------	--	--	-------------------------	--------------------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vacuumschmelze:](#)

[T60404-N4646-X201](#)