

5302U1 Multi-Conductor - Water-Blocked

For more Information
please call

1-800-Belden1

**General Description:**

Security & Alarm Cable, Rated-CMG-FPL-PLTC-ER, 4-18 AWG stranded tinned copper conductors with PVC insulation, Waterblocking tape, PVC jacket

Usage (Overall)

Suitable Applications:

Low Voltage, Water-Blocked for Use in Underground Ducts, PLTC, FPL, Intercom, Sound, Audio

Physical Characteristics (Overall)**Conductor**

AWG:

# Conductors	AWG	Stranding	Conductor Material
4	18	7x27	TC - Tinned Copper

Total Number of Conductors:

4

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
PVC - Polyvinyl Chloride	0.017

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	0.042

Overall Cable

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	White
3	Red
4	Green

Overall Cabling Separator Material:

Waterblocking Tape

Overall Nominal Diameter:

0.309 in.

Mechanical Characteristics (Overall)

Operating Temperature Range:

-30°C To +105°C

Bulk Cable Weight:

40 lbs/1000 ft.

Max. Recommended Pulling Tension:

89 lbs.

Min. Bend Radius/Minor Axis:

3.125 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:

CMG, FPL, PLTC-ER

CEC/C(UL) Specification:

CMG

EU Directive 2011/65/EU (RoHS II):

Yes

EU CE Mark:

Yes

EU Directive 2000/53/EC (ELV):

Yes

EU Directive 2002/95/EC (RoHS):

Yes

EU RoHS Compliance Date (mm/dd/yyyy):

11/06/2006

5302U1 Multi-Conductor - Water-Blocked

EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MIL Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1685 FT4/IEEE 1202 Vertical Tray Flame Test
CSA Flame Test:	FT4

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Sunlight Resistance:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
30.000

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
5.9

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Current
7.2 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
5302U1 0101000	1,000 FT	44.000 LB	BLACK	C	4 #18 PVC PVC

Notes:
C = CRATE REEL PUT-UP.

Revision Number: 4 Revision Date: 02-09-2017

© 2017 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[5302U1 0101000](#) [5302U1 0041000](#)