



For more Information
please call

1-800-Belden1



General Description:

Belden's PVC Vari-Twist series was designed to reduce crosstalk in the balanced mode by twisting the pairs, but can be mass-terminated in the flat sections with standard IDC connectors.

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
8	28	7x36	TC - Tinned Copper

Total Number of Conductors: 16

Conductor Spacing Center to Center Flat Section: .050 +/- .005

Conductor Spacing Outside Center to Outside Center: .75 +/- .012

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
PVC - Polyvinyl Chloride	0.018

Substrate Thickness and Material: .010

Insulation Resistance: >10,000 Mega Ohms

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Overall Cable

Overall Nominal Thickness Flat Section: .042 +/- .003

Overall Nominal Thickness Twisted Section: .080

Overall Nominal Width: .826

Overall Flat Section Length: 2 +/- .0

Overall Twisted Length: 18 in.

Flat Section Center to Center Spacing: 20 +/- .50

Pair

Pair Color Code Chart:

Number	Color
1	Brown/Tan
2	Red/Tan
3	Orange/Tan
4	Yellow/Tan
5	Green/Tan
6	Blue/Tan
7	Purple/Tan
8	Gray/Tan

Spacing

Twisted Pair Spacing Center to Center: .100

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +105°C

Bulk Cable Weight: 31 lbs/1000 ft.

Min. Bend Radius/Minor Axis: 1.250 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

UL Rating:	UL AWM Styles 1731, 2693, & 2697
------------	----------------------------------

EU Directive 2011/65/EU (ROHS II):	Yes
------------------------------------	-----

EU CE Mark:	Yes
-------------	-----

EU Directive 2000/53/EC (ELV):	Yes
--------------------------------	-----

EU Directive 2002/95/EC (RoHS):	Yes
---------------------------------	-----

EU RoHS Compliance Date (mm/dd/yyyy):	10/01/2005
---------------------------------------	------------

EU Directive 2002/96/EC (WEEE):	Yes
---------------------------------	-----

EU Directive 2003/11/EC (BFR):	Yes
--------------------------------	-----

CA Prop 65 (CJ for Wire & Cable):	Yes
-----------------------------------	-----

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

Flame Test

UL Flame Test:	VW-1
----------------	------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Inductance:

Description	Inductance (µH/ft)
@ 1 MHz	.24

Nom. Capacitance Conductor to Conductor:

Description	Capacitance (pF/ft)
@ 1 kHz	20
@ 1 MHz	16

Nominal Velocity of Propagation:

Description	VP (%)
	64

Nominal Delay:

Delay (ns/ft)
1.6 NS/FT.

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
68.2 OHMS/1000 FT. MAX.

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
10	3.5
20	5.5
30	7.2
40	8.8
50	10.2
60	12
70	13
80	14.2
90	15
100	16

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Current
1 Amp per conductor @ 20°C

Nominal Balanced Characteristic Impedance:

Description	Impedance (Ohm)
	115

Nominal Unbalanced Characteristic Impedance:

Description	Impedance (Ohm)
	100

9V28016 Flat - Vari-Twist® 9V280XX Series

Dielectric Withstand Voltage: 2,000 V RMS

Typical Balanced Crosstalk - dB Suppression:

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Crosstalk (dB)
10 ft. sample length		10	100	35

Typical Unbalanced Crosstalk:

Description	Pulse Rise Time (NS) (MHz)	Near End % (MHz)	Far End % (MHz)
10 ft. sample length all grounds connected together.	3	5.8	5.2
10 ft. sample length all grounds connected together.	5	4	3.2
10 ft. sample length all grounds connected together.	7	2.5	2.8

Notes (Overall)

Notes: The transition area is included in the twisted length to assure a full 2 inches of flat termination area.

Kennedy Information (Overall)

Construction: 18" of Twisted Pairs, 2" of Flat Section

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9V28016 000H100	100 FT	3.400 LB	NONE	E	8 PR #28 PVC VARI-TWIST

Notes:

E = MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 25'

Revision Number: 2 Revision Date: 11-08-2012

© 2016 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[9V28016 000H100](#)