


CAPA830

3.5" Embedded SBC with Intel® Atom™ D2550/N2600/N2800, Intel® NM10, LVDS/HDMI/VGA, Dual LANs, Audio and ZIO

Features

- Intel® Atom™ processor D2550 (1.86 GHz)/N2800 (1.86 GHz)/N2600 (1.6 GHz)
- 1 DDR3-800/1066 SO-DIMM, up to 4GB
- 6 USB 2.0 ports
- 2 COM ports
- ZIO connector
- PCI Express Mini Card V1.2 with mSATA supported



Core System



CPU	Intel® Atom™ processor D2550 1.86 GHz/N2800 1.86 GHz/N2600 1.6 GHz dual core onboard
System Memory	1 x 204-pin DDR3-800/1066 SO-DIMM, up to 4GB (N2600 supports DDR3-800, up to 2GB)
Chipset	Intel® NM10
BIOS	AMI UEFI BIOS
SSD	1 x CFast™
Watchdog Timer	255 levels, 1~255 sec.
Expansion Interface	1 x PCI Express Mini Card V1.2 with mSATA 1 x USB, 1 x PCIe x1, 1 x LPC, 1 x SMBus through a ZIO connector
Battery	Lithium 3V/220mAH
Power Input	2 x 2-pin connector +12V DC-in only AT Auto Power ON function supported
Power Requirements	Intel® Atom™ N2600 @ 1.6 GHz, 1GB DDR3 Max. RMS: +12V @ 1.077A Intel® Atom™ N2800 @ 1.86 GHz, 1GB DDR3 Max. RMS: +12V @ 1.156A Intel® Atom™ D2550 @ 1.86 GHz, 1GB DDR3 Max. RMS: +12V @ 1.44A
Size	146 x 104 mm
Board Thickness	1.6 mm
Operating Temperature	-20°C ~ +70°C (-4°F ~ +158°F), operation
Operation Humidity	10% ~ 95% relative humidity, non-condensing

I/O

MIO	1 x RS-232/422/485 (+5V/+12V powered) 1 x RS-232 (+5V/+12V powered)
SATA	1 x SATA-300
Hardware Monitoring	Detect CPU/system temperature, voltage and fan speed
Ethernet	2 ports as 10/100/1000 Mbps support Wake-on-LAN, PXE Boot ROM with Intel® 82583V
Audio	HD Codec audio as MIC-in/Line-in/Line-out with Realtek ALC662
USB	6 x USB 2.0
SMBus	System Management Bus for Advanced monitoring/control
Digital I/O	8 channels IN/OUT programmable
TPM	ST ST33TPM12LPC with TPM 1.2 compliant

Display

Chipset	Intel® GMA 3650 graphics core for D2550/ N2800 Intel® GMA 3600 graphics core for N2600
Memory Size	Share system memory
Display Interface	1 x VGA 1 x HDMI 1 x LVDS; 18/24-bit single/dual channel



Packing List

Standard		
Quick installation guide, user's manual/utility CD, cable		
Cable		
Part Number	Description	Qty
59382620000E	1 x COM w/ bracket, P=2.0 mm, L=300 mm	1
59384500100E	Audio cable w/ bracket, P=2.0 mm, L=450 mm	1
59382631000E	2 x USB 2.0 wafer cable w/ bracket 180 mm	1

Ordering Information

Standard		
CAPA830VHGGGA-D2550 (P/N: E38E830103)	3.5" Embedded SBC with Intel® Atom™ processor D2550 1.86 GHz, Intel® NM10 chipset, VGA/LVDS/HDMI, 2 GbE LANs, audio and heatsink fan	
CAPA830VHGGGA-N2800 (P/N: E38E830102)	3.5" Embedded SBC with Intel® Atom™ processor N2800 1.86 GHz, Intel® NM10 chipset, VGA/LVDS/HDMI, 2 GbE LANs and audio	
CAPA830VHGGGA-N2600 (P/N: E38E830101)	3.5" Embedded SBC with Intel® Atom™ processor N2600 1.6 GHz, Intel® NM10 chipset, VGA/LVDS/HDMI, 2 GbE LANs and audio	
CAPA830VHGGGA-D2550-ZIO (P/N: E38E830106)	3.5" Embedded SBC with Intel® Atom™ processor D2550 1.86 GHz, Intel® NM10 chipset, VGA/LVDS/HDMI, 2 GbE LANs, audio, heatsinkfan and ZIO connector	
CAPA830VHGGGA-N2800-ZIO (P/N: E38E830105)	3.5" Embedded SBC with Intel® Atom™ processor N2800 1.86 GHz, Intel® NM10 chipset, VGA/LVDS/HDMI, 2 GbE LANs, audio and ZIO connector	
CAPA830VHGGGA-N2600-ZIO (P/N: E38E830104)	3.5" Embedded SBC with Intel® Atom™ processor N2600 1.6 GHz, Intel® NM10 chipset, VGA/LVDS/HDMI, 2 GbE LANs, audio and ZIO connector	
CAPA830VHGGGA-N2600 w/ET	3.5" Embedded SBC with Intel® Atom™ processor N2600 1.6 GHz, Intel® NM10 chipset, VGA/LVDS/HDMI, 2 GbE LANs, audio and -40°C to +85°C	
Optional		
AX93262 (P/N: E393262100)	ZIO module w/ four COM ports and one PCIe Mini Card	
AX93285 (P/N: E393285100)	ZIO module w/ two COM ports and 32-bit programmable DIO	
AX93291 (P/N: E393291100)	ZIO module w/ two COM ports and two Gigabit Ethernet	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Axiomtek:](#)

[CAPA830VHGGGA-N2800](#)