

LPS60-M Series

60 Watts Medical

Data Sheet

Total Power: 60 - 80 Watts Input Voltage: 85-264 VAC 120-300 VDC

of Outputs: Single

SPECIAL FEATURES

- Medical safety approvals
- Universal input
- 3" x 5" footprint
- Remote sense
- Built in EMI filter
- Low output ripple
- Adjustable output voltage
- Overload protection
- 110 KHz switching frequency
- LPX60 enclosure kit available

SAFETY

TUV EN 60950-1 EN 60601-1

■ UL UL 2601-1

CSA 22.2 No. 601.1

E182560

CB IEC 60950-1

IEC 60601-1

CE Mark (LVD)






Electrical Specifications				
Input				
Input range	85 - 264 VAC (wide range), 120 - 300VDC			
Frequency	47 - 440 Hz			
Inrush current	<18A peak @ 115VAC, <36A peak @230 VAC, cold start @ 25°C			
Input current	1.5A max. (RMS) @ 115 VAC			
Efficiency	70% typical at full load			
EMI filter	FCC Class A conducted; CISPR22 Class A conducted; EN55022 Class A conducted; VDE0878 PT3 Class A conducted			
Safety ground leakage current	< 75μA @ 50/60 Hz; 264 VAC input			
Output				
Maximum power	60 W for convection; 80 W with 30 CFM forced air			
Adjustment range	-5, +10% minimum			
Hold-up time	20 ms @ 60 W load, 115 VAC nominal line			
Overload protection	Short circuit protection on all outputs Case overload protected @ 110 - 145% above peak rating			
Overvoltage protection	5V output; 5.7 - 6.7 VDC. Other outputs 10% to 25% above nominal output			
Remote sense	Compensates for 0.5 V lead drop min. Will operate without remote sense connected Reverse connection protected			




Environmental Specifications		
Operating temperature	0° to 50 °C ambient. Derate each output as 2.5% per degree from 50° to 70 °C, -20 °C startup	
Storage temperature	-40 °C to +85 °C	
Electromagnetic susceptibility	Designed to meet IEC61000-4-2, -4-3, -4-4, -4-5, -4-6, Level 3	
Humidity	Operating; non-condensing 5% to 95% RH	
Vibration	Three orthogonal axes, sweep at 1cot/min, 5 min.dwell at four major resonances 0.75G peak 5Hz to 500 Hz, operational	
Temperature coefficient	±0.04% per °C	
MTBF demonstrated	> 550,000 hours at full load and 25 °C ambient conditions	

Ordering Information							
Model Number	Output Voltaqe	Minlmun Load	Maxlmun Load with Convection Cooling	Maximun Load with 30CFM Forced Air	Peak Load¹	Requiation ²	Ripple P/P(PARD) ³
LPS63-M	12 V	0A	5 A	6.7 A	7.5 A	± 2%	120 mV
LPS64-M	15 V	0A	4 A	5.3 A	6 A	± 2%	150 mV
LPS65-M	24 V	0A	2.5 A	3.3 A	3.8 A	± 2%	240 mV

- 1. Peak current lasting < 30 seconds with a maximum 10% duty cycle.
- 2. At 25 °C including initial tolerance, line voltage, load currents and output voltages adjusted to factory settings.
- 3. Peak-to-peak with 20 MHz bandwidth and 10 μ F (tantalum capacitor) in parallel with a 0. μ F capacitor at rated line voltage and load ranges.



Mechanical Drawings



In the same

Pin Assignments				
Connector	LPS62-M	LPS63-M	LPS64-M	
SK1-1	Line	Line	Line	
SK1-3	Neutral	Neutral	Neutral	
SK2-1	+12 V	+15 V	+24 V	
SK2-2	+12 V	+15 V	+24 V	
SK2-3	+12 V	+15 V	+24 V	
SK2-4	Common	Common	Common	
SK2-5	Common	Common	Common	
SK2-6	Common	Common	Common	
SK201-1	+Sense	+Sense	+Sense	
SK201-2	-Sense	-Sense	-Sense	

Mating Connectors		
AC Input:	Molex 09-50-8031 (USA) Not required for (-T) option 09-91-0300 (UK) PINS: 08-58-0111	
DC Outputs:	Molex 09-50-8061 (USA) Not required for (-T) option 09-91-0600 (UK) PINS: 08-52-0113	
Remote Sense:	Molex 22-01-2025 PINS: 08-52-0113	
Astec Connector Kit	t #70-841-006, includes all of the above	

- 1. Specifications subject to change without notice.
- 2. All dimensions in inches (mm), tolerance is ±0.02" (±0.5 mm)
- 3. Mounting holes M1 and M2 should be grounded for EMI purposes.
- 4. Mounting hole M1 is safety ground connection.
- 5. Specifications are for convection rating at factory settings at 115 VAC input, 25 $^{\circ}\mathrm{C}$ unless otherwise stated.
- 6. Warranty: 2 years
- 7. Weight: 0.75 lbs/0.34 kg

WORLDWIDE OFFICES

Americas

2900 S.Diablo Way Tempe, AZ 85282 USA +1 888 412 7832

Europe (UK)

Waterfront Business Park Merry Hill, Dudley West Midlands, DY5 1LX United Kingdom +44 (0) 1384 842 211

Asia (HK)

14/F, Lu Plaza 2 Wing Yip Street Kwun Tong, Kowloon Hong Kong +852 2176 3333



www.artesyn.com

For more information: www.artesyn.com/power For support: productsupport.ep@artesyn.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Artesyn Embedded Technologies: LPS64-M LPS65-M LPS63-M