

CUSTOMER'S NAME

MOUSER ELECTRONICS

ALPHA REFERENCE NO

SP12080109



SPECIFICATION

PART NO.	ALPHA MODEL NAME
	RV141F-40-20BL-BXXK
	BXXK FOR 5K~500K

MODEL NAME

MODEL NO.

APPROVAL

PREPARED BY	REVIEWED BY	APPROVED BY
 李雪君 2012.8.21		 李延玲 2012-8-21



台灣艾華電子工業股份有限公司

桃園市中正路1221~1223號9樓

TAIWAN ALPHA ELECTRONIC CO., LTD






9F, NO.1221, Chung Cheng Rd., Taoyuan, Taiwan, R.O.C.

Tel: 886-3-3577799 Fax: 886-3-3577700

EMAIL: sales@taiwanalpha.com.tw


URL: http://www.taiwanalpha.com

SECTION A-A



L	PART NUMBER
20	RV141F-40-20BL-XXX
25	RV141F-40-25BL-XXX



△				TOLERANCES	X ±0.3 .XX ±0.10			MATERIAL	SEE TABLE
△								MATERIAL	SEE TABLE
△				SCALE	5 / 2	UNIT	P.P.M	FINISH	
△				DRAWN BY DESIGN BY CHECKED BY APPROVED BY				NAME	R14 POTENTIOMETERS LED TYPE
△				張月琴					
△				94.10.14					
△				可建志					
△				94.10.14					
△				李信昌					
△				94.10.14					
△									
△	DATE		REVISED						
△	20030702			TAIWAN ALPHA ELECTRONIC CO., LTD.				P. NO.	如附表

SPECIFICATIONS OF 14 Ø ROTARY POTENTIOMETER

一、Environment

1.1 Operating temperature range: $-10\sim+70^{\circ}\text{C}$ 使用溫度範圍: $-10\sim+70^{\circ}\text{C}$ 1.2 Storage temperature range: $-25\sim+75^{\circ}\text{C}$ 儲存溫度範圍: $-25\sim+75^{\circ}\text{C}$

1.3 Test conditions

試驗條件

Standard atmospheric conditions

標準狀態

Unless otherwise specified, the standard range of atmospheric

無特別規定之實驗及測定時以溫度

Conditions for making measurements and tests is as follows:

 $5\sim35^{\circ}\text{C}$ ，相對溼度 $45\sim85\%$ ，氣Ambient temperature: $5\sim35^{\circ}\text{C}$ Relative humidity : $45\sim85\%$ 壓 $860\sim1060\text{mbar}$ 之標準狀態測定

Air pressure: 860 mbar to 1060 mbar

If there is any doubt about the results, measurements shall be made within the following limit

發生判定疑問或另有特別要求則以基準狀態(溫度 $20\pm2^{\circ}\text{C}$ ，相對溼度Ambient temperature: $20\pm2^{\circ}\text{C}$ Relative humidity : $60\sim70\%$ $60\sim70\%$ 氣壓 $860\sim1060\text{mbar}$) 為準

Air pressure: 860 mbar to 1060 mbar

測定

二、Mechanical characteristics 機械的性能

	Item 項目	Specifications 規格
1	Total rotational angle 全迴轉角度	$300^{\circ}\pm5^{\circ}$
2	Rotational torque 迴轉轉矩	$10\sim200\text{gf-cm}$ (rotational speed $60^{\circ}/1\text{ sec.}$)
3	Shaft stop strength 軸迴轉止動強度	4kgf-cm Min 4kgf-cm 以上
4	Push and pull strength of shaft 軸壓拉強度	Push and pull static load of 8kgf shall be applied to the shaft in the axial direction for 3 seconds. No abnormality in electric characteristics and operating feeling. 在軸壓及拉的方向加 8kgf 靜負荷 3 秒鐘，作用後不會影響其電氣特性及操作感覺。
5	Shaft wobble 軸晃動	A momentary load of 500gf-cm shall be applied at the point 5mm from the tip of the shaft in a direction perpendicular to the axis of shaft, the wobble is $0.7 \times L / 30\text{ mm p-p max.}$ (L: shaft length). 軸端前 5 mm 位置加 500gf-cm ，晃動程度 $0.7 \times L / 30\text{ mm p-p}$ 以下，(L：軸長)。

SPECIFICATIONS OF 14 Ø ROTARY POTENTIOMETER

	Item 項目	Specifications 規格
6	Resistance to soldering heat 銲錫耐熱性	After soldering ,there shall be no evidence of poor contact between resistance element and terminals , or any physical damages as a result of the test 銲錫後,不能發生顯著的鬆動或接觸不良
7	Torque of click 段點脫出轉矩	30~200gf.cm (Applied for with detent type) 30~200gf.cm (附段點適用)。
8	Position of detents 段點位置	Center click, 150±2°(Applied for with detent type) 中心點, click 150±2°(附段點適用)。


三、Electrical characteristics 電氣的性能

	Item 項目	Specifications 規格
1	Nominal total resistance 全阻抗值許容公差	Terminal 1-3 5~500 KΩ±20 % 1-3 端全阻值 5~500 KΩ± 20 %
2	Rated wattage 額定功率	0.05W
3	Maximum working voltage 最大工作電壓	AC 50V (This potentiometer is designed for A.C. voltage only.) 交流 50 伏 (本製品系交流電專用，請避免使用直流電)
4	Noise 摺動雜音	Refers to JIS C6443 Less than 100mV 依 JIS C6443 測定法 100 mV 以下
5	Insulation resistance 絕緣阻抗	100MΩ min at DC250 volts DC 250V 需在 100 MΩ 以上

SPECIFICATIONS OF 14 Ø ROTARY POTENTIOMETER

Item 項目		Specifications 規格		
6	阻抗變化特性 TAPER:			
	阻抗變化特性 TAPER	測定角度(50%) Test point(50%)	端子 1-2 間輸出電壓 V1-2 端子 1-3 間輸出電壓 V1-3 (%)	端子 2-3 間輸出電壓 V2-3 端子 1-3 間輸出電壓 V1-3 (%)
	A	150°	10-25	
	B	150°	40-60	
	C	150°		10-25
	D(10A)	150°	6-15	
	X(10C)	150°		6-15
	E(25C)	150°		18-34
	K(25A)	150°	18-34	
	W(W)	90±5°	5-15	
150°		40-60		
210±5°		85-95		
7	Residual resistance 殘留阻值	Resistance at each end of the between terminals 1 and 2, and 2 and 3 shall be measured 摺動子在終端位置,在此時端子 1-2 間, 端子 2-3 間測定之電阻值	Between 1-2 1-2 間 10Ω Max 10Ω 以下	Between 2-3 2-3 間 10Ω Max 10Ω 以下
8	Dielectric strength 耐電壓	Units shall be designed to withstand 300V A.C between resistance elements and case for a period of one minute without damage or arcing. AC 300V 耐 1 分鐘		
9	V.R life 可變電阻壽命	15,000 cycles		
10	Note 其他	Meet or exceed J I S C-- 6 4 4 3 requirements 依照 JISC 6443 普通級碳素系可變電阻器		

STANDARD RESISTANCE TAPER



NO.	DATE	DESCRIPTION			MODEL NAME		
TOL. UNLESS OTHERWISE STATED		DIMENSION	SCALE	DRAWN BY	CHECKED BY	APPROVED BY	DRAWING NO.
less than 10 ±0.3		mm		何 90.8.21 建志	王 90.8.21 茂松	王 90.8.21 茂松	
above 10 ~ 30 ±0.5							
above 30 ~100 ±1.0							
above ±5°							

Common Specification of Lead-Free Soldering and Storage conditions for Potentiometers

以下焊錫條件以可變電阻置於單層 1.6mm 厚度之印刷電路板上測試為基準。

The specification below is based on testing results of 1.6mm thickness single layer printed circuit board.

1. 手工焊錫條件：

For Manual Soldering：

1-1 操作溫度最高 350°C，操作時間 3 秒以內。

To be performed within 3 seconds at 350°C or below.

2. 自動或半自動機台焊錫條件：

For Automated or Semi-Automated Soldering Equipments:

2-1 使用發泡式且比重 0.82 以上的助焊劑，發泡高度以印刷電路板厚度一半為標準，且助劑不能流入可變電阻基板表面及印刷電路板表面。

Flux of 0.82 specific gravity, applied by foam fluxer, shall be used. Foam head shall be limited to the height which is half thickness of printed circuit board to be soldered. No flux should be allowed to run up onto resistive element board of potentiometer and the surface of printed circuit board.

2-2 預熱時間不超過兩分鐘，焊錫接面（即印刷電路板底）最高預熱溫度不超過 100°C。

Regarding preheating, the entire flow duration should not exceed 2 minutes, and soldering surface temperature (undersurface of PCB) shall be settled within 100°C.

2-3 焊錫過程機台設定溫度在 260°C 以下、4 秒以內。

Solder Dipping is to be performed within 4 seconds at 260°C or below.

3. 若回轉型電位器是塑膠軸且帶有檔位，請將主軸先調整至其中一個檔位或中心檔位上才可以進行焊錫作業。

For rotary potentiometer with plastic shaft which have centre detent or multiple detents, the shaft should be settled in relevant detent position prior to soldering process.

4. 手工焊錫、自動或半自動機台焊錫不得超過一回。

Regardless of soldering facility and method, solder dipping or solder smearing must not be carried out more than 1 time.

註：本項焊錫溫度條件不適用於回流焊接作業設備。

Remarks: This specification is not recommended for and applicable in reflow soldering.

焊錫注意事項：

Caution for soldering:

如圖所示，請避免 PCB 上層表面有焊錫

Please avoid soldering on upper surface of P.C.B. as shown.

5. 保管條件(Storage conditions):


產品需儲存在原始的包裝,以及保持常溫

常濕、避免陽光直射、遠離任何腐蝕性氣體。

產品需盡快完全地使用完,建議最慢不要超過

交貨後 6 個月。產品經拆封後，全部的數量都需迅速地使用完。

The products shall be stored in the original packaging and kept at room temperature and humidity, out of direct sunlight, and away from any and all corrosive gas. The products shall be completely used as soon as possible, but no longer than 6 months from the date of delivery. Once product packaging is opened, the complete quantity of such products shall be promptly used.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Alpha \(Taiwan\):](#)

[RV141F-40-20BL-B20K](#) [RV141F-40-20BL-B10K](#) [RV141F-40-20BL-B100K](#) [RV141F-40-20BL-B5K](#) [RV141F-40-20BL-B50K](#) [RV141F-40-20BL-B1M](#) [RV141F-40-20BL-B500K](#) [RV141F-40-20BL-B250K](#)