

3M™ Thermally Conductive Silicone Interface Pads 5592 and 5592S

Product Description


3M™ Thermally Conductive Silicone Interface Pad 5592 and 5592S are soft, silicone elastomers with thermal conductivity of 1.1 W/m-K. With good dielectric properties, they are conformable at low pressure to help minimize stress on components, and fill gaps.

Features and Benefits

- Good thermal stability of the base polymer, with excellent softness of the thermal pad.
- Good thermal conductivity in a soft silicone polymer base.
- The product tack is such that a mechanical means to support the pad in a final assembly is required.
- This “S” version has a permanent PET film, 12 micrometer thick, on one side to help provide for a non-tacky surface, excellent puncture resistance, ease of handling and rework.

Product Construction

3M™ Thermally Conductive Silicone Interface Pads 5592 and 5592S	
Color	White
Pad Type	Filled Silicone Polymer
Pad Thickness	0.5 mm, 1.0 mm, 1.5 mm, 2.0 mm
Primary Filler Type	Ceramic
Top Liner / Film Type	3M pad 5592 – Silicone Coated-Removable Liner / 3M pad 5592S – 12 µm PET Film
Base Liner Thickness	Base Liner 3 mils (75 µm)



Typical Physical Properties and Performance Characteristics

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Property	Value	Method
Product Number¹	3M™ Thermally Conductive Silicone Interface Pads 5592 and 5592S	
Thermal Conductivity (W/m-K)	1.1 W/m-K	3M Test Method with low pressure (<10 psi)
Operating Temperature Range²	-60°C to 125°C	3M Test Method
Hardness Shore 00³	Shore 00 results depend on test method and thickness of the sample tested. Typical results are in the 40-50 Shore 00 range @ 6 mm test thickness without the PET film. Ask 3M for more details on pad softness.	Modified ASTM D2240
Dielectric Breakdown	375 V/mil AC (3M pad 5592S tested)	3M TM (ASTM D149)
Volume Resistivity	3 x 10 ¹² Ohms (3M pad 5592S tested)	ASTM D257
Flammability Rating		
0.5mm	UL 94 V-1	UL 94
1.0mm	UL 94 V-1	UL 94
3.0mm	UL 94 V-0	UL 94

Notes:

¹ 3M pad 5592S has a 12 micrometer PET Film added to provide for a non-tacky surface, increased puncture resistance, and ease of handling and rework.

² Potential Operating Temperature Range (°C). End use application testing will determine final temperature range based on final design and other environmental conditions. Suggested temperature range is based on a 3M Test Method.

³ 3M pad 5592S tested with-out PET film on product.

Application Guidelines

Substrate surfaces should be clean and dry prior to the thermal pad application to help ensure best thermal performance. A clean surface can improve the thermal performance of an application.

- 1) Isopropyl alcohol (isopropanol) applied with a lint-free wipe or swab should be adequate for removing surface contamination such as dust or fingerprints. Do not use “denatured alcohol” or glass cleaners, which often contain oily components. Allow the surface to dry for several minutes before applying the thermal pad. More aggressive solvents (such as acetone, methyl ethyl ketone (MEK) or toluene) may be required to remove heavier contamination (grease, machine oils, solder flux, etc.) but should be followed by a final isopropanol wipe as described above.

Note: Be sure to read and follow the manufacturers’ precautions and directions when using solvents.

- 2) Apply the thermal pad to one substrate at a modest angle with the use of a squeegee, rubber roller or finger pressure to help reduce the potential for air entrapment under the thermal pad during its application. Remove the release liner before application.
- 3) Assemble the part by applying compression to the substrates to help ensure a good wetting of the substrate surfaces with the thermal pads. Rigid substrates are more difficult to assemble without air entrapment as most rigid parts are not flat. Flexible substrates can be assembled to rigid or flexible parts with much less concern about air entrapment because one of the flexible substrate can conform to the other substrates during application.

Application Ideas

- 3M™ Thermally Conductive Silicone Interface Pads are designed to provide a preferential heat-transfer path between heat-generating and cooling devices (e.g., fans, heat pipes and heat sinks).

Storage and Shelf Life

The shelf life of 3M™ Thermally Conductive Interface Silicone Pad 5592 and 5592S is 24 months from the manufacture date when stored in original packaging at 21°C (70°F) and 50% relative humidity.

Regulatory

For regulatory information about this product, contact your 3M representative.

Technical Information

The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer

Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability

Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



Electronics Materials Solutions Division

3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
1-800-251-8634 phone
651-778-4244 fax
www.3M.com/electronics

3M is a trademark of 3M Company.
Please recycle.
© 3M 2014. All rights reserved.
60-5002-0135-9



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[3M:](#)

[5592](#) [5592-1.5](#) [5592-2.0](#) [5592S-0.5](#) [5592S-1.0](#) [5592S-1.5](#) [5592S-2.0](#)