



Slot Mount Series

Slot mount gaskets are a standard in the electronic enclosure industry. These gaskets are used in shorter lengths as ESD contacts and longer lengths as EMI gaskets, which clip into slots or slide onto mounted tracks.



RF Alternate Finger Slot Mount															Black = inches										Red = mm		
P/N	A		B		Finger		Pitch		Mat. Thick		C		D		*E		*F Recommended		*G		Length		Fingers				
11-32AF-XX-16	0.11	2.80	0.32	8.10	0.169	4.30	0.187	4.75	0.004	0.102	0.085	2.159	0.020	0.508	0.09	2.286	0.26	6.604	0.04	1.016	16	406	85				
11-S-32AF-XX-16	0.11	2.80	0.32	8.10	0.169	4.30	0.187	4.75	0.002	0.050	0.085	2.159	0.020	0.508	0.09	2.286	0.26	6.604	0.04	1.016	16	406	85				
22-60AF-XX-16	0.22	5.59	0.60	15.24	0.250	6.35	0.282	7.16	0.005	0.127	0.140	3.556	0.035	0.889	0.14	3.556	0.52	13.208	0.07	1.778	16	406	57				
22-S-60AF-XX-16	0.22	5.59	0.60	15.24	0.250	6.35	0.282	7.16	0.003	0.080	0.140	3.556	0.035	0.889	0.14	3.556	0.52	13.208	0.07	1.778	16	406	57				




**MOUNTING
OPTIONS**
■ Slot

*May vary depending on application


XX - Select material/finish (see page 16)



Alternate Finger Mounting Hole Recommendations




RH Mounting Hole Pattern



Compression/Deflection

(Alternate Finger Slot Mount Series)



Slot Mount Series [cont.]



RH Slot Mount		Black = inches Red= mm																					
P/N	A		B		Finger		Pitch		Mat. Thick		C		D		*N		*O Recommended		*P		Length		Fingers
11-28RH-XX-16	0.11	2.80	0.28	7.11	0.169	4.30	0.187	4.75	0.003	0.076	0.075	1.90	0.02	0.76	0.09	2.29	0.22	5.59	0.04	1.02	16	406	86
11-28RH-XX-17	0.11	2.80	0.28	7.11	0.169	4.30	0.187	4.75	0.003	0.076	0.075	1.90	0.02	0.76	0.09	2.29	0.22	5.59	0.04	1.02	0.17	4	1
11-28RH-XX-36	0.11	2.80	0.28	7.11	0.169	4.30	0.187	4.75	0.003	0.076	0.075	1.90	0.02	0.76	0.09	2.29	0.22	5.59	0.04	1.02	0.36	9	2
11-28RH-XX-54	0.11	2.80	0.28	7.11	0.169	4.30	0.187	4.75	0.003	0.076	0.075	1.90	0.02	0.76	0.09	2.29	0.22	5.59	0.04	1.02	0.54	14	3
11-28RH-XX-73	0.11	2.80	0.28	7.11	0.169	4.30	0.187	4.75	0.003	0.076	0.075	1.90	0.02	0.76	0.09	2.29	0.22	5.59	0.04	1.02	0.73	19	4
11-S-28RH-XX-16	0.11	2.80	0.28	7.11	0.169	4.30	0.187	4.75	0.002	0.050	0.075	1.90	0.02	0.76	0.09	2.29	0.22	5.59	0.04	1.02	16	406	86
11-S-28RH-XX-17	0.11	2.80	0.28	7.11	0.169	4.30	0.187	4.75	0.002	0.050	0.075	1.90	0.02	0.76	0.09	2.29	0.22	5.59	0.04	1.02	0.17	4	1
11-S-28RH-XX-36	0.11	2.80	0.28	7.11	0.169	4.30	0.187	4.75	0.002	0.050	0.075	1.90	0.02	0.76	0.09	2.29	0.22	5.59	0.04	1.02	0.36	9	2
11-S-28RH-XX-54	0.11	2.80	0.28	7.11	0.169	4.30	0.187	4.75	0.002	0.050	0.075	1.90	0.02	0.76	0.09	2.29	0.22	5.59	0.04	1.02	0.54	14	3
11-S-28RH-XX-73	0.11	2.80	0.28	7.11	0.169	4.30	0.187	4.75	0.002	0.050	0.075	1.90	0.02	0.76	0.09	2.29	0.22	5.59	0.04	1.02	0.73	19	4
11-32RH-XX-16	0.11	2.80	0.32	8.10	0.169	4.30	0.187	4.75	0.003	0.102	0.09	2.29	0.02	0.51	0.09	2.29	0.26	6.60	0.04	1.02	16	406	86
11-32RH-XX-17	0.11	2.80	0.32	8.10	0.169	4.30	0.187	4.75	0.003	0.102	0.09	2.29	0.02	0.51	0.09	2.29	0.26	6.60	0.04	1.02	0.17	4	1
11-32RH-XX-36	0.11	2.80	0.32	8.10	0.169	4.30	0.187	4.75	0.003	0.102	0.09	2.29	0.02	0.51	0.09	2.29	0.26	6.60	0.04	1.02	0.36	9	2
11-32RH-XX-54	0.11	2.80	0.32	8.10	0.169	4.30	0.187	4.75	0.003	0.102	0.09	2.29	0.02	0.51	0.09	2.29	0.26	6.60	0.04	1.02	0.54	14	3
11-32RH-XX-73	0.11	2.80	0.32	8.10	0.169	4.30	0.187	4.75	0.003	0.102	0.09	2.29	0.02	0.51	0.09	2.29	0.26	6.60	0.04	1.02	0.73	19	4
11-S-32RH-XX-16	0.11	2.80	0.32	8.10	0.169	4.30	0.187	4.75	0.002	0.050	0.09	2.29	0.02	0.51	0.09	2.29	0.26	6.60	0.04	1.02	16	406	86
11-S-32RH-XX-17	0.11	2.80	0.32	8.10	0.169	4.30	0.187	4.75	0.002	0.050	0.09	2.29	0.02	0.51	0.09	2.29	0.26	6.60	0.04	1.02	0.17	4	1
11-S-32RH-XX-36	0.11	2.80	0.32	8.10	0.169	4.30	0.187	4.75	0.002	0.050	0.09	2.29	0.02	0.51	0.09	2.29	0.26	6.60	0.04	1.02	0.36	9	2
11-S-32RH-XX-54	0.11	2.80	0.32	8.10	0.169	4.30	0.187	4.75	0.002	0.050	0.09	2.29	0.02	0.51	0.09	2.29	0.26	6.60	0.04	1.02	0.54	14	3
11-S-32RH-XX-73	0.11	2.80	0.32	8.10	0.169	4.30	0.187	4.75	0.002	0.050	0.09	2.29	0.02	0.51	0.09	2.29	0.26	6.60	0.04	1.02	0.73	19	4
13-30RH-XX-16	0.13	3.30	0.30	7.62	0.169	4.30	0.187	4.75	0.004	0.102	0.09	2.29	0.03	0.76	0.09	2.29	0.25	6.35	0.05	1.27	16	406	86
13-37RH-XX-16	0.13	3.30	0.37	9.40	0.225	5.715	0.250	6.35	0.003	0.080	0.09	2.29	0.02	0.51	0.09	2.29	0.31	7.87	0.04	1.02	16	406	86
13-37RH-XX-17	0.13	3.30	0.37	9.40	0.225	5.715	0.250	6.35	0.003	0.080	0.09	2.29	0.02	0.51	0.09	2.29	0.31	7.87	0.04	1.02	0.17	4	1
13-37RH-XX-36	0.13	3.30	0.37	9.40	0.225	5.715	0.250	6.35	0.003	0.080	0.09	2.29	0.02	0.51	0.09	2.29	0.31	7.87	0.04	1.02	0.36	9	2
13-37RH-XX-54	0.13	3.30	0.37	9.40	0.225	5.715	0.250	6.35	0.003	0.080	0.09	2.29	0.02	0.51	0.09	2.29	0.31	7.87	0.04	1.02	0.54	14	3
13-37RH-XX-73	0.13	3.30	0.37	9.40	0.225	5.715	0.250	6.35	0.003	0.080	0.09	2.29	0.02	0.51	0.09	2.29	0.31	7.87	0.04	1.02	0.73	19	4
13-S-37RH-XX-16	0.13	3.30	0.37	9.40	0.225	5.715	0.250	6.35	0.002	0.050	0.09	2.29	0.02	0.51	0.09	2.29	0.31	7.87	0.04	1.02	16	406	86
13-S-37RH-XX-17	0.13	3.30	0.37	9.40	0.225	5.715	0.250	6.35	0.002	0.050	0.09	2.29	0.02	0.51	0.09	2.29	0.31	7.87	0.04	1.02	0.17	4	1
13-S-37RH-XX-36	0.13	3.30	0.37	9.40	0.225	5.715	0.250	6.35	0.002	0.050	0.09	2.29	0.02	0.51	0.09	2.29	0.31	7.87	0.04	1.02	0.36	9	2
13-S-37RH-XX-54	0.13	3.30	0.37	9.40	0.225	5.715	0.250	6.35	0.002	0.050	0.09	2.29	0.02	0.51	0.09	2.29	0.31	7.87	0.04	1.02	0.54	14	3
13-S-37RH-XX-73	0.13	3.30	0.37	9.40	0.225	5.715	0.250	6.35	0.002	0.050	0.09	2.29	0.02	0.51	0.09	2.29	0.31	7.87	0.04	1.02	0.73	19	4
22-60RH-XX-16	0.22	5.60	0.60	15.20	0.250	6.40	0.281	7.10	0.005	0.130	0.14	3.56	0.04	1.02	0.14	3.56	0.52	13.21	0.06	1.52	16	406	57
22-60RH-XX-25	0.22	5.60	0.60	15.20	0.250	6.40	0.281	7.10	0.005	0.130	0.14	3.56	0.04	1.02	0.14	3.56	0.52	13.21	0.06	1.52	0.25	6	1
22-60RH-XX-53	0.22	5.60	0.60	15.20	0.250	6.40	0.281	7.10	0.005	0.130	0.14	3.56	0.04	1.02	0.14	3.56	0.52	13.21	0.06	1.52	0.53	14	2
22-S-60RH-XX-16	0.22	5.60	0.60	15.20	0.250	6.40	0.281	7.10	0.003	0.080	0.14	3.56	0.04	1.02	0.14	3.56	0.52	13.21	0.06	1.52	16	406	57
22-S-60RH-XX-25	0.22	5.60	0.60	15.20	0.250	6.40	0.281	7.10	0.003	0.080	0.14	3.56	0.04	1.02	0.14	3.56	0.52	13.21	0.06	1.52	0.25	6	1
22-S-60RH-XX-53	0.22	5.60	0.60	15.20	0.250	6.40	0.281	7.10	0.003	0.080	0.14	3.56	0.04	1.02	0.14	3.56	0.52	13.21	0.06	1.52	0.53	14	2



**MOUNTING
OPTIONS**
■ Slot

*May vary depending on application

XX - Select material/finish (see page 16)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[LeaderTech:](#)

[22-60RH-BD-.25](#)