








PRODUCT NO.
10116658-#52**



NOTE
1. PRODUCT SPEC. : GS-12-195
2. PACKAGING SPEC. : GS-14-786

3. MATERIAL:
1) HOUSING : LCP, UL94V-0, COLOR BLACK
2) CONTACT : COPPER ALLOY
3) HOLD DOWN : BRASS

4. FINISH
1) TERMINAL : SEE TABLE
2) HOLD DOWN : SEE TABLE


5. CO-PLANARITY : 0.1 MAX.(INCLUDE HOLD DOWN)

6. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.




7. THE HOUSING WILL WITHSTAND EXPOSURE TO 260° PEAK TEMPERATURE FOR 10 SECONDS IN A REFLOW SOLDER APPLICATION.

www.fciconnect.com				surface	tolerance std	projection	MM	
				ASME Y14.5	ASME Y14.5			
				TOLERANCES UNLESS OTHERWISE SPECIFIED			size	Scale
				ANGULAR	LINEAR	0.X	±0.3	1:1
						0.XX	±0.15	
						0.XXX	±0.08	
				0°	±5°	ECN		
				Product family			Spec ref	RELEASED
				DDR II 0.6mm PITCH 200 POS			10116658	Rev.
				STANDARD TYPE ASS'Y			A	
				catalog no			CUSTOMER COPY	sheet 1 of 4

PRODUCT NO.
10116658-52**



RECOMMENDED MOUNTING P.C.B LAYOUT



DETAIL Y
SCALE 10:1

1		2		3		4		5		6		7		8	
PRODUCT NO.		LOCATING PEG		TERMINAL CONTACT AREA FINISH		HOLD DOWN FINISH		SOLDER TAIL FINISH							
A	10116658-052FSLF	YES		Au FLASH		PURE Sn PLATING		Au FLASH		10116658- LF For Rohs OPTIONS: TAIL PLATING CODE MUST BE 0~3. HOLD DOWN PLATING CODE MUST BE "S". "LF" CODE IS EXIST IN THE END. EX: 10116658-252TSLF FOR NOT Rohs COMPATIBLE: THIS "LF" CODE IS "BLANK". EX:10116658-452TS <PACKING METHOD> R : TAPE REEL DEFAULT : TRAY <HOLD DOWN FINISH> S : Pure Sn B : Sn-Pb <CONTACT AREA FINISH> F : Au FLASH T : Au 0.3μm MIN. A : Au 0.76μm MIN. <TOTAL HEIGHT> 52 : 5.2mm <LOCATING PEG, SOLDER TAIL FINISH> 0 : YES, Au FLASH 1 : NO, Au FLASH 2 : YES, Pure Sn PLATING 3 : NO, Pure Sn PLATING 4 : YES, Sn-Pb PLATING 5 : NO, Sn-Pb PLATING					
	10116658-152FSLF	NO													
	10116658-052TSLF	YES		Au 0.3μm MIN.											
	10116658-152TSLF	NO													
	10116658-052ASLF	YES		Au 0.76μm MIN.											
10116658-152ASLF	NO														
B	10116658-052FB	YES		Au FLASH		Sn-Pb PLATING									
	10116658-152FB	NO													
	10116658-052TB	YES		Au 0.3μm MIN.											
	10116658-152TB	NO													
	10116658-052AB	YES		Au 0.76μm MIN.											
10116658-152AB	NO														
C	10116658-252FSLF	YES		Au FLASH		PURE Sn PLATING		Pure Sn PLATING							
	10116658-352FSLF	NO													
	10116658-252TSLF	YES		Au 0.3μm MIN.											
	10116658-352TSLF	NO													
	10116658-252ASLF	YES		Au 0.76μm MIN.											
10116658-352ASLF	NO														
D	10116658-252FB	YES		Au FLASH		Sn-Pb PLATING									
	10116658-352FB	NO													
	10116658-252TB	YES		Au 0.3μm MIN.											
	10116658-352TB	NO													
	10116658-252AB	YES		Au 0.76μm MIN.											
10116658-352AB	NO														
E	10116658-452FS	YES		Au FLASH		PURE Sn PLATING		Sn-Pb PLATING							
	10116658-552FS	NO													
	10116658-452TS	YES		Au 0.3μm MIN.											
	10116658-552TS	NO													
	10116658-452AS	YES		Au 0.76μm MIN.											
10116658-552AS	NO														
F	10116658-452FB	YES		Au FLASH		Sn-Pb PLATING									
	10116658-552FB	NO													
	10116658-452TB	YES		Au 0.3μm MIN.											
	10116658-552TB	NO													
	10116658-452AB	YES		Au 0.76μm MIN.											
10116658-552AB	NO														

FCI

Copyright FCI.

FCI

title
DDR II 0.6mm PITCH 200 POS
STANDARD TYPE ASS'Y
catalog no

10116658
CUSTOMER COPY

Rev.
A
sheet 4 of 4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10116658-252ASRLF](#) [10116658-052TSLF](#) [10116658-252FSLF](#) [10116658-352ASLF](#) [10116658-352FSLF](#)
[10116658-052ASRLF](#) [10116658-252TSLF](#) [10116658-052ASLF](#) [10116658-052FSRLF](#) [10116658-052TSRLF](#)