



REV	DOCUMENT	CHANGED BY	CHECK
6	0038111	PK 20MAY08	ASD



RELEASE NO.	SR - 7570
REPLACES	-

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± 0.030 TWO PLACE .XX ± 0.015 THREE PLACE .XXX ± 0.005 FOUR PLACE .XXXX ± ANGLES ±		DRAWN	VK	17OCT07	Honeywell				
OPERATING FORCE — — — - 3 OZ MAX		CONTACT ARRANGEMENT S P D T					CHECK	RJ	17OCT07					
RELEASE FORCE— — — — - 1 OZ MIN		30 VOLTS DC RATING			0.030 0.015 0.005		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - BASIC				
DIFFERENTIAL TRAVEL— — — .002 MAX		SEA LEVEL 50,000 FT												
OVERTRAVEL — — — — — .005 MIN		INDUCTIVE 3 AMP 2.5 AMP					INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME		REV
		RESISTIVE 5 AMP 5 AMP								B	I	21SM144		6
		MAXIMUM INRUSH 24 AMP			THIRD ANGLE PROJECTION 		RASTER			SCALE	-	WEIGHT .006 LB MAX	SHEET 1 OF 1	
		APPROVALS KEMA, CE 5A, 250V ~ T85 1E4 												
		UL, CSA 5A, 250 VAC   BRAND L4												

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[21SM144](#)