


HONEYWELL PART NUMBER
341SM169-H252
PRODUCT CODE TZA2939

CORROSION RESISTANT
STEEL ACTUATOR

REV	DOCUMENT	CHANGED BY	CHECK
3	0041782	PK 21JUL08	ASD



NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375 ±.002 CENTERS
- 2 - TERMINALS ARE PLATED FOR SOLDERING
- 3 - SWITCH WILL WITHSTAND TEMPERATURE OF 250°F
- 4 CHARACTERISTICS TAKEN AT POINT "A"

RELEASE NO.	PR - 19095
REPLACES	X93276 - SM

CHARACTERISTICS 		ELECTRICAL DATA		DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± TWO PLACE .XX ± THREE PLACE .XXX ± FOUR PLACE .XXXX ± ANGLES ± 0.030 0.015 0.005		DRAWN	VK	03 DEC 07						
OPERATING FORCE — — 45 GRAMS MAX		CONTACT ARRANGEMENT S P D T				CHECK	RJ	03 DEC 07						
RELEASE FORCE— — — 7 GRAMS MIN		APPROVALS	KEMA, CE	11A 250V ~ T85 1E4 5A 30 Vdc T85 1E4 		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - BASIC					
DIFFERENTIAL TRAVEL— — — .018 MAX				UL, CSA	11A 1/4 HP 125 250 VAC 5A 30 VDC  	BRAND L190	INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE B	TYPE I	DRAWING NAME 341SM169-H252		REV 3
OVERTRAVEL — — — — — .017 MIN							THIRD ANGLE PROJECTION 			RASTER			SCALE -	WEIGHT .006 LB MAX

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[341SM169-H252](#)