

5x20mm / No. 201P

DIN 41571, T.2, 250V, M

Specifications



Time-Current Characteristic

Medium Time Lag (M)

Standard

DIN 41571, T.2

Approvals

cURus

Features

Visual fault indication
Direct solderable or plug-in versions
Worldwide availability

Packaging

000: Bulk (1000 pcs.)
002: Bulk (20x10 pcs.)
043: With mounted holder - Tape/Reel (1250 pcs.)
on request

Materials

Tube: Glass
End Caps: Nickel-plated brass
Optional Holders: Nickel-plated caps
Tin-plated copper wires

Operating Temperature

-25°C to +70°C (consider de-rating)

Climatic Category

-25°C/+70°C/21 days (EN 60068-1..3)

Stock Conditions

+10°C to +60°C
relative humidity ≤ 75% yearly average,
without dew, maximum value for 30 days-95%

Vibration Resistance

24 cycles at 15 min. each (EN 60068-2-6)
10 - 60Hz at 0.75mm amplitude
60 - 2000Hz at 10g acceleration

Solderability

260°C, ≤ 3 sec. (Wave)
350°C, ≤ 1 sec. (Hand)

Soldering Heat Resistance

260°C, 10 sec. (IEC 68-2-20)


Marking

Ⓜ, M, Current Rating, 250V, C

Unit Weight

1.1g (approx.)
2.1g (with leads)

Dimensions (mm)



Optional Holders

"P" = leadfree



Limits for Pre-arcing Time

Rated Current	$1.5 \times I_N$	$2.1 \times I_N$	$4 \times I_N$	$10 \times I_N$
32mA ... 1.25A	> 1h	< 10 min	40ms ... 2s	5ms ... 90ms

Permissible continuous operating current is ≤ 100% at ambient temperature of 23°C (73.4°F).

Rated Current	Amp Code	Voltage Rating	Breaking Capacity	Voltage Drop $1.0 \times I_N$ max. (mV)	Power Dissipation $1.5 \times I_N$ Ⓜ max. (W)	Melting Integral $10 \times I_N$ Ⓜ min. (A²s)	Approvals
63mA	0063	250V		600	0.1	0.011	•
80mA	0080	250V		540	0.2	0.017	•
100mA	0100	250V		500	0.2	0.022	•
125mA	0125	250V		440	0.2	0.033	•
160mA	0160	250V		400	0.2	0.085	•
200mA	0200	250V		340	0.3	0.12	•
250mA	0250	250V	80A / 250VAC	320	0.3	0.13	•
315mA	0315	250V	50-60Hz	300	0.3	0.16	•
400mA	0400	250V	cos φ = 1.0	230	0.4	0.28	•
500mA	0500	250V		210	0.4	0.35	•
630mA	0630	250V		190	0.5	0.6	•
800mA	0800	250V		170	0.6	1.1	•
1.00A	1100	250V		160	0.7	2.0	•
1.25A	1125	250V		160	0.8	3.2	•


Note: 1.00 means the number one with two decimal places. 1,000 means the number one thousand.

Order Information

Qty.	Order-Number	Series	Amp Code	Packaging
		201P		

Specifications are subject to change without notice

5x20mm / No. 201



Contact Littelfuse for individual I-t curves

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

[20100800001](#) [20100800021](#) [20103150001](#) [20103150021](#) [20100630021](#) [20100630001](#) [20101600021](#)
[20101600001](#) [20100630001P](#) [20100630021P](#) [20100630301P](#) [20100630531P](#) [20100800001P](#) [20100800021P](#)
[20100800301P](#) [20100800431P](#) [20100800531P](#) [20101000001P](#) [20101000021P](#) [20101000301P](#) [20101000431P](#)
[20101000531P](#) [20101250001P](#) [20101250021P](#) [20101250301P](#) [20101250431P](#) [20101250531P](#) [20101600001P](#)
[20101600021P](#) [20101600301P](#) [20101600431P](#) [20101600531P](#) [20102000001P](#) [20102000021P](#) [20102000301P](#)
[20102000431P](#) [20102000531P](#) [20102500001P](#) [20102500021P](#) [20102500301P](#) [20102500531P](#) [20103150001P](#)
[20103150021P](#) [20103150301P](#) [20104000001P](#) [20104000021P](#) [20105000001P](#) [20105000021P](#) [20105000301P](#)
[20106300001P](#) [20106300021P](#) [20108000001P](#) [20108000021P](#) [20111000001P](#) [20111000021P](#) [20111000431P](#)
[20111250001P](#) [20111250021P](#) [20100320431](#) [20102500021](#) [20102500001](#) [20108000021](#) [20108000001](#)
[20101250001](#) [20111250001](#) [20111250021](#) [20105000021](#) [20101000021](#) [20102000021](#) [20111000021](#) [20102000001](#)
[20101000001](#) [20105000001](#) [20111000001](#) [20106300001](#) [20106300021](#) [20100630431P](#) [20100500001P](#)