













# PM Series

## Standard Size Slide Switches

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE

SPECIFICATIONS	FEATURES
<b>Contact rating:</b> 6 Amps at 125 VAC, 3 Amps at 250 VAC <b>Initial contact resistance:</b> 30 milliohms max. <b>Insulation resistance:</b> 100 megohms min. at 500 VDC <b>Dielectric strength:</b> 1000 VAC for 1 minute (min.) <b>Electrical life:</b> 10,000 cycles min. <b>Operating temperature range:</b> -20°C to +60°C <b>Actuation force:</b> 500g ± 200g <b>Solder heat resistance:</b> 260°C max. for 3 seconds <b>Solvent washing permissible</b>	<ul style="list-style-type: none"> <li>● Wash-through open frame construction.</li> <li>● UL &amp; CSA recognized.</li> <li>● Threaded mounting holes standard - M3X0.5.</li> <li>● Panel mounting.</li> </ul>
	MATERIALS
	<b>Contacts:</b> Silver plated phosphor bronze <b>Terminals:</b> Tin plated brass <b>Actuator:</b> Nylon, type 6/6 <b>Base:</b> Phenolic laminated sheet <b>Frame:</b> Zinc plated steel

MODEL NO.			
<b>PM13B012</b>			
	<p><b>1P2T</b></p>  <p>● = COMMON</p>	 <p><b>MECHANICAL OUTLINE</b></p>	 <p><b>PANEL CUTOUT</b></p>
<b>PM13B022</b>			
	<p><b>2P2T</b></p>  <p>● = COMMON</p>	 <p><b>MECHANICAL OUTLINE</b></p>	 <p><b>P. C. BOARD LAYOUT</b></p>
<b>PM13B022P</b>			
	<p><b>2P2T</b></p>  <p>● = COMMON</p>	 <p><b>MECHANICAL OUTLINE</b></p>	 <p><b>PANEL CUTOUT</b></p>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Apem:](#)

[PM13B022](#) [PM13B022P](#)