


SPECIFICATIONS

	GRADE	
SILIKROME®	COMMERCIAL	MILITARY
Material	Silicone Rubber ASTM D 1418	Silicone Rubber conforming to A-A-59588 Class II GR 50
Temperature Range	-112°F to +400°F (-80°C to +204°C)	-160°F to +450°F (-106°C to +260°C)
	-112°F to +575°F (-80°C to +302°C)	
Shelf Life	25 Years (minimum)	
Resistant to	Salt spray, sunlight, ozone, cleaning solutions, and most acids	
Physical Characteristics	Flexible, non-breakable, re-usable. Acts as shock mount. Protects against shattering. Easy to mount.	



SECTION AA

B	REDRAWN and MAT'L CHANGED				S. GOK	05.28.09
A	CAD COMPUTER GENERATED					1-10-03
REV.	DESCRIPTION					DATE
MAXIMUM AND MINIMUM MEASUREMENTS ARE STATED DIRECTLY ON EACH DIMENSION.	TITLE:	SILIKROMES® COLORED FILTERS FOR INCANDESCENT T-2 LAMPS	ENG.	S. GOK	05.28.09	
			DWN.	J. SCHULTZ	3-23-64	
			CHKD.	J. CELLA	05.28.09	
MAT'L: SEE ABOVE		APM-HEXSEAL CORPORATION	SCALE	DWG. NO.	1813/15	
COLOR: SPECIFY			4 : 1			

THIS DRAWING COVERS PROPRIETARY ITEM AND IS THE PROPERTY OF THE APM-HEXSEAL CORPORATION.
THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE WRITTEN APPROVAL OF AN OFFICER OF THE APM-HEXSEAL CORPORATION.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[APM HEXSEAL:](#)

[1813/15](#) [1813/15 B1 C](#) [1813/15 G1 C](#) [1813/15 R2 C](#) [1813/15 Y1 C](#)