


Radial Leaded Fuse, PTC, 60 VDC



16.0 - 60.0VDC · 0.1 - 11 A

Approvals and Compliances

Description

- THT standard industry type
- Directly solderable on printed circuit boards

Applications

- Computer & Peripherals
- General electronics
- Automotive applications

References

[Packaging Details](#)

Weblinks

[pdf datasheet](#), [html-datasheet](#), [General Product Information](#), [Packaging details](#), [Distributor-Stock-Check](#), [Detailed request for product](#)

Technical Data

V max	16.0 - 60.0VDC
I _{max}	40 - 100A
I hold	0.1 - 11 A
Attachment	PCB,THT
Allowable Operation Temperature	-40 °C to 85 °C
Material: Terminals	see variants
Weight	0.35 g
Storage Conditions	0 °C to 40 °C, max. 70% r.h.
Product Marking	 Type, I hold

Soldering Methods	Wave Soldering Profile
Solderability	235 °C / 2 sec
Resistance to Soldering Heat	260 °C / 10 sec
Passing Aging	+85 °C, 1000 Hours -> +/- 5% Typical Resistance Change
Humidity Aging	+85 °C, 85% r.h., 1000 Hours -> +/- 5% Typical Resistance Change
Thermal Shock	MIL-STD-202, Method 107 (+125 °C to -55 °C, 10 Cycles) -> +/- 15% Typical Resistance Change
Vibration	MIL-STD-883C, Method 2007.1, Test Condition A
Resistance to Solvents	MIL-STD-202, Methode 215
Flammability	UL 94V-0

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in [Details about Approvals](#)

Approvals

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products.

Approval Reference Type: PFRA

Approval Logo	Certificates	Certification Body	Description
	TUEV Approvals	TUEV	Technischer Überwachungsverein
	UL Approvals	UL	UL File Number: E172175

Product standards

Product standards that are referenced

Organization	Design	Standard	Description
	Designed according to	UL 1434	Thermistor-type devices
	Designed according to	CSA 22.2 No. 0 TIL No. CA-3A	General requirements - Canadian electrical code, part II

Application standards

Application standards where the product can be used


Organization	Design	Standard	Description
	Designed for applications acc.	IEC/UL 60950	IEC 60950-1 includes the basic requirements for the safety of information technology equipment.

Compliances


The product complies with following Guide Lines

Identification	Details	Initiator	Description
	CE declaration of conformity	SCHURTER AG	The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008.
	RoHS	SCHURTER AG	EU Directive RoHS 2011/65/EU
	China RoHS	SCHURTER AG	The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.
	REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.

Dimension [mm]




PFRA.010 - PFRA.185



PFRA.250 - PFRA.1100

Time-Current-Curves



Letter heights and Fonts

A max [mm]	Insert depth	C min [mm]	C max [mm]	D min [mm]	E max [mm]	Ø Lead [mm]	Terminal	Order Number	
7.4	12.7	4.4	5.8	7.6	3.1	0.51	Tin-Pated NiCu	PFRA.010	■
7.4	12.7	4.4	5.8	7.6	3.1	0.51	Tin-Pated NiCu	PFRA.010.2	
7.4	12.7	4.4	5.8	7.6	3.1	0.51	Tin-Plated CuFe	PFRA.017	■
7.4	12.7	4.4	5.8	7.6	3.1	0.51	Tin-Plated CuFe	PFRA.017.2	
7.4	12.7	4.4	5.8	7.6	3.1	0.51	Tin-Plated CuFe	PFRA.020	■
7.4	12.7	4.4	5.8	7.6	3.1	0.51	Tin-Plated CuFe	PFRA.020.2	
7.4	12.7	4.4	5.8	7.6	3.1	0.51	Tin-Plated CuFe	PFRA.025	■
7.4	12.7	4.4	5.8	7.6	3.1	0.51	Tin-Plated CuFe	PFRA.025.2	
7.4	13.4	4.4	5.8	7.6	3.1	0.51	Tin-Plated CuFe	PFRA.030	■
7.4	13.4	4.4	5.8	7.6	3.1	0.51	Tin-Plated CuFe	PFRA.030.2	
7.4	13.7	4.4	5.8	7.6	3.1	0.51	Tin-Plated CuFe	PFRA.040	■
7.4	13.7	4.4	5.8	7.6	3.1	0.51	Tin-Plated CuFe	PFRA.040.2	
7.9	13.7	4.4	5.8	7.6	3.1	0.51	see variants	PFRA.050	■
7.9	13.7	4.4	5.8	7.6	3.1	0.51	see variants	PFRA.050.2	
9.7	15.2	4.4	5.8	7.6	3.1	0.51	see variants	PFRA.065	■
9.7	15.2	4.4	5.8	7.6	3.1	0.51	see variants	PFRA.065.2	
10.4	16	4.4	5.8	7.6	3.1	0.51	see variants	PFRA.075	■
10.4	16	4.4	5.8	7.6	3.1	0.51	see variants	PFRA.075.2	
11.7	16.7	4.4	5.8	7.6	3.1	0.51	see variants	PFRA.090	■
11.7	16.7	4.4	5.8	7.6	3.1	0.51	see variants	PFRA.090.2	
8.9	14	4.4	5.8	7.6	3	0.51	see variants	PFRA.110	■
8.9	14	4.4	5.8	7.6	3	0.51	see variants	PFRA.110.2	
8.9	18.9	4.4	5.8	7.6	3	0.51	see variants	PFRA.135	
8.9	18.9	4.4	5.8	7.6	3	0.51	see variants	PFRA.135.2	
10.2	16.8	4.4	5.8	7.6	3	0.51	see variants	PFRA.160	■
10.2	16.8	4.4	5.8	7.6	3	0.51	see variants	PFRA.160.2	
12	18.4	4.4	5.8	7.6	3	0.51	see variants	PFRA.185	■
12	18.4	4.4	5.8	7.6	3	0.51	see variants	PFRA.185.2	
12	18.3	4.4	5.8	7.6	3	0.81	see variants	PFRA.250	■
12	18.3	4.4	5.8	7.6	3	0.81	see variants	PFRA.250.2	
12	18.3	4.4	5.8	7.6	3	0.81	see variants	PFRA.300	■
12	18.3	4.4	5.8	7.6	3	0.81	see variants	PFRA.300.2	
14.4	24.8	4.4	5.8	7.6	3	0.81	see variants	PFRA.400	■
14.4	24.8	4.4	5.8	7.6	3	0.81	see variants	PFRA.400.2	
17.4	24.9	9.5	10.9	7.6	3	0.81	see variants	PFRA.500	■
19.3	31.9	9.5	10.9	7.6	3	0.81	see variants	PFRA.600	
22.1	29.8	9.5	10.9	7.6	3	0.81	see variants	PFRA.700	
24.2	32.9	9.5	10.9	7.6	3	0.81	see variants	PFRA.800	■
24.2	32.9	9.5	10.9	7.6	3	0.81	see variants	PFRA.900	
24.2	32.9	9.5	10.9	7.6	3	0.81	see variants	PFRA.1100	

■ Most Popular.

Availability for all products can be searched real-time: <https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

Thermal Derating Chart Ihold [A]

-40 °C	-20 °C	0 °C	23 °C	40 °C	50 °C	60 °C	70 °C	85 °C	Order Number	
0.16	0.14	0.12	0.1	0.08	0.07	0.06	0.05	0.04	PFRA.010	■
0.16	0.14	0.12	0.1	0.08	0.07	0.06	0.05	0.04	PFRA.010.2	
0.26	0.23	0.2	0.17	0.14	0.12	0.11	0.09	0.07	PFRA.017	■
0.26	0.23	0.2	0.17	0.14	0.12	0.11	0.09	0.07	PFRA.017.2	
0.31	0.27	0.24	0.2	0.16	0.14	0.13	0.11	0.08	PFRA.020	■
0.31	0.27	0.24	0.2	0.16	0.14	0.13	0.11	0.08	PFRA.020.2	
0.39	0.34	0.3	0.25	0.2	0.18	0.16	0.14	0.1	PFRA.025	■

-40 °C	-20 °C	0 °C	23 °C	40 °C	50 °C	60 °C	70 °C	85 °C	Order Number
0.39	0.34	0.3	0.25	0.2	0.18	0.16	0.14	0.1	PFRA.025.2
0.47	0.41	0.36	0.3	0.24	0.22	0.19	0.16	0.12	PFRA.030
0.47	0.41	0.36	0.3	0.24	0.22	0.19	0.16	0.12	PFRA.030.2
0.62	0.54	0.48	0.4	0.32	0.29	0.25	0.22	0.16	PFRA.040
0.62	0.54	0.48	0.4	0.32	0.29	0.25	0.22	0.16	PFRA.040.2
0.78	0.68	0.6	0.5	0.41	0.36	0.32	0.27	0.2	PFRA.050
0.78	0.68	0.6	0.5	0.41	0.36	0.32	0.27	0.2	PFRA.050.2
1.01	0.88	0.77	0.65	0.53	0.47	0.41	0.35	0.26	PFRA.065
1.01	0.88	0.77	0.65	0.53	0.47	0.41	0.35	0.26	PFRA.065.2
1.16	1.02	0.89	0.75	0.61	0.54	0.47	0.41	0.3	PFRA.075
1.16	1.02	0.89	0.75	0.61	0.54	0.47	0.41	0.3	PFRA.075.2
1.4	1.22	1.07	0.9	0.73	0.65	0.57	0.49	0.36	PFRA.090
1.4	1.22	1.07	0.9	0.73	0.65	0.57	0.49	0.36	PFRA.090.2
1.6	1.43	1.27	1.1	0.91	0.85	0.75	0.67	0.57	PFRA.110
1.6	1.43	1.27	-	0.91	0.85	0.75	0.67	0.57	PFRA.110.2
1.96	1.76	1.55	1.35	1.12	1.04	0.92	0.82	0.7	PFRA.135
1.96	1.76	1.55	1.35	1.12	1.04	0.92	0.82	0.7	PFRA.135.2
2.32	2.08	1.84	1.6	1.33	1.32	1.09	0.98	0.83	PFRA.160
2.32	2.08	1.84	1.6	1.33	1.32	1.09	0.98	0.83	PFRA.160.2
2.68	2.41	2.13	1.85	1.54	1.42	1.26	1.13	0.96	PFRA.185
2.68	2.41	2.13	1.85	1.54	1.42	1.26	1.13	0.96	PFRA.185.2
3.63	3.25	2.88	2.5	2.08	1.93	1.7	1.53	1.3	PFRA.250
3.63	3.25	2.88	2.5	2.08	1.93	1.7	1.53	1.3	PFRA.250.2
4.35	3.9	3.45	3	2.49	2.31	2.04	1.83	1.56	PFRA.300
4.35	3.9	3.45	3	2.49	2.31	2.04	1.83	1.56	PFRA.300.2
5.8	5.2	4.6	4	3.32	3.08	2.72	2.44	2.08	PFRA.400
5.8	5.2	4.6	4	3.32	3.08	2.72	2.44	2.08	PFRA.400.2
7.25	6.5	5.75	5	4.15	3.85	3.4	3.05	2.6	PFRA.500
8.7	7.8	6.9	6	4.98	4.62	4.08	3.66	3.12	PFRA.600
10.1	9.1	8.05	7	5.81	5.39	4.76	4.27	3.64	PFRA.700
11.6	10.4	9.2	8	6.64	6.16	5.44	4.88	4.16	PFRA.800
13	11.7	10.3	9	7.47	6.93	6.12	5.49	4.68	PFRA.900
16.1	14.6	13.1	11	9.4	8.8	7.8	6.9	5.2	PFRA.1100

Most Popular:

Availability for all products can be searched real-time:<https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

Electrical Characteristics at 23 °C

V max [VDC]	I max [A]	I hold [A]	I trip [A]	R initial min [Ω]	R initial max [Ω]	R 1hour max [Ω]	Max Time to trip [A]	Max Time to Trip [s]	Tripped Power Dissipation [W]	Order Number
60.0	40	0.1	0.2	2.5	4.5	7.5	0.5	4	0.38	PFRA.010
60.0	40	0.1	0.2	2.5	4.5	7.5	0.5	4	0.38	PFRA.010.2
60.0	40	0.17	0.34	2	3.2	8	0.85	3	0.48	PFRA.017
60.0	40	0.17	0.34	2	3.2	8	0.85	3	0.48	PFRA.017.2
60.0	40	0.2	0.4	1.5	2.84	4.4	1	2.2	0.40	PFRA.020
60.0	40	0.2	0.4	1.5	2.84	4.4	1	2.2	0.40	PFRA.020.2
60.0	40	0.25	0.5	1	1.95	3	1.25	2.5	0.45	PFRA.025
60.0	40	0.25	0.5	1	1.95	3	1.25	2.5	0.45	PFRA.025.2
60.0	40	0.3	0.6	0.76	1.36	2.1	1.5	3	0.50	PFRA.030
60.0	40	0.3	0.6	0.76	1.36	2.1	1.5	3	0.50	PFRA.030.2
60.0	40	0.4	0.8	0.52	0.86	1.29	2	3.8	0.55	PFRA.040
60.0	40	0.4	0.8	0.52	0.86	1.29	2	3.8	0.55	PFRA.040.2
60.0	40	0.5	1	0.41	0.77	1.17	2.5	4	0.75	PFRA.050
60.0	40	0.5	1	0.41	0.77	1.17	2.5	4	0.75	PFRA.050.2
60.0	40	0.65	1.3	0.27	0.48	0.72	3.25	5.3	0.90	PFRA.065

V max [VDC]	I max [A]	I hold [A]	I trip [A]	R initial min [Ω]	R initial max [Ω]	R 1hour max [Ω]	Max Time to trip [A]	Max Time to Trip [s]	Tripped Power Dissipation [W]	Order Number
60.0	40	0.65	1.3	0.27	0.48	0.72	3.25	5.3	0.90	PFRA.065.2
60.0	40	0.75	1.5	0.18	0.4	0.6	3.75	6.3	0.90	PFRA.075
60.0	40	0.75	1.5	0.18	0.4	0.6	3.75	6.3	0.90	PFRA.075.2
60.0	40	0.9	1.8	0.14	0.31	0.47	4.5	7.2	1.00	PFRA.090
60.0	40	0.9	1.8	0.14	0.31	0.47	4.5	7.2	1.00	PFRA.090.2
30.0	40	1.1	2.2	0.1	0.18	0.27	5.5	6.6	0.70	PFRA.110
30.0	40	-	2.2	0.1	0.18	0.27	5.5	6.6	0.70	PFRA.110.2
30.0	40	1.35	2.7	0.065	0.115	0.17	6.75	7.3	0.80	PFRA.135
30.0	40	1.35	2.7	0.065	0.115	0.17	6.75	7.3	0.80	PFRA.135.2
30.0	40	1.6	3.2	0.055	0.105	0.15	8	8	0.90	PFRA.160
30.0	40	1.6	3.2	0.055	0.105	0.15	8	8	0.90	PFRA.160.2
30.0	40	1.85	3.7	0.04	0.07	0.11	9.25	8.7	1.00	PFRA.185
30.0	40	1.85	3.7	0.04	0.07	0.11	9.25	8.7	1.00	PFRA.185.2
30.0	40	2.5	5	0.025	0.048	0.07	12.5	10.3	1.20	PFRA.250
30.0	40	2.5	5	0.025	0.048	0.07	12.5	10.3	1.20	PFRA.250.2
30.0	40	3	6	0.02	0.05	0.08	15	10.8	2.00	PFRA.300
30.0	40	3	6	0.02	0.05	0.08	15	10.8	2.00	PFRA.300.2
30.0	40	4	8	0.01	0.03	0.05	20	12.7	2.50	PFRA.400
30.0	40	4	8	0.01	0.03	0.05	20	12.7	2.50	PFRA.400.2
30.0	40	5	10	0.01	0.03	0.05	25	14.5	3.00	PFRA.500
30.0	40	6	12	0.005	0.02	0.04	30	16	3.50	PFRA.600
30.0	40	7	14	0.005	0.02	0.03	35	17.5	3.80	PFRA.700
30.0	40	8	16	0.005	0.02	0.03	40	18.8	4.00	PFRA.800
30.0	40	9	18	0.005	0.01	0.02	45	20	4.20	PFRA.900
16.0	100	11	22	0.003	0.01	0.01	40	20	4.50	PFRA.1100

Most Popular:

Availability for all products can be searched real-time: <https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

Packaging Unit	PFRA.xxxx	Bulk (500 pcs.)
	PFRA.010.2 - PFRA.160.2	Taped 34 cm Reel (3000 pcs.)
	PFRA.185.2 - PFRA.400.2	Taped 34 cm Reel (1500 pcs.)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Schurter:

[PFRA.075.2](#) [PFRA.017](#) [PFRA.090.2](#) [PFRA.600](#) [PFRA.185.2](#) [PFRA.300.2](#) [PFRA.160](#) [PFRA.400.2](#) [PFRA.250.2](#)
[PFRA.025](#) [PFRA.065](#) [PFRA.110.2](#) [PFRA.040](#) [PFRA.050](#) [PFRA.050.2](#) [PFRA.135.2](#) [PFRA.090](#) [PFRA.135](#)
[PFRA.250](#) [PFRA.020.2](#) [PFRA.900](#) [PFRA.010](#) [PFRA.010.2](#) [PFRA.250.2.010](#) [PFRA.800](#) [PFRA.185](#) [PFRA.400](#)
[PFRA.500](#) [PFRA.030](#) [PFRA.110](#) [PFRA.040.2](#) [PFRA.020](#) [PFRA.160.2](#) [PFRA.017.2](#) [PFRA.300](#) [PFRA.700](#)
[PFRA.075](#) [PFRA.065.2](#) [PFRA.025.2](#) [PFRA.030.2](#) [PFRA.1100](#)