

8A, 400V - 1000V Surface Mount Glass Passivated Rectifiers

FEATURES

- Low forward voltage drop
- Ideal for automated placement
- High surge current capability
- Compliant to RoHS Directive 2011/65/EU and in accordance to WEEE 2002/96/EC
- Halogen-free according to IEC 61249-2-21



MECHANICAL DATA

Case: DO-214AB (SMC)

Molding compound, UL flammability classification rating 94V-0

Moisture sensitivity level: level 1, per J-STD-020

Part no. with suffix "H" means AEC-Q101 qualified

Packing code with suffix "G" means green compound (halogen-free)

Terminal: Matte tin plated leads, solderable per JESD22-B102

Meet JESD 201 class 2 whisker test

Polarity: Indicated by cathode band

Weight: 0.27 g (approximately)

DO-214AB (SMC)

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS (T _A =25°C unless otherwise noted)							
PARAMETER		SYMBOL	S8GC	S8JC	S8KC	S8MC	UNIT
Maximum repetitive peak reverse voltage		V _{RRM}	400	600	800	1000	V
Maximum RMS voltage		V _{RMS}	280	420	560	700	V
Maximum DC blocking voltage		V _{DC}	400	600	800	1000	V
Maximum average forward rectified current		I _{F(AV)}	8				A
Peak forward surge current 8.3 ms single half sine-wave	T _J =25°C	I _{FSM}	200				A
	T _J =125°C		170				
Peak forward surge current 1.0 ms single half sine-wave	T _J =25°C	I _{FSM}	600				A
	T _J =125°C		338				
Maximum instantaneous forward voltage (Note 1) I _F = 8 A		V _F	0.985				V
Maximum reverse current @ rated V _R	T _J =25°C	I _R	10				μA
	T _J =125°C		250				
Typical Junction Capacitance (Note 2)		C _J	48				pF
Typical thermal resistance		R _{θJL}	12.5				°C/W
		R _{θJA}	44				
Operating junction temperature range		T _J	- 55 to +150				°C
Storage temperature range		T _{STG}	- 55 to +150				°C

Note 1: Pulse test with PW=300μs, 1% duty cycle

Note 2: Measured at 1.0MHz and applied reverse voltage of 4.0V DC

ORDERING INFORMATION					
PART NO.	PART NO. SUFFIX	PACKING CODE	PACKING CODE SUFFIX (*)	PACKAGE	PACKING
S8xC (Note 1)	H	R7	G	SMC	850 / 7" Plastic reel
		R6		SMC	3,000 / 13" Paper reel
		M6		SMC	3,000 / 13" Plastic reel

Note 1: "xx" defines voltage from 400V (S8GC) to 1000V (S8MC)

*: Optional available

EXAMPLE					
PREFERRED P/N	PART NO.	PART NO. SUFFIX	PACKING CODE	PACKING CODE SUFFIX	DESCRIPTION
S8MCHR7G	S8MC	H	R7	G	AEC-Q101 qualified Green compound

RATINGS AND CHARACTERISTICS CURVES

(T_A=25°C unless otherwise noted)

FIG.1 MAXIMUM FORWARD CURRENT DERATING CURVE




FIG. 2 MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT




FIG. 3 TYPICAL FORWARD CHARACTERISTICS






FIG. 4 TYPICAL REVERSE CHARACTERISTICS




PACKAGE OUTLINE DIMENSIONS

DO-214AB (SMC)



DIM.	Unit (mm)		Unit (inch)	
	Min	Max	Min	Max
A	2.90	3.20	0.114	0.126
B	6.60	7.11	0.260	0.280
C	5.59	6.22	0.220	0.245
D	2.00	2.62	0.079	0.103
E	1.00	1.60	0.039	0.063
F	7.75	8.13	0.305	0.320
G	0.10	0.20	0.004	0.008
H	0.15	0.31	0.006	0.012

SUGGESTED PAD LAYOUT



Symbol	Unit (mm)	Unit (inch)
A	3.3	0.130
B	2.5	0.098
C	6.8	0.268
D	4.4	0.173
E	9.4	0.370

MARKING DIAGRAM



P/N = Specific Device Code
G = Green Compound
YW = Date Code
F = Factory Code

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Taiwan Semiconductor:

[S8GC](#) [S8MC](#) [S8JC](#) [S8KC](#) [S8JCHR6](#) [S8KCHR6G](#) [S8KCHR6](#) [S8KCHR7G](#) [S8KCHR7](#) [S8MC R6](#) [S8JC R7G](#)
[S8GCHR6](#) [S8MCHR7](#) [S8JCHR7G](#) [S8MC R6G](#) [S8JCHR6G](#) [S8MCHR7G](#) [S8JC R6G](#) [S8MC R7G](#) [S8GC R6](#)
[S8JCHR7](#) [S8GC R6G](#) [S8JC R6](#) [S8GCHR7G](#) [S8KC R6G](#) [S8MCHR6](#) [S8GCHR6G](#) [S8GCHR7](#) [S8GC R7G](#) [S8KC](#)
[R7G](#) [S8KC R6](#) [S8MCHR6G](#)