


NPN 100mA 50V Digital Transistors (Bias Resistor Built-in Transistors)

Parameter	Value
V _{CC}	50V
I _{C(MAX.)}	100mA
R ₁	47kΩ
R ₂	10kΩ


● Features

- 1) Built-In Biasing Resistors
- 2) Built-in bias resistors enable the configuration of an inverter circuit without connecting external input resistors (see inner circuit).
- 3) The bias resistors consist of thin-film resistors with complete isolation to allow negative biasing of the input. They also have the advantage of completely eliminating parasitic effects.
- 4) Only the on/off conditions need to be set for operation, making the circuit design easy.
- 5) Complementary PNP Types: DTA144V series
- 6) Lead Free/RoHS Compliant.

Outline



•Inner circuit



Application

Switching circuit, Inverter circuit, Interface circuit, Driver circuit

Packaging specifications

Part No.	Package	Package size	Taping code	Reel size (mm)	Tape width (mm)	Basic ordering unit.(pcs)	Marking
DTC144VUA	UMT3	2021	T106	180	8	3000	166
DTC144VKA	SMT3	2928	T146	180	8	3000	E66

● Absolute maximum ratings (T_a = 25°C)

Parameter			Values	Unit	
Supply voltage		V _{cc}	50	V	
Input voltage			-10 to 40	V	
Output current			30	mA	
Collector current	Collector current		100	mA	
Davies dia in eties	DTC144VUA	D *2	200	1	
Power dissipation	DTC144VKA	P_D^{*2} 200 mW		mvv	
Junction temperature		T _j	150	°C	
Range of storage temperature		T _{stg}	-55 to +150	°C	

• Electrical characteristics $(T_a = 25^{\circ}C)$

Downwortow	Cymah al	Canditions	Values			Lloit	
Parameter	Symbol	Conditions	Min.	Тур.	Max.	Unit	
Input valtage	$V_{I(off)}$	V _{CC} = 5V, I _O = 100μA	-	-	1	- V	
Input voltage	V _{I(on)}	$V_{O} = 0.3V, I_{O} = 2mA$	6	-	-		
Output voltage	V _{O(on)}	I _O /I _I = 10mA / 0.5mA	-	0.1	0.3	V	
Input current	I _I	V _I = 5V	-	-	0.16	mA	
Output current	I _{O(off)}	V _{CC} = 50V, V _I = 0V	-	-	0.5	μA	
DC current gain	G _I	V _O = 5V, I _O = 5mA	33	-	-	-	
Input resistance	R ₁	-	32.9	47	61.1	kΩ	
Resistance ratio	R ₂ /R ₁	-	0.17	0.21	0.26	-	
Transition frequency	f _T *1	V _{CE} = 10V, I _E = -5mA, f = 100MHz	-	250	-	MHz	

2/6

^{*1} Characteristics of built-in transistor

^{*2} Each terminal mounted on a reference footprint

● Electrical characteristic curves (T_a =25°C)

Fig.1 Input voltage vs. output current (ON characteristics)




Fig.2 Output current vs. input voltage (OFF characteristics)




Fig.3 Output current vs. output voltage






Fig.4 DC current gain vs. output current




●Electrical characteristic curves (T_a =25°C)

Fig.5 Output voltage vs. output current



Dimensions

UMT3



Pattern of terminal position areas [Not a recommended pattern of soldering pads]

DIM	MILIM	ETERS	INC	HES
	MIN	MAX	MIN	MAX
Α	0.80	1.00	0.031	0.039
A1	0.00	0.10	0.000	0.004
A3	0.2	25	0.0	10
b	0.15	0.30	0.006	0.012
С	0.10	0.20	0.004	0.008
D	1.90	2.10	0.075	0.083
E	1.15	1.35	0.045	0.053
е	0.65		0.026	
HE	2.00	2.20	0.079	0.087
L1	0.20	0.50	0.008	0.020
Lp	0.25	0.55	0.010	0.022
Q	0.10	0.30	0.004	0.012
х	=	0.10	=	0.004


DIM	MILIM	ETERS	INCHES		
	MIN	MAX	MIN	MAX	
b2	_	0.50	_	0.020	
e1	1.55		0.0	061	
11	_	0.65	_	0.026	

Dimension in mm/inches



Dimensions

SMT3



Pattern of terminal position areas [Not a recommended pattern of soldering pads]

DIM	MILIM	ETERS	INCHES		
DIM	MIN	MAX	MIN	MAX	
Α	1.00	1.30	0.039	0.051	
A1	0.00	0.10	0.000	0.004	
A3	0.	25	0.0	10	
b	0.35	0.50	0.014	0.020	
С	0.09	0.25	0.004	0.010	
D	2.80	3.00	0.110	0.118	
E	1.50	1.80	0.059	0.071	
е	0.95		0.037		
HE	2.60	3.00	0.102	0.118	
L1	0.30	0.60	0.012	0.024	
Lp	0.40	0.70	0.016	0.028	
Q	0.20	0.30	0.008	0.012	
x	2	0.10		0.004	
У	ш)	0.10	_	0.004	
DIM	MILIMETERS		INC	HES	
	MIN	MAX	MIN	MAX	
b2	_	0.60	_	0.024	

Dimension in mm/inches

e1



0.035

0.083

0.90

2.10

Notes

No copying or reproduction of this document, in part or in whole, is permitted without the consent of ROHM Co.,Ltd.

The content specified herein is subject to change for improvement without notice.

The content specified herein is for the purpose of introducing ROHM's products (hereinafter "Products"). If you wish to use any such Product, please be sure to refer to the specifications, which can be obtained from ROHM upon request.

Examples of application circuits, circuit constants and any other information contained herein illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.

Great care was taken in ensuring the accuracy of the information specified in this document. However, should you incur any damage arising from any inaccuracy or misprint of such information, ROHM shall bear no responsibility for such damage.

The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM and other parties. ROHM shall bear no responsibility whatsoever for any dispute arising from the use of such technical information.

The Products specified in this document are intended to be used with general-use electronic equipment or devices (such as audio visual equipment, office-automation equipment, communication devices, electronic appliances and amusement devices).

The Products specified in this document are not designed to be radiation tolerant.

While ROHM always makes efforts to enhance the quality and reliability of its Products, a Product may fail or malfunction for a variety of reasons.

Please be sure to implement in your equipment using the Products safety measures to guard against the possibility of physical injury, fire or any other damage caused in the event of the failure of any Product, such as derating, redundancy, fire control and fail-safe designs. ROHM shall bear no responsibility whatsoever for your use of any Product outside of the prescribed scope or not in accordance with the instruction manual.

The Products are not designed or manufactured to be used with any equipment, device or system which requires an extremely high level of reliability the failure or malfunction of which may result in a direct threat to human life or create a risk of human injury (such as a medical instrument, transportation equipment, aerospace machinery, nuclear-reactor controller, fuel-controller or other safety device). ROHM shall bear no responsibility in any way for use of any of the Products for the above special purposes. If a Product is intended to be used for any such special purpose, please contact a ROHM sales representative before purchasing.

If you intend to export or ship overseas any Product or technology specified herein that may be controlled under the Foreign Exchange and the Foreign Trade Law, you will be required to obtain a license or permit under the Law.



Thank you for your accessing to ROHM product informations. More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

http://www.rohm.com/contact/

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ROHM Semiconductor:
DTC144VKAT146 DTC144VUAT106