

CMOS/ 1.8V, 2.5V, 3.3V Compatible/ 2.5×2.0mm



RoHS Compliant

### Features

- Miniature ceramic package  
2.5 (L) × 2.0 (W) × 0.7 (H) mm (Typ.)
- Highly reliable with seam welding
- CMOS output
- Supply voltage 1.8/ 2.5/ 3.3V  
Wide operating voltage range 1.6 to 3.63V
- Low current consumption
- High output frequency 125MHz

Table 1

Freq. Tol. Code	Tol. × 10 <sup>-6</sup>	Operating Temperature Range (°C)	Note
0	± 50	-10 to +70	Standard specifications
S	± 30		
U	± 25	-40 to +85	With only certain frequencies
F	± 100		
G	± 50		
6	± 50		

### How to Order

KC2520B 25.0000 C 1 0 E 00  
① ② ③ ④ ⑤ ⑥ ⑦

- ① Type (2.5×2.0mm SMD)
- ② Output Frequency
- ③ Output Type (CMOS)
- ④ Supply Voltage (1.8V, 2.5V, 3.3V Compatible)
- ⑤ Frequency Tolerance (See Table 1)
- ⑥ Symmetry/ INH Function (45/ 55%, Stand-by)
- ⑦ Customer Special Model Suffix (STD Specification is "00")

Packaging (Tape & Reel 2000 pcs./ reel)


### Specifications

Item	Symbol	Conditions	Specifications		Units	
			Min.	Max.		
Output Frequency Range	fo		1.5	125	MHz	
Frequency Tolerance	f <sub>tol</sub>	Initial tolerance, Operating temperature range, Rated power supply voltage change, Aging (1 year @25°C), Shock and vibration	Op.Temp.: -40 to +85°C Op. Temp.: -10 to +70°C/ -40 to +85°C/ -40 to +105°C Op.Temp.: -10 to +70°C	-100 -50 -30	+100 +50 +30	×10 <sup>-6</sup>
Storage Temperature Range	T <sub>stg</sub>		-55	+125		
Operating Temperature Range	T <sub>use</sub>	Standard Specifications Extend (Option)	-10 -40	+70 +105	°C	
Max. Supply Voltage	—	1.5≤fo≤80MHz 80<fo≤125MHz	-0.6 -0.3	+6.0 +4.0	V	
Supply Voltage	V <sub>cc</sub>		+1.6	+3.63	V	
Current Consumption (Maximum Loaded/ 1.6≤V <sub>cc</sub> ≤2.0V)	I <sub>cc</sub>	1.5≤fo≤24MHz	—	2.5	mA	
		24<fo≤40MHz	—	3.5		
		40<fo≤60MHz	—	5.0		
		60<fo≤80MHz	—	6.0		
		80<fo≤125MHz	—	11.0		
Current Consumption (Maximum Loaded/ 2.0<V <sub>cc</sub> ≤2.8V)	I <sub>cc</sub>	1.5≤fo≤24MHz	—	3.0	mA	
		24<fo≤40MHz	—	4.5		
		40<fo≤60MHz	—	5.5		
		60<fo≤80MHz	—	6.5		
		80<fo≤125MHz	—	14.0		
Current Consumption (Maximum Loaded/ 2.8<V <sub>cc</sub> ≤3.63V)	I <sub>cc</sub>	1.5≤fo≤24MHz	—	3.5	mA	
		24<fo≤40MHz	—	5.0		
		40<fo≤60MHz	—	6.0		
		60<fo≤80MHz	—	8.0		
		80<fo≤125MHz	—	17.0		
Stand-by Current	I <sub>std</sub>		—	10	μA	
Symmetry	SYM	@50%V <sub>cc</sub>	45	55	%	
Rise/ Fall Time (10% V <sub>cc</sub> to 90% V <sub>cc</sub> Maximum Loaded)	tr/ tf	1.6≤V <sub>cc</sub> ≤2.0V/ 1.5<fo≤80MHz	—	6.5	ns	
		2.0<V <sub>cc</sub> ≤2.8V/ 1.5<fo≤80MHz	—	5.0		
		2.8<V <sub>cc</sub> ≤3.63V/ 1.5<fo≤80MHz	—	4.5		
		1.6≤V <sub>cc</sub> ≤3.63V/ 80<fo≤125MHz	—	4.0		
Low Level Output Voltage	V <sub>OL</sub>	I <sub>OL</sub> =4mA	—	10%V <sub>cc</sub>	V	
High Level Output Voltage	V <sub>OH</sub>	I <sub>OH</sub> =-4mA	90%V <sub>cc</sub>	—	V	
Output Load	L <sub>CMOS</sub>	CMOS Output	—	15	pF	
Low Level Input Voltage	V <sub>IL</sub>		—	30%V <sub>cc</sub>	V	
High Level Input Voltage	V <sub>IH</sub>		70%V <sub>cc</sub>	—	V	
Disable Time	t <sub>dis</sub>		—	100	ns	
Enable Time	t <sub>ena</sub>		—	5	ms	
Start-up Time	t <sub>str</sub>	@Minimum operating voltage to be 0 sec.	—	10	ms	
1 Sigma Jitter	J <sub>Sigma</sub>	Measured with Wavecrest SIA-3000	1.5≤fo≤80MHz	—	8	ps
			80<fo≤125MHz	—	4	
Peak to Peak Jitter	J <sub>PK-PK</sub>	Measured with Wavecrest SIA-3000	1.5≤fo≤80MHz	—	80	ps
			80<fo≤125MHz	—	40	

Note: All electrical characteristics are defined at the maximum load and operating temperature range.  
Please contact us for inquiry about operating temperature range, available frequencies and other conditions.


### Dimensions

(Unit: mm)



### Recommended Land Pattern

(Unit: mm)



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## AVX:

[KC2520B27.0000C20E00](#) [KC2520B48.0000C10E00](#) [KC2520B27.0000C10E00](#) [KC2520B25.0000C10E00](#)  
[KC2520B24.0000C10E00](#) [KC2520B14.3182C10E00](#) [KC2520B24.5760C10E00](#) [KC2520B25.0000C1GE00](#)  
[KC2520B33.3333C1GE00](#) [KC2520B4.09600C1GE00](#) [KC2520B48.0000C1GE00](#) [KC2520B7.37280C1GE00](#)  
[KC2520B25.0000C2GE00](#) [KC2520B27.0000C2GE00](#) [KC2520B33.3333C2GE00](#) [KC2520B48.0000C2GE00](#)  
[KC2520B12.0000C10E00](#) [KC2520B14.7456C1GE00](#) [KC2520B33.3333C1GESH](#) [KC2520B50.0000C1FE00](#)  
[KC2520B50.0000C1GE00](#) [KC2520B66.6667C1GE00](#) [KC2520B16.0000C20EME](#) [KC2520B16.0000C10E00](#)  
[KC2520B30.0000C10E00](#) [KC2520B40.0000C10E00](#) [KC2520B50.0000C10E00](#) [KC2520B7.37280C2GE00](#)  
[KC2520B4.09600C2GE00](#) [KC2520B80.0000C1GE00](#) [KC2520B10.0000C1GE00](#) [KC2520B3.68640C1GE00](#)  
[KC2520B20.0000C1GE00](#) [KC2520B60.0000C1GE00](#) [KC2520B14.3182C1GE00](#) [KC2520B16.0000C1GE00](#)  
[KC2520B30.0000C1GE00](#) [KC2520B8.00000C1GE00](#) [KC2520B49.1520C1GE00](#) [KC2520B40.0000C1GE00](#)  
[KC2520B4.00000C1GE00](#) [KC2520B24.0000C1GE00](#) [KC2520B12.0000C1GE00](#) [KC2520B19.2000C1GE00](#)  
[KC2520B6.00000C1GE00](#) [KC2520B1.84320C1GE00](#) [KC2520B16.3840C1GE00](#) [KC2520B27.0000C1GE00](#)  
[KC2520B83.2500C1HETC](#)