

Glass Encapsulated Automotive TransGuard®



GENERAL DESCRIPTION

The Glass Encapsulated Automotive TransGuard multilayer varistors are zinc oxide (ZnO) based ceramic semiconductor devices with non-linear, bi-directional V-I characteristics.

They have the advantage of offering bi-directional overvoltage protection as well as EMI/RFI attenuation in a single SMT package. The Automotive Series high current and high energy handling capability make them well suited for protection against automotive related transients.

The additional glass encapsulation is designed for specific customer requirements for enhanced acid-resistance against harsh environment or process such as acidic environment, salts or chlorite flux process.

GENERAL CHARACTERISTICS

Operating Temperature: -55°C to 125°C

FEATURES

- High Reliability
- High Energy Absorption (Load Dump)
- High Current Handling
- Bi-Directional protection
- EMI/RFI attenuation in off-state
- Multi-strike capability
- Sub 1nS response to ESD strike
- Glass Encapsulated
- AEC Q200 Qualified

APPLICATIONS

- Various Automotive Applications where Glass Encapsulation is needed for Harsh Environment / Acid-Resistance
- Various Automotive Applications
- Internal Combustion Engine (ICE) Vehicles
- Hybrid Electric Vehicles (HEV)
- Plug-in Hybrid Electric Vehicles (PHEV)
- Commercial Vehicles
- Sensors
- LIN BUS
- ECU
- DC Motor
- Relays
- and more

HOW TO ORDER

| | | | | | | | | |
|----------|-------------------------|-------------------|----------------------|--|---|--------------------------------------|--|------------------|
| V | G | AS | 1812 | 16 | P | 400 | R | P |
| Varistor | Glass Encapsulated Chip | Automotive Series | Case Size | Working Voltage | Energy Rating | Clamping Voltage | Package | Termination |
| | | | 1210 1812 2220 | 16 = 16Vdc 34 = 34Vdc 65 = 65Vdc | S = 2.0J P = 2.7-3.0J U = 4.0-5.0J Y = 7.2-12J | 400 = 42V 770 = 77V 131 = 135V | D = 7" reel R = 7" reel T = 13" reel | P = Ni/Sn plated |

PHYSICAL DIMENSIONS: mm (inches)

| Size (EIA) | Length (L) | Width (W) | Max Thickness (T) | Land Length (t) |
|------------|----------------------------|----------------------------|-------------------|---------------------------|
| 1210 | 3.20±0.20 (0.126±0.008) | 2.49±0.20 (0.098±0.008) | 1.70 (0.067) | 0.14 max. (0.045 max.) |
| 1812 | 4.50±0.30 (0.177±0.012) | 3.20±0.30 (0.126±0.012) | 2.00 (0.079) | 1.00 max. (0.040 max.) |
| 2220 | 5.70±0.40 (0.224±0.016) | 5.00±0.40 (0.197±0.016) | 2.50 (0.098) | 1.00 max. (0.040 max.) |



ELECTRICAL CHARACTERISTICS


| PN | V _{W DC} | V _{W AC} | V _B | V _C | I _{VC} | I _L | E _T | E _{LD} | I _P | Cap | Freq | V _{jump} | P diss |
|----------------|-------------------|-------------------|----------------|----------------|-----------------|----------------|----------------|-----------------|----------------|-------|------|-------------------|--------|
| VGAS181216P400 | 16 | 11 | 24.5±10% | 42 | 5 | 10 | 2.9 | 10 | 1000 | 5000 | K | 27.5 | 0.07 |
| VGAS222016Y400 | 16 | 11 | 24.5±10% | 42 | 10 | 10 | 7.2 | 25 | 1500 | 13000 | K | 25.5 | 0.1 |
| VGAS121034S770 | 34 | 30 | 47.0±10% | 77 | 2,5 | 15 | 2 | 3 | 400 | 1000 | K | 48 | 0.04 |
| VGAS181234U770 | 34 | 30 | 47.0±10% | 77 | 5 | 15 | 5 | 6.1 | 800 | 1500 | K | 48 | 0.08 |
| VGAS222034Y770 | 34 | 30 | 47.0±10% | 77 | 10 | 15 | 12 | 25 | 2000 | 6300 | K | 48 | 0.24 |
| VGAS121065P131 | 65 | 50 | 82.0±10% | 135 | 2,5 | 15 | 2.7 | - | 350 | 600 | K | 48 | 0.05 |

| | | | |
|---------------------|---|-----------------------|---|
| V _W (DC) | DC Working Voltage [V] | E _T | Transient Energy Rating [J, 10x1000µs] |
| V _W (AC) | AC Working Voltage [V] | E _{LD} | Load Dump Energy (x10) [J] |
| V _B | Typical Breakdown Voltage [V @ 1mA _{DC} , 25°C] | I _P | Peak Current Rating [A, 8x20µs] |
| V _C | Clamping Voltage [V @ I _{VC}] | Cap | Typical capacitance [pF] @ frequency specified and 0.5V _{RMS} , 25°C, M = 1MHz, K = 1kHz |
| I _{VC} | Test Current for V _C [A, 8x20µs] | V _{jump} | Jump Start [V, 5min] |
| I _L | Maximum leakage current at the working voltage, 25°C [µA] | P _{DISS MAX} | Max Power Dissipation [W] |

AUTOMOTIVE SERIES – LOAD DUMP TEST

According to ISO DP7637 rev 2 Pulse 5

Automotive Load Dump Pulse (According to ISO 7637 Pulse 5)



When using the test method indicated below, the amount of Energy dissipated by the varistor must not exceed the Load Dump Energy value specified in the product table.

12V SYSTEMS

| | | | |
|-----------------------|-------------|-----------|-----------|
| VGAS181216P400 | 0.5Ω | 1Ω | 4Ω |
| 100ms | 46 | 52 | 72 |
| 200ms | 37 | 41 | 59 |
| 400ms | 32 | 35 | 51 |
| VGAS222016Y400 | 0.5Ω | 1Ω | 4Ω |
| 100ms | 53 | 60 | 77 |
| 200ms | 50 | 55 | 73 |
| 400ms | 47 | 50 | 66 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AVX:](#)

[VGAS121065P131DP](#) [VGAS222034Y770DP](#) [VGAS121034S770DP](#) [VGAS181216P400DP](#) [VGAS222016Y400DP](#)
[VGAS181234U770DP](#)