

C3225X8R1E155K160AA

TDK Item Description : C3225X8R1E155KT****



Application & Main Feature

Commercial Grade (High Temperature Application)

Series

C3225 [EIA CC1210]

Dimensions

L 3.20mm +/-0.4mm
W 2.50mm +/-0.3mm
T 1.60mm +/-0.2mm
B 0.20mm Min.
G

Temperature Characteristic

X8R (-55 to 150 degC +/-15%)

Rated Voltage

1E (25Vdc)

Capacitance

1.5uF

Capacitance Tolerance

K (+/-10%)

Dissipation Factor


3% Max.

Insulation Resistance


333Mohm Min.

AEC-Q200


Not Applicable




DC Bias Characteristic




|Z|, ESR vs. Freq. Characteristics




Temperature Characteristic



Cap. vs. Freq. Characteristic



Ripple Temperature Rise Characteristic



All specifications are subject to change without notice.

September 28, 2013

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TDK:

[C3225X8R1E155K160AA](#)