

Server Remote Control, External KVM over IP

MODEL NUMBER: **B051-000**



Description

Tripp Lite's B051-000 is an IP implemented KVM solution that allows network administrators to access a server or KVM switch from any station connected to the network, whether from the LAN, WAN, or the Internet. Network administrators can enjoy freedom from being bound to the server room; work from anywhere in the office, remote locations, or even from home! Since the B051-000 uses TCP/IP as its communication protocol, network administrators can remotely access attached KVM switches, allowing remote control of the attached servers to perform many tasks with ease and speed, such as installing and running GUI applications, BIOS level troubleshooting, routine monitoring, system maintenance, system administration, and rebooting. It supports 10Base-T, 100Base-T, TCP/IP, and HTTP through the Java Client. The server can be accessed whether it is down the hall, on the other side of town, or thousands of miles away! Utilizing advanced security technologies, the B051-000 provides password protection, advanced encryption technologies, sophisticated user filters and user management, stealth mode and automatic lockout to make sure that remote access is secure. The B051-000 offers high resolution (up to 1600 x 1200 @ 60Hz), user-friendly Windows GUI Client Software and Java client software. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

- Provides IP Access to KVM switches or servers that do not have built-in IP functionality.
- Virtual Media lets the connected computer access media such as flash drives, DVD/CD drives, and Smart Card / CAC readers
- Supports both IPv4 and IPv6
- Features an RS-232 serial port for connection of a serial device, such as a switch or router
- Remote authentication support: RADIUS, LDAP, LDAPS and MS Active Directory
- Track critical events on the installation, such as user logins and system reboot, via SMTP email notification, SNMP traps, the included Windows-based Log Server, or Syslog server.

Highlights

- Remotely access a server or KVM switch via LAN, WAN, or the Internet
- Supports both IPv4 and IPv6
- Features an RS-232 serial port for connection of a serial device, such as a switch or router
- Virtual Media lets the connected computer access media such as flash drives, DVD/CD drives, and Smart Card / CAC readers
- Remote authentication support: RADIUS, LDAP, LDAPS and MS Active Directory
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

Remote Console Computer Requirements

- Browsers must support 128-bit SSL encryption
- For the browser-based Java Applet and non-browser AP Java Client, the latest version of Sun's Java Runtime Environment (JRE) must be installed, and 250 MB of memory available after installation
- For the Log Server, you must have the Microsoft Jet OLEDB 4.0 or higher driver installed
- For best results we recommend that the computers used to access the B051-000 have at



- Multi-level authentication - Up to 64 accounts can be created, with any combination of Administrators, Users, and Select accounts.
- Advanced encryption technology - 1024 bit RSA, 56 bit DES, 256 bit AED and 128 bit SSL
- Message board feature allows users to communicate with each other, and allows a user to take exclusive control of the KVM switch.
- Export/import user account and configuration settings directly to the B051-000 IP Remote Access Unit.
- Access the connected server or KVM switch via your web browser using the browser-based Windows or Java applications
- Access the connected server or KVM switch without a browser using the non-browser Windows or Java applications
- Supports TCP/IP, HTTP, HTTPS, UDP, DHCP, SSL, ARP, DNS, ICMP, CHAP, PPP, 10Base-T and 100Base-T.
- Superior video resolution: up to 1600 x 1200 @ 60Hz; 24-bit color depth for remote sessions.
- PPP mode (modem) dial-up support for out-of-band, and low bandwidth operation.
- Supports importing third party CA certificates]
- Multi-Language Support - Administrator Utility can be displayed in English, German, Russian, Japanese, Korean, Traditional Chinese and Simplified Chinese
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

- least a Pentium III, 1 GHz processor, with their screen resolution set to 1024 x 768
- For best results, a network transfer speed of at least 512 kbps is recommended
- For the browser-based Windows Client, at least 60 MB of memory must be available after installation
- For the non-browser Windows Client, at least 25 MB of memory must be available after installation

Connected Computer/Server or KVM Requirements

- VGA, SVGA or Multisync port
- An available type A USB port or (x2) PS/2 keyboard/mouse ports

Package Includes

- B051-000 IP Remote Access Unit
- USB KVM Cable Kit
- PS/2 KVM Cable Kit
- USB - PS/2 Console Connector Kit
- USB 2.0 Virtual Media Cable
- External Power Adapter with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A / Output: 5V, 2.6A, Max 13W)
- 0U Rackmount Kit
- Software CD with Owners' Manual
- Quick Start Guide



Specifications

| OVERVIEW | |
|---------------------------------------|---|
| AC Adapter | Input: 100-240V~0.5A, 50-60Hz / Output: 5V, 2.6A, Max 13W |
| Accessories Type | Remote Management |
| PHYSICAL | |
| Unit Weight (lbs.) | 1.08 |
| Unit Weight (kg) | 0.49 |
| Material of Construction | Metal |
| Included Mounting Accessories | 0U Bracket |
| ENVIRONMENTAL | |
| Storage Temperature Range | -20 to +60 C |
| Relative Humidity | 0 - 80% RH Non-Condensing |
| Operating Temperature | 0 to 50 C |
| BTUs | 25.605 |
| CONNECTIONS | |
| Computer/Server Ports - Port 1 | Modified HD15F (18 pin) |
| Included Cable (Side A) - Connector 1 | Modified HD15F (18 pin) |
| Included Cable (Side B) - Connector 2 | PS/2 Female |
| Included Cable (Side B) - Connector 3 | PS/2 Female |
| Included Cable (Side B) - Connector 4 | USB-A Female |
| Included Cable (Side B) - Connector 5 | USB-A Female |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 1-year limited warranty |

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[B051-000](#)