


Model 4499RJ Sterile, Single-Use, Skin Probe

Connector



Sensor & Tempheart

- FDA Registered
- CE Marked for global sales
- Sterile single-use probe
- Skin surface measurement
- 400 series nominal resistance response curve
- 2252.4 ohm Resistance @ 25°C (including adaptor cable lead wire resistance)
- Interchangeable $\pm 0.1^\circ\text{C}$, 25°C to 45°C per EN 12470,
- RJ-11 style connector
- Reflective adhesive "Tempheart" pad included
- RoHS Compliant



DESCRIPTION

400-series sterile single-use temperature probe for skin surface measurement

FEATURES

- FDA / CE MDD
- Standard 400 series resistance response
- Skin probe sensor with adhesive "Tempheart"
- Individual Sterile pouch with 3-year shelf life
- RJ-11 style connector
- 20 probes per box


APPLICATIONS

- Continuous patient monitoring
- Skin temperature measurement

PERFORMANCE SPECS

Parameter	Units	Value
Resistance @ 25°C (including lead resistance)	Ohms	2252.4
Tolerance 25°C to 45°C	°C	± 0.1
Beta Value 25/85	K	3976
Tolerance on Beta Value	%	0.4
Typical response time in stirred fluid	Seconds	< 9
Insulation Resistance (Min. of 100Mohms for 1 Sec.)	Volts	500
Liquid immersion with 15VDC applied	Ohms	> 15Meg

MECHANICAL DETAILS



Model 4499 Sterile, Single-Use, Skin Probe

RESISTANCE VS TEMPERATURE VALUES

Temp °C	K Ohms
25	2.2524
26	2.1564
27	2.0644
28	1.9774
29	1.8944

Temp °C	K Ohms
30	1.8154
31	1.7394
32	1.6674
33	1.5994
34	1.5334

Temp °C	K Ohms
35	1.4714
36	1.4124
37	1.3554
38	1.3014
39	1.2494

Temp °C	K Ohms
40	1.2004
41	1.1524
42	1.1074
43	1.0644
44	1.0234
45	0.9842

ORDERING INFORMATION

Part Number	Description	Ω @25°C	MOQ
861551TP	4499RJ Skin Probe (Box of 20)	2252.4 *	10 Boxes

* When using 4940 adaptor cable

NORTH AMERICA

Measurement Specialties, Inc.
2670 Indian Ripple Road
Dayton, OH 45440
Tel: 1-937-427-1231
Fax: 1-937-427-1640

Sales email:
temperature.info.dayton@meas-spec.com

EUROPE

Measurement Specialties, Inc
Ballybrit Business Park
Galway, Ireland
Tel: +353-91-753238
Fax: +353-91-770789

Sales email:
temperature.sales.emea@meas-spec.com

ASIA

Measurement Specialties (China) Ltd.
No. 26 Langshan Road
Shenzhen High-Tech Park (North)
Nanshan District, Shenzhen 518057
China
Tel: +86 (0) 755 33305088
Fax: +86 (0) 755 33305099

Sales email:
temperature.sales.asia@meas-spec.com

The information in this sheet has been carefully reviewed and is believed to be accurate; however, no responsibility is assumed for inaccuracies. Furthermore, this information does not convey to the purchaser of such devices any license under the patent rights to the manufacturer. Measurement Specialties, Inc. reserves the right to make changes without further notice to any product herein. Measurement Specialties, Inc. makes no warranty, representation or guarantee regarding the suitability of its product for any particular purpose, nor does Measurement Specialties, Inc. assume any liability arising out of the application or use of any product or circuit and specifically disclaims any and all liability, including without limitation consequential or incidental damages. Typical parameters can and do vary in different applications. All operating parameters must be validated for each customer application by customer's technical experts. Measurement Specialties, Inc. does not convey any license under its patent rights nor the rights of others.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[861551TP](#)