

FOR MORE INFORMATION, CONTACT:  
STEVEN MCINTIRE, PRODUCT MANAGER  
PH: 1-717-986-7622  
EMAIL: [SJMCINTI@TE.COM](mailto:SJMCINTI@TE.COM)



Introducing  
**CeeLok Fas-T Connector**  
*10 GBASE-T connector*

[te.com/ADM](http://te.com/ADM)

©2011 Tyco Electronics Corporation, a TE Connectivity Ltd.  
Company. All Rights Reserved.

10/2011

TE Connectivity and TE connectivity (logo) and TE (logo) are  
trademarks of the TE Connectivity Ltd. family of companies.  
Other logos, product and/or company names might be trade-  
marks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information herein, nothing herein constitutes  
any guarantees that such information is error-free or any other representation, warranty or guarantee that the informa-  
tion is accurate, correct, reliable or current. The TE entity issuing this publication reserves the right to make any adjust-  
ments to the information contained herein at any time without notice. All implied warranties of merchantability or fitness  
for a particular purpose are expressly disclaimed. The dimensions herein are for reference purposes only and are sub-  
ject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions  
and design specifications.



CeeLok Fas-T Connector


KEY FEATURES

Accommodates size 8 shell for weight and space savings

10 Gbit-Ethernet - Cat 6A or Cat 7 wire

1 Gbit-Ethernet - Cat 5e

Crimp-snap, 39029-style contacts for easy termination and field repairability



T-shaped pin pattern improves SI through uniform crosstalk cancellation

Backshell integrated in plug body provides low profile, low cost, low weight strain relief & EMI protection

Compatible with multiple braid terminations, adaptor styles and seal boots

Insert assembly mechanically retained for ≥25 lb. retention force

Scoop-proof design



Optional nickel plate shown in this photo

CeeLok Fas-T Connector

DESCRIPTION

Small, rugged connector designed for 10 GBASE-T or other 100 Ohm applications  
Field repairable crimp-snap contacts  
38999 Style, size 8 shell

APPLICATIONS

10 GBASE-T Ethernet data transmission in harsh aerospace and defense environments  
Cat 6A or Cat 7 compatible for 10 Gbit-Ethernet  
Cat 5e compatible for 1 Gbit-Ethernet  
Military applications include:  
Soldier worn devices, Missiles, Rotary Wing, C4I, Ground Vehicles, Fixed Wing Aircraft and Shipboard  
Commercial Aerospace applications include:  
IFE, Avionics

ELECTRICAL

10 Gbit-Ethernet      Cat 6a or Cat 7 wire  
1 Gbit-Ethernet      Cat 5e  
Electrical performance specifications:  
- Insulation resistance: 500 mega-ohms ambient, 1000 Mega-ohms at 175°C  
- Dielectric withstanding voltage: 500 VAC sea level, 100 VAC @ 50,000 ft.  
- Shielding effectiveness per MIL-DTL-38999  
- Shell to shell conductivity - 2mV max.

MECHANICAL

Performance Specifications:  
- Vibration, Sine: MIL-STD-202, Condition G (30G)  
- Vibration, Random: EIA-364-28 Condition V Letter J (37.8G)  
- Durability: 500 mating cycles  
- Contact Retention: 10 lb. min.  
- Coupling Torque: 8 in-lb. max.

MATERIALS

Shell: Aluminum alloy for lightweight, rugged performance  
Insert: High temperature thermoplastic for excellent temperature endurance. Low dielectric constant for superior signal integrity.  
Contacts: Copper alloy

STANDARDS & SPECS

Product Spec: 108-2482

APPLICATION TOOLING

Crimp tool PN: M22520/2-01

PHYSICAL OR OTHER PROPERTIES


Operating Temperature: -65°C to +175°C  
Altitude Immersion: 50,000 ft. (mated condition)  
Unmated Condition: IP 67  
Shells available in Electroless Nickel or Black Zinc Nickel for DOD-Approved, RoHS compliant, corrosion resistance (500 hr Salt Mist)

ORDERING INFORMATION


Nickel Plate:		Black Zinc Nickel:	
Plug	2102353-1	Plug	2102353-2
Receptacle	2102352-1	Receptacle	2102352-2
PC Tail Receptacle	2102351-1	PC Tail Receptacle	2102351-2

PRODUCT DIMENSIONS


Plug Kit Assembly



Receptacle Kit Assembly



PC Tail Assembly



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2102351-1](#) [2102351-2](#) [2102352-1](#) [2102352-2](#) [2102353-1](#) [2102353-2](#)