


## High Voltage Ceramic Disc Capacitors 10 kVDC & 15 kVDC

Fig. 1



LEAD OFFSET 'LO'	
10 kVDC series NOMINAL	0.20 (5.0 mm)
15 kVDC series NOMINAL	0.30 (7.6 mm)

### INSULATION RESISTANCE:

min. 1000  $\Omega$ F or 200 000 M $\Omega$

### TOLERANCE ON CAPACITANCE:

$\pm 20\%$ ; + 80 - 20 %

### DISSIPATION FACTOR:

0.2 % max. at 1 kHz; 1V (Class 1)  
2.0 % max. at 1 kHz; 1V (Class 2)

### CATEGORY TEMPERATURE RANGE:

(- 25 to + 85) °C

### CLIMATIC CATEGORY ACC. TO EN60068-1:

25/085/21

### OPERATING TEMPERATURE RANGE:

(- 25 to + 105) °C

### FEATURES

- Low losses
- High capacitance in small size
- High stability



**RoHS**  
COMPLIANT

### APPLICATIONS

- TV & Monitors
- SMPS
- DC and Pulse High voltage
- X-Ray Equipment

### DESIGN

The capacitors consist of a ceramic disc of which both sides are silver-plated. Connection leads are made of tinned copper having diameters of 0.032" (0.81 mm).

The capacitors may be supplied with straight leads having lead spacing of 0.375 (9.5 mm), 0.500" (12.7 mm) or 0.750" (10.1 mm)

The standard tolerances are  $\pm 20\%$  or + 80 - 20 %.

Coating is made of flame retardant epoxy resin in accordance with "UL94V-0".

### CAPACITANCE RANGE:

100 pF to 3300 pF

### DIELECTRIC STRENGTH BETWEEN LEADS:

10 kVDC	15 000 VDC, 2 s
15 kVDC	24 000 VDC, 2 s
	(in dielectric fluid)

### CERAMIC DIELECTRIC:

T3M (Class 1)  
X5F, Y5R, Y5U, Z5U (Class 2)



ORDERING INFORMATION, CERAMIC 10 kVDC								
C (pF)	TOL. (%)	D DIAMETER INCH (mm)	T THICKNESS INCH (mm)	LS LEAD SPACE	WIRE SIZE		ORDERING CODE	
					AWG	INCH (mm)		
<b>T3M (N4700)</b>								
250	± 20 %	0.490 (12.4)	0.290 (7.4)	0.375 (9.5)	20	0.032 (0.81)	615R100GATT25	
500		0.680 (17.3)	0.320 (8.1)	0.500 (12.7)			615R100GATT50	
680		0.750 (19.1)	0.300 (7.6)				615R100GATT68	
820		0.810 (20.6)	615R100GATT82					
1000		0.980 (24.9)	0.320 (8.1)	615R100GATD10				
<b>X5F</b>								
100	± 20 %	0.680 (17.3)	0.370 (9.4)	0.500 (12.7)	20	0.032 (0.81)	615R100GAT10	
250			0.300 (7.6)				615R100GAT25	
500			0.345 (8.8)				615R100GAT50	
<b>Y5R</b>								
100	± 20 %	0.490 (12.4)	0.330 (7.4)	0.375 (9.5)	20	0.032 (0.81)	615R100GAST10	
250			0.340 (8.6)				615R100GAST25	
500			0.310 (7.9)				615R100GAST50	
1000			0.750 (19.1)	0.320 (8.1)			0.500 (12.7)	615R100GAD10
2500			0.980 (24.9)	0.330 (7.4)				615R100GATD25
<b>Y5U</b>								
1000	+ 80/- 20 %	0.680 (17.3)	0.330 (7.4)	0.500 (12.7)	20	0.032 (0.81)	615R100GASD10	
<b>Z5U</b>								
2500	+ 80/- 20 %	0.750 (19.1)	0.350 (8.9)	0.500 (12.7)	20	0.032 (0.81)	615R100GAD25	
3300		0.980 (24.9)	0.390 (9.9)				615R100GAD33	

ORDERING INFORMATION, CERAMIC 15 kVDC								
C (pF)	TOL. (%)	D DIAMETER INCH (mm)	T THICKNESS INCH (mm)	LS LEAD SPACE	WIRE SIZE		ORDERING CODE	
					AWG	INCH (mm)		
<b>T3M (N4700)</b>								
100	± 20 %	0.490 (12.4)	0.470 (11.9)	0.500 (12.7)	20	0.032 (0.81)	615R150GATT10	
250		0.670 (17.0)	0.430 (10.9)	0.750 (19.1)			615R150GATT25	
390		0.750 (19.1)	0.425 (10.8)				615R150GATT39	
500		0.810 (20.6)	0.410 (10.4)				615R150GATT50	
750		0.980 (24.9)	0.350 (8.9)	615R150GATT75				
<b>X5F</b>								
100	± 20 %	0.670 (17.0)	0.430 (10.9)	0.750 (19.1)	20	0.032 (0.81)	615R150GAT10	
250			0.455 (11.6)				615R150GAT25	
<b>Y5R</b>								
100	± 20 %	0.490 (12.4)	0.490 (12.4)	0.500 (12.7)	20	0.032 (0.81)	615R150GAST10	
250			0.480 (12.2)				615R150GAST25	
500			0.670 (17.0)	0.430 (10.9)			0.750 (19.1)	615R150GAT50
1000			0.980 (24.9)	0.460 (11.7)				615R150GATD10
<b>Y5U</b>								
500	+ 80/- 20 %	0.490 (12.4)	0.375 (9.5)	0.500 (12.7)	20	0.032 (0.81)	615R150GAST50	
1000		0.670 (17.0)	0.420 (10.7)	0.750 (19.1)			615R150GAD10	
<b>Z5U</b>								
2200	+ 80/- 20 %	0.980 (24.9)	0.510 (13.0)	0.750 (19.1)	20	0.032 (0.81)	615R150GAD22	
2500			0.450 (11.4)				615R150GAD25	



## Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

[615R100GAD47](#) [615R100GAD33](#) [615R150GAD10](#) [615R100GAD25](#) [615R100GAD10](#) [615R150GAST50](#)  
[615R150GAD25](#) [615R150GAT10](#) [615RX7RAM103EN202M](#) [615R100GAT50](#) [615R150GATT75](#) [615R100GATD10](#)  
[615R100GATT82](#) [615R150GATD10](#)