












PANEL CUT OUT




SWITCH FUNCTION A1
CIRCUIT DIAGRAM




OBSOLETE 1571102-5
SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER 25FEB2002	TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK D.ROHDE 16NOV05			
		APVD D.ROHDE 16NOV05	NAME POWER ROCKER SWITCH, 21.2mm X 36.6mm MIN PANEL SIZE DPST, NON-ILLUMINATED		
		PRODUCT SPEC	SIZE A2		
MATERIAL 1		APPLICATION SPEC	CAGE CODE 00779		
		WEIGHT -	DRAWING NO C-1571102		
		FINISH 2	RESTRICTED TO -		
CUSTOMER DRAWING			SCALE 2:1	SHEET 2 of 4	REV D1



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—





PANEL CUT OUT



2.00–3.00 [.079–.118]	21.2+0.1 [.835+.004]	37.0+0.2 [1.457+.008]
1.25–2.00 [.049–.079]	21.2+0.1 [.835+.004]	36.8+0.2 [1.449+.008]
.075–1.25 [.030–.049]	21.2+0.1 [.835+.004]	36.6+0.2 [1.441+.008]
PANEL THICKNESS	Y	X



SWITCH FUNCTION A1
CIRCUIT DIAGRAM



OBSOLETE —1571102—9—
SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER 25FEB2002		 TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK D.ROHDE 16NOV05					
		APVD D.ROHDE 16NOV05		NAME POWER ROCKER SWITCH, 21.2mm X 36.6mm MIN PANEL SIZE DPST, NON-ILLUMINATED			
		PRODUCT SPEC —					
		APPLICATION SPEC —					
MATERIAL 		FINISH 		SIZE A2	CAGE CODE 00779	DRAWING NO C-1571102	RESTRICTED TO —
CUSTOMER DRAWING				SCALE 2:1	SHEET 3 of 4	REV D1	

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

By

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

1

MATERIALS:
ROCKER BUTTON, FRAME & HOUSING: NYLON 66, UL 94 V-2.
PLUNGER: PHENOLIC
SEAL: SILICONE RUBBER
SCREW TERMINAL, ACTIVE CONTACTOR, CONTACTOR SUPPORT: COPPER ALLOY PER ASTM B152
QC & SOLDER TERMINAL: COPPER ALLOY PER ASTM B036
SPRING: STEEL WIRE
CONTACTS: SILVER-TIN OXIDE

2

FINISH:
CONTACTOR SUPPORT, ACTIVE CONTACTOR: 1.01µm [.000040] MIN SILVER
QC TERMINAL: 1.27µm [.000050] MIN NICKEL
SOLDER TERMINAL: 1.27µm [.000050] MIN TIN

3

ELECTRICAL SPECIFICATIONS:
CURRENT AND VOLTAGE: 6
CONTACT RESISTANCE (INITIAL): <50mΩ
DIELECTRIC STRENGTH (INITIAL): >1000 VAC, 1 MINUTE
INSULATION RESISTANCE (INITIAL): >100MΩ MIN (500VDC BETWEEN OPEN CONTACTS)
ELECTRICAL LIFE ENDURANCE: >6000 OPERATIONS, VOLTAGE DROP: <100mV
TEMPERATURE RISE AT TERMINALS: <30°C, 6000 OPERATIONS
(AMBIENT CONDITIONS: 25±2°C AND 65±5%R.H)

4

MECHANICAL SPECIFICATIONS:
ACTUATING FORCE: 1100g MIN, 1900g MAX
OPERATING LIFE ENDURANCE: >100,000 OPERATIONS
TERMINAL RETENTION FORCE: >9kg- SOLDER LUG
>9kg- QC TAB
>6.8kg- #6-32 UNC SCREW TERMINAL

5

ENVIRONMENTAL SPECIFICATIONS:
AMBIENT TEMPERATURE: -20°C TO +85°C
DEGREE OF PROTECTION: IP66

6

20A 125VAC, 10A 250VAC/16A 125VAC, 3/4HP/ 10A 277VAC, 3/4HP

7

COUNTRY OF ORIGIN AND TERMINAL IDENTIFICATION NUMBERS
MOLDED APPROXIMATELY AS SHOWN ON THE SWITCH HOUSING.

8

ELECTRICAL RATINGS, APPROVED AGENCY LOGOS AND THE TE CONNECTIVITY LOGO LASER MARKED APPROXIMATELY AS SHOWN ON THE SWITCH HOUSING.

9

COMPONENT RECOGNIZED TO US & CANADIAN STANDARDS, UL FILE NO. E46765.

10

ROHS 2002/95/EC COMPLIANT

ALCOSWITCH PART NUMBER

X1X2X3X4X5X6

X7X8X9

X10X11X12X13X14

SWITCH TYPE: X1X2 = PR - POWER ROCKER

SECONDARY ROCKER COLOR: X12 = Ø - NOT APPLICABLE

PANEL CUT OUT SIZE: X3 = C - 21.2x36.6 MIN
[.835x1.441]

NUMBER OF POLES: X4 = D - DOUBLE

SWITCH FUNCTION: X5X6 = A1-ON-OFF, WITH OPAQUE, SINGLE-COLOR
ROCKER BUTTON.

LEGEND TEXT PATTERN: X13 =
ØA B C

LEGEND TEXT COLOR: X14 = Ø - NOT APPLICABLE
G - GREEN
R - RED
B - BLACK
W - WHITE

CURRENT RATING: X7X8 = 20 - 6

TERMINAL TYPE: X9 = F - QC TAB
L - SOLDER LUG
S - #6-32 UNC SCREW

FRAME COLOR: X10 = B - BLACK
W - WHITE

ROCKER COLOR: X11 = B - BLACK
G - GREEN
R - RED
W - WHITE
Y - YELLOW

OBSOLETE	3	PRCDA1-20S-BB0CW	1-1571102-1
	3	PRCDA1-20S-BB0BW	1-1571102-0
	3	PRCDA1-20S-BB000	1571102-9
	2	PRCDA1-20L-BR000	1571102-8
	1	PRCDA1-20F-BR000	1571102-7
	2	PRCDA1-20L-BB0CW	1571102-6
	2	PRCDA1-20L-BB0BW	1571102-5
OBSOLETE	2	PRCDA1-20L-BB000	1571102-4
	1	PRCDA1-20F-BB0CW	1571102-3
	1	PRCDA1-20F-BB0BW	1571102-2
OBSOLETE	1	PRCDA1-20F-BB000	1571102-1
	SHEET REF	ALCOSWITCH PART NUMBER	TE PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN M.BINNER 25FEB2002

CHK D.ROHDE 16NOV05

APVD D.ROHDE 16NOV05

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

DIMENSIONS: mm [INCHES]

0

PLC

±

-

1

PLC

±

-

2

PLC

±

-

3

PLC

±

-

4

PLC

±

-

ANGLES

±

-

FINISH

2

TE Connectivity

POWER ROCKER SWITCH, 21.2mm X 36.6mm MIN
PANEL SIZE DPST, NON-ILLUMINATED

SIZE A2

CAGE CODE 00779

DRAWING NO. C-1571102

RESTRICTED TO -

SCALE 2:1

SHEET 4 OF 4

REV D1

1471-9 (1/15)

1571102

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[PRCDA1-20F-BB000](#)