



NOTES:

1 MATERIAL HOUSING: THERMOPLASTIC, UL94V-0, POST: BRASS

2 FINISH CONTACT AREA, 'D' MIN Au ON NICKEL 0.0013 MIN ALL OVER POST TINE: 0.001 MIN TIN-LEAD

	0.00078	—	—	2	2	5-	-0	E
	0.0002	—	—	2	2	4-	-9	
		48	24	50	50	4-	-8	
		46	23	48	48	4-	-7	
		44	22	46	46	4-	-6	
		42	21	44	44	4-	-5	
		40	20	42	42	4-	-4	
		38	19	40	40	4-	-3	
		36	18	38	38	4-	-2	
		34	17	36	36	4-	-1	
		32	16	34	34	4-	-0	
		30	15	32	32	3-	-9	
		28	14	30	30	3-	-8	
		26	13	28	28	3-	-7	
OBSELETE		24	12	26	26	3-	-6	B
		22	11	24	24	3-	-5	
		20	10	22	22	3-	-4	
OBSELETE		18	9	20	20	3-	-3	
		16	8	18	18	3-	-2	
		14	7	16	16	3-	-1	
		12	6	14	14	3-	-0	
		10	5	12	12	2-	-9	
		8	4	10	10	2-	-8	
		6	3	8	8	2-	-7	
		4	2	6	6	2-	-6	
	0.00078	2	1	4	4	2-	-5	
		48	24	50	50	2-	-4	
		46	23	48	48	2-	-3	
		44	22	46	46	2-	-2	
		42	21	44	44	2-	-1	
		40	20	42	42	2-	-0	
		38	19	40	40	1-	-9	
		36	18	38	38	1-	-8	
		34	17	36	36	1-	-7	
		32	16	34	34	1-	-6	
		30	15	32	32	1-	-5	
		28	14	30	30	1-	-4	
	OBSELETE		26	13	28	28	1-	-3
		24	12	26	26	1-	-2	A
		22	11	24	24	1-	-1	
		20	10	22	22	1-	-0	
		18	9	20	20		-9	
		16	8	18	18		-8	
OBSELETE		14	7	16	16		-7	
		12	6	14	14		-6	
OBSELETE		10	5	12	12		-5	
		8	4	10	10		-4	
OBSELETE		6	3	8	8		-3	
		4	2	6	6		-2	
	0.0002	2	1	4	4	178751-1		
STATUS	"D"	"C"	"B" SPACES	"A" REF	NO OF POS	ASS'Y P/N		

Copyright ©1991
AMP MANUFACTURING (SINGAPORE) PTE LTD.
ALL RIGHTS RESERVED

AMP

AMP MANUFACTURING
(SINGAPORE) PTE. LTD.

WIRE RANGE
— mm² (AWG) —

INSULATION DIA
— mmφ

NAME
AMPMODU 2MM PITCH POST HOR, V-TYPE, L=1.5

MATERIAL
SEE NOTE 1

FINISH
SEE NOTE 2

GENERAL TOLERANCE
0< 10 : ±0.2
10< 30 : ±0.25
30< 100 : ±0.3
ANGLES : ±°

SIZE LOC NUMBER
A2 DY 178751

C REVISED FP00-0055-99 LWY LSC 1JUN00

LTR REVISION RECORD DR CHK DATE

DR. 10APR91 I. ENOMOTO
CHK. 27MAY91 T. DOI

APP. SF LEONG

SCALE 8:1

REV. C

SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[178751-4](#)