





Dual P-Channel 1.8-V (G-S) MOSFET

PRODUCT SUMMARY		
V_{DS} (V)	$r_{DS(on)}$ (Ω)	I_D (A)
-8	0.600 @ $V_{GS} = -4.5$ V	± 0.60
	0.850 @ $V_{GS} = -2.5$ V	± 0.50
	1.200 @ $V_{GS} = -1.8$ V	± 0.42

TrenchFET[®]
Power MOSFETs
1.8-V Rated

Marking Code

Lot Traceability
and Date Code

Part # Code

ABSOLUTE MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)				
Parameter		Symbol	5 secs	Steady State
Drain-Source Voltage		V_{DS}	-8	
Gate-Source Voltage		V_{GS}	± 8	
Continuous Drain Current ($T_J = 150^\circ\text{C}$) ^a	$T_A = 25^\circ\text{C}$	I_D	± 0.60	± 0.57
	$T_A = 85^\circ\text{C}$		± 0.43	± 0.41
Pulsed Drain Current		I_{DM}	± 1.0	
Continuous Diode Current (Diode Conduction) ^a		I_S	-0.25	-0.23
Maximum Power Dissipation ^a	$T_A = 25^\circ\text{C}$	P_D	0.30	0.27
	$T_A = 85^\circ\text{C}$		0.16	0.14
Operating Junction and Storage Temperature Range		T_J, T_{stg}	-55 to 150	

THERMAL RESISTANCE RATINGS				
Parameter		Symbol	Typical	Maximum
Maximum Junction-to-Ambient ^a	$t \leq 5$ sec	R_{thJA}	360	415
	Steady State		400	460
Maximum Junction-to-Foot (Drain)	Steady State	R_{thJF}	300	350

Notes

a. Surface Mounted on 1" x 1" FR4 Board.



SPECIFICATIONS ($T_J = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)







Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Static						
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}, I_D = -250\ \mu\text{A}$	-0.45			V
Gate-Body Leakage	I_{GSS}	$V_{DS} = 0\ \text{V}, V_{GS} = \pm 8\ \text{V}$			± 100	nA
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS} = -6.4\ \text{V}, V_{GS} = 0\ \text{V}$			-1	μA
		$V_{DS} = -6.4\ \text{V}, V_{GS} = 0\ \text{V}, T_J = 85^\circ\text{C}$			-5	
On-State Drain Current ^a	$I_{D(on)}$	$V_{DS} = -5\ \text{V}, V_{GS} = -4.5\ \text{V}$	-1.0			A
Drain-Source On-State Resistance ^a	$r_{DS(on)}$	$V_{GS} = -4.5\ \text{V}, I_D = -0.57\ \text{A}$		0.51	0.600	Ω
		$V_{GS} = -2.5\ \text{V}, I_D = -0.48\ \text{A}$		0.720	0.850	
		$V_{GS} = -1.8\ \text{V}, I_D = -0.20\ \text{A}$		1.0	1.200	
Forward Transconductance ^a	g_{fs}	$V_{DS} = -10\ \text{V}, I_D = -0.57\ \text{A}$		1.2		S
Diode Forward Voltage ^a	V_{SD}	$I_S = -0.23\ \text{A}, V_{GS} = 0\ \text{V}$		-0.8	-1.2	V
Dynamic^b						
Total Gate Charge	Q_g	$V_{DS} = -4\ \text{V}, V_{GS} = -4.5\ \text{V}, I_D = -0.57\ \text{A}$		1.5	2.3	nC
Gate-Source Charge	Q_{gs}			0.17		
Gate-Drain Charge	Q_{gd}			0.16		
Turn-On Delay Time	$t_{d(on)}$	$V_{DD} = -4\ \text{V}, R_L = 8\ \Omega$ $I_D \approx -0.5\ \text{A}, V_{GEN} = -4.5\ \text{V}, R_G = 6\ \Omega$		6	12	ns
Rise Time	t_r			25	50	
Turn-Off Delay Time	$t_{d(off)}$			10	20	
Fall Time	t_f			10	20	
Source-Drain Reverse Recovery Time	t_{rr}	$I_F = -0.23\ \text{A}, di/dt = 100\ \text{A}/\mu\text{s}$		20	40	





Notes

a. Pulse test; pulse width $\leq 300\ \mu\text{s}$, duty cycle $\leq 2\%$.

b. Guaranteed by design, not subject to production testing.

TYPICAL CHARACTERISTICS (25°C UNLESS NOTED)

**TYPICAL CHARACTERISTICS (25°C UNLESS NOTED)****On-Resistance vs. Drain Current****Capacitance****Gate Charge****On-Resistance vs. Junction Temperature****Source-Drain Diode Forward Voltage****On-Resistance vs. Gate-to-Source Voltage**

TYPICAL CHARACTERISTICS (25 °C UNLESS NOTED)




Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[SI1905DL-T1](#) [SI1905DL-T1-E3](#)