


Automotive, Sulfur Resistant Lead (Pb)-Free Thick Film, Rectangular Chip Resistors


FEATURES

- Superior resistance against H₂S-atmosphere
- Stability $\Delta R/R = 1\%$ for 1000 h at 70 °C
- Metal glaze on high quality ceramic
- Pure tin solder contacts on Ni barrier layer, provides compatibility with lead (Pb)-free and lead containing soldering processes
- AEC-Q200 qualified, rev. C compliant
- Material categorization: For definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE

| STANDARD ELECTRICAL SPECIFICATIONS | | | | | | | | |
|---|----------------|------------------|---|---------------------------------|---|------------------|---------------------------|----------|
| MODEL | CASE SIZE INCH | CASE SIZE METRIC | POWER RATING $P_{70\text{ }^\circ\text{C}}$ W | LIMITING ELEMENT VOLTAGE MAX. V | TEMPERATURE COEFFICIENT ppm/K | TOLERANCE % | RESISTANCE RANGE Ω | SERIES |
| RCA0402 | 0402 | RR1005 | 0.063 | 50 | ± 50 | $\pm 0.5, \pm 1$ | 100 to 1.0M | E24; E96 |
| | | | | | ± 100 | ± 0.5 | 10 to 1.0M | E24; E96 |
| | | | | | ± 100 | ± 1 | 10 to 10M | E24; E96 |
| | | | | | ± 200 | ± 1 | 1.0 to 9.76 | E24; E96 |
| | | | | | ± 200 | ± 5 | 1.0 to 10M | E24 |
| Zero-Ohm-Resistor: $R_{\text{max.}} = 20 \text{ m}\Omega, I_{\text{max.}} \text{ at } 70\text{ }^\circ\text{C} = 1.5 \text{ A}$ | | | | | | | | |
| RCA0603 | 0603 | RR1608 | 0.10 | 75 | ± 50 | $\pm 0.5, \pm 1$ | 100 to 10M | E24; E96 |
| | | | | | ± 100 | ± 0.5 | 10 to 10M | E24; E96 |
| | | | | | ± 100 | ± 1 | 1.0 to 10M | E24; E96 |
| | | | | | ± 200 | ± 5 | 1.0 to 10M | E24 |
| | | | | | Zero-Ohm-Resistor: $R_{\text{max.}} = 20 \text{ m}\Omega, I_{\text{max.}} \text{ at } 70\text{ }^\circ\text{C} = 2.0 \text{ A}$ | | | |
| RCA0805 | 0805 | RR2012 | 0.125 | 150 | ± 50 | $\pm 0.5, \pm 1$ | 100 to 10M | E24; E96 |
| | | | | | ± 100 | ± 0.5 | 10 to 10M | E24; E96 |
| | | | | | ± 100 | ± 1 | 1.0 to 10M | E24; E96 |
| | | | | | ± 200 | ± 5 | 1.0 to 10M | E24 |
| | | | | | Zero-Ohm-Resistor: $R_{\text{max.}} = 20 \text{ m}\Omega, I_{\text{max.}} \text{ at } 70\text{ }^\circ\text{C} = 2.5 \text{ A}$ | | | |
| RCA1206 | 1206 | RR3216 | 0.25 | 200 | ± 50 | $\pm 0.5, \pm 1$ | 100 to 10M | E24; E96 |
| | | | | | ± 100 | ± 0.5 | 10 to 10M | E24; E96 |
| | | | | | ± 100 | ± 1 | 1.0 to 10M | E24; E96 |
| | | | | | ± 200 | ± 5 | 1.0 to 10M | E24 |
| | | | | | Zero-Ohm-Resistor: $R_{\text{max.}} = 20 \text{ m}\Omega, I_{\text{max.}} \text{ at } 70\text{ }^\circ\text{C} = 3.5 \text{ A}$ | | | |
| RCA1210 | 1210 | RR3225 | 0.5 | 200 | ± 50 | $\pm 0.5, \pm 1$ | 100 to 1.0M | E24; E96 |
| | | | | | ± 100 | ± 0.5 | 10 to 1.0M | E24; E96 |
| | | | | | ± 100 | ± 1 | 1.0 to 10M | E24; E96 |
| | | | | | ± 200 | ± 5 | 1.0 to 10M | E24 |
| | | | | | Zero-Ohm-Resistor: $R_{\text{max.}} = 20 \text{ m}\Omega, I_{\text{max.}} \text{ at } 70\text{ }^\circ\text{C} = 5.0 \text{ A}$ | | | |
| RCA1218 | 1218 | RR3246 | 1.0 | 200 | ± 50 | $\pm 0.5, \pm 1$ | 100 to 2.2M | E24; E96 |
| | | | | | ± 100 | ± 0.5 | 100 to 2.2M | E24; E96 |
| | | | | | ± 100 | ± 1 | 1.0 to 2.2M | E24; E96 |
| | | | | | ± 200 | ± 5 | 1.0 to 2.2M | E24 |
| | | | | | Zero-Ohm-Resistor: $R_{\text{max.}} = 20 \text{ m}\Omega, I_{\text{max.}} \text{ at } 70\text{ }^\circ\text{C} = 7.0 \text{ A}$ | | | |
| RCA2010 | 2010 | RR5025 | 0.75 | 400 | ± 50 | $\pm 0.5, \pm 1$ | 100 to 10M | E24; E96 |
| | | | | | ± 100 | ± 0.5 | 10 to 10M | E24; E96 |
| | | | | | ± 100 | ± 1 | 1.0 to 10M | E24; E96 |
| | | | | | ± 200 | ± 5 | 1.0 to 10M | E24 |
| | | | | | Zero-Ohm-Resistor: $R_{\text{max.}} = 20 \text{ m}\Omega, I_{\text{max.}} \text{ at } 70\text{ }^\circ\text{C} = 6.0 \text{ A}$ | | | |
| RCA2512 | 2512 | RR6332 | 1.0 | 500 | ± 50 | $\pm 0.5, \pm 1$ | 100 to 10M | E24; E96 |
| | | | | | ± 100 | ± 0.5 | 10 to 10M | E24; E96 |
| | | | | | ± 100 | ± 1 | 1.0 to 10M | E24; E96 |
| | | | | | ± 200 | ± 5 | 1.0 to 10M | E24 |
| | | | | | Zero-Ohm-Resistor: $R_{\text{max.}} = 20 \text{ m}\Omega, I_{\text{max.}} \text{ at } 70\text{ }^\circ\text{C} = 7.0 \text{ A}$ | | | |

Notes

- These resistors do not feature a limited lifetime when operated within the permissible limits. However, resistance value drift increasing over operating time may result in exceeding a limit acceptable to the specific application, thereby establishing a functional time.
- Marking: See document "Surface Mount Resistor Marking" (document number 20020).
- Power rating depends on the max. temperature at the solder point, the component placement density and the substrate material.



| TECHNICAL SPECIFICATIONS | | | | | | | | | |
|--|-------------|------------------------|---------|---------|---------|---------|---------|---------|---------|
| PARAMETER | UNIT | RCA0402 | RCA0603 | RCA0805 | RCA1206 | RCA1210 | RCA1218 | RCA2010 | RCA2512 |
| Rated dissipation P_{70} ⁽¹⁾ | W | 0.063 | 0.10 | 0.125 | 0.25 | 0.5 | 1.0 | 0.75 | 1.0 |
| Limiting element voltage U_{max} . AC/DC | V | 50 | 75 | 150 | 200 | 200 | 200 | 400 | 500 |
| Insulation voltage $U_{ins.}$ (1 min) | V | > 75 | > 100 | > 200 | > 300 | > 300 | > 300 | > 300 | > 300 |
| Insulation resistance | Ω | > 10^9 | | | | | | | |
| Category temperature range | $^{\circ}C$ | - 55 to + 155 | | | | | | | |
| Failure rate | h^{-1} | < 0.1×10^{-9} | | | | | | | |
| Mass | mg | 0.65 | 2 | 5.5 | 10 | 16 | 29.5 | 25.5 | 40.5 |

Note

⁽¹⁾ The power dissipation on the resistor generates a temperature rise against the local ambient, depending on the heat flow support of the printed-circuit board (thermal resistance). The rated dissipation applies only if the permitted film temperature of 155 °C is not exceeded.

| PART NUMBER AND PRODUCT DESCRIPTION | | | | | | | | | | | | | | |
|--|---|---|---|---|---|--|---|---|---|----------------------------------|---|---|---|---|
| Part Number: RCA080510K0FKEA ⁽²⁾ | | | | | | | | | | | | | | |
| R | C | A | 0 | 8 | 0 | 5 | 1 | 0 | K | 0 | F | K | E | A |
| MODEL | | VALUE | | TOLERANCE | | TCR | | PACKAGING ⁽³⁾ | | | | | | |
| RCA0402 RCA0603 RCA0805 RCA1206 RCA1210 RCA1218 RCA2010 RCA2512 | | R = Decimal K = Thousand M = Million 0000 = 0 Ω Jumper | | D = $\pm 0.5\%$ F = $\pm 1\%$ J = $\pm 5\%$ Z = Jumper | | H = ± 50 ppm/K K = ± 100 ppm/K N = ± 200 ppm/K S = Jumper | | EA EB EC ED EE EF EG EH EK | | | | | | |
| Product Description: RCA0805 10K 1% 100 ET1 e3 | | | | | | | | | | | | | | |
| RCA0805 | | 10K | | 1% | | 100 | | ET1 | | e3 | | | | |
| MODEL | | RESISTANCE VALUE | | TOLERANCE | | TCR | | PACKAGING ⁽³⁾ | | LEAD (Pb)-FREE | | | | |
| RCA0402 RCA0603 RCA0805 RCA1206 RCA1210 RCA1218 RCA2010 RCA2512 | | 10R = 10 Ω 10K = 10 k Ω 1M = 1 M Ω 0R0 = Jumper | | $\pm 0.5\%$ $\pm 1\%$ $\pm 5\%$ | | ± 50 ppm/K ± 100 ppm/K ± 200 ppm/K | | ET1, ET5 ET6, ET7 EF4, E02 E67, E82 ET9 | | e3 = Pure tin termination finish | | | | |

Notes

- ⁽²⁾ Preferred way for ordering products is by use of the PART NUMBER
- ⁽³⁾ Please refer to table PACKAGING, see next page


| PACKAGING | | | | | | | | |
|-----------|------------|---------------|-------|--------------|----------------|---------|---------------|---------|
| MODEL | REEL | | | | | | | |
| | TAPE WIDTH | DIAMETER | PITCH | PIECES/ REEL | PACKAGING CODE | | | |
| | | | | | PART NUMBER | | PRODUCT DESC. | |
| | | | | | PAPER | BLISTER | PAPER | BLISTER |
| RCA0402 | 8 mm | 180 mm/7" | 2 mm | 10 000 | ED | | ET7 | |
| | | 285 mm/11.25" | 2 mm | 20 000 | EC | | ET6 | |
| | | 330 mm/13" | 2 mm | 50 000 | EE | | EF4 | |
| RCA0603 | 8 mm | 180 mm/7" | 4 mm | 5000 | EA | | ET1 | |
| | | 285 mm/11.25" | 4 mm | 10 000 | EB | | ET5 | |
| | | 330 mm/13" | 4 mm | 20 000 | EC | | ET6 | |
| RCA0805 | 8 mm | 180 mm/7" | 4 mm | 5000 | EA | | ET1 | |
| | | 285 mm/11.25" | 4 mm | 10 000 | EB | | ET5 | |
| | | 330 mm/13" | 4 mm | 20 000 | EC | | ET6 | |
| RCA1206 | 8 mm | 180 mm/7" | 4 mm | 5000 | EA | | ET1 | |
| | | 285 mm/11.25" | 4 mm | 10 000 | EB | | ET5 | |
| | | 330 mm/13" | 4 mm | 20 000 | EC | | ET6 | |
| RCA1210 | 8 mm | 180 mm/7" | 4 mm | 5000 | EA | | ET1 | |
| | | 285 mm/11.25" | 4 mm | 10 000 | EB | | ET5 | |
| | | 330 mm/13" | 4 mm | 20 000 | EC | | ET6 | |
| RCA1218 | 12 mm | 180 mm/7" | 4 mm | 4000 | | EK | | ET9 |
| RCA2010 | 12 mm | 180 mm/7" | 4 mm | 4000 | | EF | | E02 |
| RCA2512 | 12 mm | 180 mm/7" | 8 mm | 2000 | | EG | | E67 |
| | | | 4 mm | 4000 | | EH | | E82 |

| DIMENSIONS in millimeters | | | | | | | | | | | | |
|---------------------------|--------|--|-------------|-------------|---------------------------------------|-----------|-----------------------|-----|-----|----------------|-----|-----|
| | | | | | | | | | | | | |
| SIZE | | DIMENSIONS | | | | | SOLDER PAD DIMENSIONS | | | | | |
| INCH | METRIC | L | W | H | T1 | T2 | REFLOW SOLDERING | | | WAVE SOLDERING | | |
| | | | | | | | a | b | l | a | b | l |
| 0402 | 1005 | 1.0 ± 0.05 | 0.5 ± 0.05 | 0.35 ± 0.05 | 0.25 ± 0.05 | 0.2 ± 0.1 | 0.4 | 0.6 | 0.5 | | | |
| 0603 | 1608 | 1.55 ^{+0.10} _{-0.05} | 0.85 ± 0.1 | 0.45 ± 0.05 | 0.3 ± 0.2 | 0.3 ± 0.2 | 0.5 | 0.9 | 1.0 | 0.9 | 0.9 | 1.0 |
| 0805 | 2012 | 2.0 ^{+0.20} _{-0.10} | 1.25 ± 0.15 | 0.45 ± 0.05 | 0.3 ^{+0.20} _{-0.10} | 0.3 ± 0.2 | 0.7 | 1.3 | 1.2 | 0.9 | 1.3 | 1.3 |
| 1206 | 3216 | 3.2 ^{+0.10} _{-0.20} | 1.6 ± 0.15 | 0.55 ± 0.05 | 0.45 ± 0.2 | 0.4 ± 0.2 | 0.9 | 1.7 | 2.0 | 1.1 | 1.7 | 2.3 |
| 1210 | 3225 | 3.2 ± 0.2 | 2.5 ± 0.2 | 0.55 ± 0.05 | 0.45 ± 0.2 | 0.4 ± 0.2 | 0.9 | 2.5 | 2.0 | 1.1 | 2.5 | 2.2 |
| 1218 | 3246 | 3.2 ^{+0.10} _{-0.20} | 4.6 ± 0.15 | 0.55 ± 0.05 | 0.45 ± 0.2 | 0.4 ± 0.2 | 1.05 | 4.9 | 1.9 | 1.25 | 4.8 | 1.9 |
| 2010 | 5025 | 5.0 ± 0.15 | 2.5 ± 0.15 | 0.6 ± 0.1 | 0.6 ± 0.2 | 0.6 ± 0.2 | 1.0 | 2.5 | 3.9 | 1.2 | 2.5 | 3.9 |
| 2512 | 6332 | 6.3 ± 0.2 | 3.15 ± 0.15 | 0.6 ± 0.1 | 0.6 ± 0.2 | 0.6 ± 0.2 | 1.0 | 3.2 | 5.2 | 1.2 | 3.2 | 5.2 |



FUNCTIONAL PERFORMANCE

| PERFORMANCE IN SULFUR-CONTAINING AMBIANCE | | |
|--|---|---|
| TEST NAME | HUMID SULFUR VAPOR TEST | HUMID SULFUR VAPOR TEST (Accelerated) |
| Reference specification | ASTM B809-95 | ASTM B809-95 accelerated conditions |
| Test conditions (temperature, humidity) | 60 °C ± 2 °C 85 % ± 4 % RH | 90 °C ± 2 °C 74 % ± 7 % RH |
| Aggressive agent | Sulfur (saturated vapor) | Sulfur (saturated vapor) |
| Failure criteria in VI under magnification | No silver sulfide growth at the interface between termination and protective overcoat. No signs of mechanical damage. | No silver sulfide growth at the interface between termination and protective overcoat. No signs of mechanical damage. |
| Failure criteria in electrical test | ≤ (± 1 % R + 0.05 Ω) | ≤ (± 1 % R + 0.05 Ω) |
| Time before failure | 8000 h | 1000 h |





| TEST PROCEDURES AND REQUIREMENTS | | | | | |
|----------------------------------|----------------------------|---|--|---|--------------------------------|
| EN 60115-1 CLAUSE | IEC 60068-2 TEST METHOD | TEST | PROCEDURE | REQUIREMENTS PERMISSIBLE CHANGE (ΔR) | |
| | | | | SIZE 0402 | SIZE 0603 TO 2512 |
| | | | | STABILITY CLASS 2 OR BETTER | |
| | | | Stability for product types: | 1 Ω to 10 M Ω | |
| | | | RCA e3 | 0.5 %, ± 1 %, ± 5 % | |
| 4.5 | - | Resistance | - | 0.5 %, ± 1 %, ± 5 % | |
| 4.8.4.2 | - | Temperature coefficient | (20/- 55/20) °C and (20/125/20) °C | ± 50 ppm/K, ± 100 ppm/K, ± 200 ppm/K | |
| 4.13 | - | Short time overload | $U = 2.5 \times \sqrt{P_{70} \times R} \leq 2 \times U_{max.}$; duration: According to style | $\pm (0.25 \% R + 0.05 \Omega)$ | |
| 4.19 | 14 (Na) | Rapid change of temperature | 30 min. at - 55 °C; 30 min. at 125 °C 5 cycles 1000 cycles | $\pm (0.25 \% R + 0.05 \Omega)$ $\pm (1 \% R + 0.05 \Omega)$ | |
| 4.25.1 | - | Endurance at 70 °C | $U = \sqrt{P_{70} \times R} \leq U_{max.}$; 1.5 h on; 0.5 h off; 70 °C, 1000 h | $\pm (1 \% R + 0.05 \Omega)$ | $\pm (0.5 \% R + 0.05 \Omega)$ |
| 4.18.2 | 58 (Td) | Resistance to soldering heat | Solder bath method (260 \pm 5) °C (10 \pm 1) s | $\pm (0.25 \% R + 0.05 \Omega)$ | |
| 4.24 | 78 (Cab) | Damp heat, steady state | (40 \pm 2) °C; (93 \pm 3) % RH; 56 days | $\pm (1 \% R + 0.05 \Omega)$ | $\pm (0.5 \% R + 0.05 \Omega)$ |
| 4.25.3 | - | Endurance at upper category temperature | 155 °C, 1000 h | $\pm (0.5 \% R + 0.05 \Omega)$ | |

All tests are carried out in accordance with the following specifications:

- EN 60115-1, generic specification
- EN 140400, sectional specification
- EN 140401-802, detail specification
- AEC-Q200, automotive specification
- IEC 60068-2, environmental test procedures
- ASTM B 809-95, standard test method for porosity in metallic coatings by humid sulfur.

Packaging of components is done in paper or blister tapes according to IEC 60286-3.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[RCA06032K74FKEA](#) [RCA040275K0FKED](#) [RCA2512237KFKEG](#) [RCA040216K2FKED](#) [RCA06033K01FKEA](#)
[RCA060322R1FKEA](#) [RCA060312K7FKEA](#) [RCA1206301KFKEA](#) [RCA060371K5FKEA](#) [RCA06039K09FKEA](#)
[RCA120616R2FKEA](#) [RCA04021K50FKED](#) [RCA120682R5FKEA](#) [RCA0402464KFKEA](#) [RCA0603604RFKEA](#)
[RCA04022K40FKED](#) [RCA080510K0FKEC](#) [RCA04026K04FKED](#) [RCA0603432RFKEA](#) [RCA060345K3FKEA](#)
[RCA12062K00FKEA](#) [RCA04025K10FKED](#) [RCA060310M0FKEA](#) [RCA060334K0FKEA](#) [RCA080547K0FKEA](#)
[RCA0402383KFKEA](#) [RCA08055R60FKEA](#) [RCA0402475RFKEA](#) [RCA06033K16FKEA](#) [RCA0805150RFKEA](#)
[RCA080547K5FKEA](#) [RCA12062K67FKEA](#) [RCA120647R0FKEA](#) [RCA12104K75FKEA](#) [RCA12064M02FKEA](#)
[RCA12063R00FKEA](#) [RCA0603150KFKEA](#) [RCA040280R6FKED](#) [RCA04029K09FKED](#) [RCA2010453RFKEF](#)
[RCA12065R60JNEA](#) [RCA0402240RFKEA](#) [RCA2512150KFKEG](#) [RCA12064R75FKEA](#) [RCA040224K9FKED](#)
[RCA04022K80FKED](#) [RCA08054K75FKEA](#) [RCA06032R20FKEC](#) [RCA080521K5FKEA](#) [RCA1206210KFKEA](#)