

549945 Composite - CCTV Plus Audio or Power or Pan and Tilt CCTV Control Applications



For more Information
please call

1-800-Belden1



General Description:

PTZ (CCTV+Power/Audio) Cable, Rated-CMG, 1-RG59 20 AWG solid bare copper with foam polyolefin, 95% bare copper braid, 1-18 AWG stranded bare copper pair with polyolefin insulation, Siamese with PVC jacket

Usage (Overall)

Suitable Applications: CCTV plus Audio, Pan and Tilt CCTV Control

Coax

Physical Characteristics

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	20	Solid	BC - bare Copper	0.032

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
Gas-injected FHDPE - Foam High Density Polyethylene	0.145

Inner Shield

Inner Shield Material:

Type	Inner Shield Material	% Coverage (%)
Braid	BC - Bare Copper	95.000

Applicable Specifications and Agency Compliance

Applicable Standards & Environmental Programs

EU CE Mark: Yes
RG Type: 59/U

Electrical Characteristics

Nom. Characteristic Impedance:

Impedance (Ohm)
75

Nom. Inductance:

Inductance (µH/ft)
0.097

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)
16.300

Nominal Velocity of Propagation:

VP (%)
83.000

Nominal Delay:

Delay (ns/ft)
1.220

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
10.000

Nom. Inner Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
3.500

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
1.000	0.300
5.000	0.650

549945 Composite - CCTV Plus Audio or Power or Pan and Tilt CCTV Control Applications

10.000	0.900
50.000	1.900
100.000	2.600
200.000	3.600
400.000	5.000
700.000	7.000
900.000	8.000
1000.000	8.500

Max. Operating Voltage - UL:

350 V RMS

Twisted Pair

Physical Characteristics

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (in.)
1	18	7x26	BC - Bare Copper	0.046

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
PP - Polypropylene	0.059

Twisted Pair Color Code Chart:

Number	Color
1	Black and Red

Electrical Characteristics

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
22.500

Physical Characteristics (Overall)

Conductor

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 0.232 x 0.450 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -30°C To +80°C

UL Temperature Rating: 75°C

Bulk Cable Weight: 54 lbs/1000 ft.

Max. Recommended Pulling Tension: 102 lbs.

Min. Bend Radius/Minor Axis: 2.500 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMG

NEC Articles: 800

CEC/C(UL) Specification: CMG

EU Directive 2011/65/EU (ROHS II): Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

549945 Composite - CCTV Plus Audio or Power or Pan and Tilt CCTV Control Applications

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Flame Test

UL Flame Test: UL1685 UL Loading

C(UL) Flame Test: FT4

Suitability

Suitability - Indoor: Yes

Suitability - Outdoor: Yes

Suitability - Aerial: Yes

Plenum/Non-Plenum

Plenum (Y/N): No

Plenum Number: 649948

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
549945 0091000	1,000 FT	53.000 LB	WHITE	C	RG59 + 2C18 CMG SIAM
549945 009500	500 FT	28.500 LB	WHITE	C	RG59 + 2C18 CMG SIAM
549945 0101000	1,000 FT	53.000 LB	BLACK	C	RG59 + 2C18 CMG SIAM
549945 010500	500 FT	28.500 LB	BLACK	C	RG59 + 2C18 CMG SIAM

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 5 Revision Date: 03-13-2013

© 2017 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[549945 0101000](#) [549945 009500](#) [549945 0091000](#) [549945 010500](#)