



Glass Passivated Rectifier Diode Modules

VRRM 800 to 1800V


IFAV 165 Amp

Applications

- Non-controllable rectifiers for AC/AC converters
- Line rectifiers for transistorized AC motor controllers
- Field supply for DC motors

Features

- Blocking voltage: 800 to 1800V
- Heat transfer through aluminum oxide DBC ceramic isolated metal baseplate
- Glass passivated chip
- UL E243882 approved



Module Type

TYPE			VRRM	VRS
MSCD165-08	MSAD165-08	MSKD165-08	800V	900V
MSCD165-12	MSAD165-12	MSKD165-12	1200V	1300V
MSCD165-16	MSAD165-16	MSKD165-16	1600V	1700V
MSCD165-18	MSAD165-18	MSKD165-18	1800V	1900V

Maximum Ratings

Symbol	Conditions	Values	Units
IFAV	Single phase ,half wave 180° conduction Tc=101℃	165	A
IF(RMS)	Single phase ,half wave 180° conduction Tc=101℃	220	A
IFSM	t=10mS Tvj =45℃	6000	A
i ² t	t=10mS Tvj =45℃	180000	A ² s
Visol	a.c.50HZ;r.m.s.;1min	3000	V
Tvj		-40 to +150	℃
Tstg		-40 to +125	℃
Mt	To terminals(M6)	5±15%	Nm
Ms	To heatsink(M6)	5±15%	Nm
Weight	Module (Approximately)	160	g

Thermal Characteristics

Symbol	Conditions	Values	Units
Rth(j-c)	Per diode	0.21	℃/W
Rth(c-s)	Module	0.05	℃/W

Electrical Characteristics

Symbol	Conditions	Values			Units
		Min.	Typ.	Max.	
VFM	T=25℃ IF =300A	—	1.20	1.40	V
IRD	Tvj=150℃ VRD=VRRM	—	—	9	mA

Performance Curves




Fig1. Power dissipation




Fig2. Forward Current Derating Curve




Fig3. Transient thermal impedance




Fig4. Max Non-Repetitive Forward Surge Current





Fig5. Forward Characteristics

CASE: D2



Dimensions in mm

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Microsemi:

[MSKD165-12](#) [MSAD165-12](#) [MSAD165-16](#) [MSCD165-18](#) [MSCD165-12](#) [MSCD165-08](#) [MSAD165-08](#) [MSKD165-18](#)
[MSAD165-18](#)