




## Features

- Lead free as standard
- RoHS compliant\*
- Low capacitance - 1.3 pF
- ESD protection >25 kV
- Surge protection

## Applications


- Personal Digital Assistants (PDAs)
- Notebook and PC computers
- Memory card protection
- SIM card port protection
- Portable electronics

# CDSC706-0504C - Surface Mount TVS Diode Array

## General Information

The CDSC706-0504C device provides ESD, EFT and Surge protection for high speed data ports meeting IEC 61000-4-2 (ESD), IEC 61000-4-4 (EFT) and IEC 61000-4-5 (Surge) requirements. The Transient Voltage Suppressor array, protecting up to 4 data lines, offers a Working Peak Reverse Voltage of 5 V and Minimum Breakdown Voltage of 6 V.

The SC70-6L packaged device will mount directly onto the industry standard SC70-6 footprint. Bourns® Chip Diodes conform to JEDEC standards, are easy to handle with standard pick and place equipment and the flat configuration minimizes roll away.



## Thermal Characteristics (@ T<sub>A</sub> = 25 °C Unless Otherwise Noted)

| Parameter                                               | Symbol               | CDSC706-0504C          | Unit |
|---------------------------------------------------------|----------------------|------------------------|------|
| Peak Pulse Power (t <sub>p</sub> = 8/20 μs)             | I <sub>PP</sub>      | 6.5                    | A    |
| Storage Temperature                                     | T <sub>STG</sub>     | -55 to +150            | °C   |
| Operating Temperature                                   | T <sub>OPR</sub>     | -55 to +85             | °C   |
| Operating Supply Voltage                                | V <sub>DC</sub>      | 6                      | V    |
| ESD per IEC61000-4-2 (Air) (I/O Pins)                   | V <sub>esd</sub> IO  | 18                     | kV   |
| ESD per IEC61000-4-2 (Contact) (I/O Pins)               |                      | 14                     |      |
| ESD per IEC61000-4-2 (Air) (V <sub>CC</sub> to GND)     | V <sub>esd</sub> VCC | 30                     | kV   |
| ESD per IEC61000-4-2 (Contact) (V <sub>CC</sub> to GND) |                      | 30                     |      |
| DC Voltage at any I/O Pin                               | V <sub>IO</sub>      | (GND-0.5) to (VCC+0.5) | V    |

## Electrical Characteristics (@ T<sub>A</sub> = 25 °C Unless Otherwise Noted)

| Parameter                                                                                                                                            | Symbol                | CDSC706-0504C | Unit |
|------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|---------------|------|
| Maximum Reverse Standoff Voltage <sup>1</sup>                                                                                                        | V <sub>RWM</sub>      | 5.0           | V    |
| Maximum Leakage Current <sup>1</sup> @ V <sub>RWM</sub>                                                                                              | I <sub>L</sub>        | 5.0           | μA   |
| Maximum Channel Leakage Current @ V <sub>RWM</sub>                                                                                                   | I <sub>CD</sub>       | 1.0           | μA   |
| Minimum Reverse Breakdown Voltage <sup>1</sup><br>@ I <sub>BV</sub> =1 mA                                                                            | V <sub>BR</sub>       | 6.0           | V    |
| Maximum Forward Voltage <sup>4</sup> @ I <sub>F</sub> = 15 mA                                                                                        | V <sub>F</sub>        | 1.0           | V    |
| Maximum Clamping Voltage <sup>2</sup> @ 5 A 8/20 μs                                                                                                  | V <sub>C</sub>        | 9.0           | V    |
| Typical ESD Clamping Voltage- I/O <sup>2</sup>                                                                                                       | V <sub>clamp io</sub> | 12.5          | V    |
| Maximum Channel Input Capacitance <sup>2</sup><br>@ V <sub>PIN5</sub> =5 V, V <sub>PIN2</sub> =0 V, V <sub>IN</sub> =2.5 V, f=1 MHz                  | C <sub>IN</sub>       | 1.6           | pF   |
| Max. Channel to Channel Input Capacitance <sup>3</sup><br>@ V <sub>PIN5</sub> =5 V, V <sub>PIN2</sub> =0 V, V <sub>IN</sub> =2.5 V, f=1 MHz          | C <sub>CROSS</sub>    | 0.14          | pF   |
| Max. Variation of Channel Input Capacitance<br>@ V <sub>PIN5</sub> =5 V, V <sub>PIN2</sub> =0 V, V <sub>IN</sub> =2.5 V, f=1 MHz<br>(I/O Pin to GND) | ΔC <sub>IN</sub>      | 0.07          | pF   |

**Notes:** 1: Pin 5 to Pin 2 (ground)  
2: Pin 1, 3, 4 or 6 to Pin 2 (ground)


3: Between any two of pins 1, 3, 4, 6.  
4: Pin 2 (ground) to Pin 5

# CDSC706-0504C - Surface Mount TVS Diode Array


**BOURNS®**

## Product Dimensions


This is a molded JEDEC SC70-6L package with lead free 100 % Matte Sn on the lead frame. It weighs approximately 7 mg and has a flammability rating of UL 94V-0.



## Configuration



## Recommended Footprint



DIMENSIONS =  $\frac{\text{MILLIMETERS}}{(\text{INCHES})}$

## Typical Part Marking

CDSC706-0504C.....C05

## How to Order

Common Code **CD**

Chip Diode **SC706**

Package **05**

Working Peak Reverse Voltage **04**

Number of Lines **C**

Suffix **C**


C = Low Capacitance

# CDSC706-0504C - Surface Mount TVS Diode Array


**BOURNS®**

## Rating & Characteristic Curves


### Clamping Voltage vs. Peak Pulse Current




### Pulse Waveform




### Overshoot and Clamping Voltage




### Power Derating Curve



### Forward Voltage vs. Forward Current



### Typical Variation of $C_{in}$ vs. $V_{in}$




# CDSC706-0504C - Surface Mount TVS Diode Array

**BOURNS®**

## Packaging Information

The product is packaged in tape and reel format per EIA-481 Standard.



| Item                   | Symbol         | SC70-6L                                   |
|------------------------|----------------|-------------------------------------------|
| Carrier Width          | A              | $\frac{2.25 \pm 0.10}{(0.088 \pm 0.004)}$ |
| Carrier Length         | B              | $\frac{2.34 \pm 0.10}{(0.092 \pm 0.004)}$ |
| Carrier Depth          | C              | $\frac{1.22 \pm 0.10}{(0.048 \pm 0.004)}$ |
| Sprocket Hole          | d              | $\frac{1.55 \pm 0.05}{(0.061 \pm 0.002)}$ |
| Reel Outside Diameter  | D              | $\frac{178}{(7.008)}$                     |
| Reel Inner Diameter    | D <sub>1</sub> | $\frac{50.0}{(1.969)} \text{ MIN.}$       |
| Feed Hole Diameter     | D <sub>2</sub> | $\frac{13.0 \pm 0.20}{(0.512 \pm 0.008)}$ |
| Sprocket Hole Position | E              | $\frac{1.75 \pm 0.10}{(0.069 \pm 0.004)}$ |
| Punch Hole Position    | F              | $\frac{3.50 \pm 0.05}{(0.138 \pm 0.002)}$ |
| Punch Hole Pitch       | P              | $\frac{4.00 \pm 0.10}{(0.157 \pm 0.004)}$ |
| Sprocket Hole Pitch    | P <sub>0</sub> | $\frac{4.00 \pm 0.10}{(0.157 \pm 0.004)}$ |
| Embossment Center      | P <sub>1</sub> | $\frac{2.00 \pm 0.05}{(0.079 \pm 0.002)}$ |
| Overall Tape Thickness | T              | $\frac{0.20 \pm 0.10}{(0.008 \pm 0.004)}$ |
| Tape Width             | W              | $\frac{8.00 \pm 0.20}{(0.315 \pm 0.008)}$ |
| Reel Width             | W <sub>1</sub> | $\frac{14.4}{(0.567)} \text{ MAX.}$       |
| Quantity per Reel      | --             | 3000                                      |

REV. 12/12

Specifications are subject to change without notice.  
Customers should verify actual device performance in their specific applications.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bourns:

[CDSC706-0504C](#)