


# Stratos

## RJS-ST31 Optical Transceiver

Connectivity for  
Business Critical Continuity™



4x / 2x / 1x Fiber Channel Applications,  
850nm Micro Module 4.25 / 2.125 / 1.0625 GBaud

### Product Overview

The Emerson Network Power Connectivity Solutions RJS-ST31 transceiver module is a high performance integrated full duplex data link for bi-directional communication over multimode optical fiber. It has been designed for use in space constrained applications, and offers the mandatory FC compliance commonly provided by SFF and SFP transceivers. This optoelectronic transceiver module is a Class 1 Laser product compliant with FDA Radiation Performance Standards, 21 CFR Subchapter J. This component is also Class 1 Laser compliant according to International Safety Standard IEC-825-1/EN 60825.

### Ordering Information

RJ	S	-	ST3	1
<b>Communications Protocol</b> S=4XFC / 2XFC / 1XFC 4.25 / 2.125 / 1.0625 GBaud			<b>Wavelength</b> 1=850nm (multimode)	

### Key Features & Benefits

- 4.25 GBaud Fiber Channel Compliant
- 2.125 GBaud Fiber Channel Compliant
- 1.0625 GBaud Fiber Channel Compliant
- 100Ω differential DC coupled inputs/outputs
- Industry Standard LC Connector Interface
- Metal housing
- Single +3.3V Power Supply
- RoHS Compliant

### Module Specifications – Electrical: 0°C<T<sub>c</sub><+70°C, +3.135<V<sub>cc</sub><+3.465V

Parameter	Sym	MIN	Typ	MAX	Unit	Notes
Supply Current			125	195	mA	0°C<T <sub>c</sub> <+70°C, +3.135<V <sub>cc</sub> <+3.465V
<b>Transmitter</b>						
Input Swing (Differential)	V <sub>in</sub>	500		2200	mV <sub>pp</sub>	
Input Impedance (Differential) <sup>1</sup>	R <sub>in</sub>		100		Ω	Internally terminated
TX_DISABLE Input Voltage – High	V <sub>iH</sub>	2		3.465	V	
TX_DISABLE Input Voltage – Low	V <sub>iL</sub>	0		0.8	V	
<b>Receiver</b>						
Output Swing (Differential)		300		1200	mV <sub>pp</sub>	
Output Impedance (Differential)	R <sub>out</sub>		100		Ω	
Single Detect Output Voltage – High <sup>2</sup>	V <sub>roH</sub>	V <sub>cc</sub> -0.5		V <sub>cc</sub> +0.3	V	I <sub>o</sub> = 400μA; Host V <sub>cc</sub>
Single Detect Output Voltage – Low <sup>3</sup>	V <sub>roL</sub>	0		0.8	V	I <sub>o</sub> = -4.0mA

# Stratos

## RJS-ST31 Optical Transceiver

Connectivity for  
Business-Critical Continuity™

### Module Specifications – Optical: 0°C<Tc<+70°C, +3.135<Vcc<+3.465V

Parameter	Sym	MIN	Typ	MAX	Unit	Notes
<b>Transmission Distance</b>						
50µm Core Diameter MMF		150	250		M	BER<1.0E-12 @ 4.25 GBaud
		300	500			BER<1.0E-12 @ 2.125 GBaud
		550	1000			BER<1.0E-12 @ 1.25/1.0625 GBaud
62.5µm Core Diameter MMF		70	150		M	BER<1.0E-12 @ 4.25 GBaud
		150	300			BER<1.0E-12 @ 2.125 GBaud
		300	500			BER<1.0E-12 @ 1.25/1.0625 GBaud
<b>Transmitter</b>						
Optical Center Wavelength	λ	830	850	860	nm	
Spectral Width	Δλ			0.85	nm	RMS
Optical Transmit Power	Popt	-9		-3	dBm	Average @ 850nm
Optical Modulation Amplitude	OMA	247			µW	Pk-pk @ 4.25 GBaud
		196			µW	Pk-pk @ 2.125 GBaud
		156			µW	Pk-pk @ 1.0625 GBaud
Relative Intensity Noise	RIN			-118	dB/Hz	Measured with -12dB optical return loss
Output Eye	Complies with ANSI FC-PI Specification and Class 1 Laser Eye Safety					
<b>Receiver</b>						
Optical Input Wavelength	λ	830		860	nm	
Optical Input Power	Pr	-15		0	dBm	BER<1.0E-12 @ 4.25 GBaud
		-18		0		BER<1.0E-12 @ 2.125 GBaud
		-20		0		BER<1.0E-12 @ 1.25/1.0625 GBaud
Optical Modulation Input	OMA	61			µW	Pk-pk @ 4.25 GBaud
		49				Pk-pk @ 2.125 GBaud
		31				Pk-pk @ 1.0625 GBaud
Optical Return Loss	ORL	12			dB	
SD – Deasserted	Pd	-29			dBm	
SD – Asserted	Pa			-15	dBm	4.25 GBaud
				-18		2.125 GBaud
				-20		1.25/1.0625 GBaud
SD – Hysteresis	Pa-Pd		2.25	3.5	dB	

For more information on this product consult the RJS-ST31 product data sheet.

#### IMPORTANT NOTICE

Stratos International, Inc. reserves the right to make changes to or discontinue any optical link product or service identified in this publication, without notice. Stratos International, Inc. recommends that its customers obtain the latest version of the publications to verify, before placing orders, that the information being relied on is current. Stratos International, Inc. warrants performance of its optical link products to current specifications in accordance with the Stratos International, Inc. standard warranty. Testing and other quality control techniques are utilized to the extent that Stratos International, Inc. has determined it to be necessary to support this warranty. Specific testing of all parameters of each optical link product is not necessarily performed on all optical link products. Stratos International, Inc. products are not designed for use in life support appliances, devices, or systems where malfunction of a Stratos International, Inc. product can reasonably be expected to result in a personal injury. Stratos International, Inc. customers using or selling optical link products for use in such applications do so at their own risk and agree to fully indemnify Stratos International, Inc. for any damages resulting from such improper use or sale. Stratos International, Inc. assumes no liability for Stratos International, Inc. applications assistance, customer product design, software performance, or infringement of patents or services described here in. Nor does Stratos International, Inc. warrant or represent that a license, either expressed or implied is granted under any patent right, copyright, or intellectual property right, and makes no representations or warranties that these products are free from patent, copyright, or intellectual property rights. Applications that are described herein for any of the optical link products are for illustrative purposes only. Stratos International, Inc. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[RJS-ST31](#)