



EC3AW SERIES

3 WATT 4:1 INPUT RANGE

DC-DC CONVERTERS



FEATURES

- * 3W Isolated Output
- * DIP-24/SMD Package
- * Efficiency to 77%
- * 4:1 Input Range
- * Regulated Outputs
- * Pi Input Filter
- * Continuous Short Circuit Protection



MODEL NUMBER	INPUT VOLTAGE	OUTPUT VOLTAGE	OUTPUT CURRENT	INPUT CURRENT		% EFF.	CASE
				NO LOAD	FULL LOAD		
EC3AW01	9-36 VDC	5 VDC	600 mA	15 mA	174 mA	72	DIP-24
EC3AW02	9-36 VDC	12 VDC	250 mA	15 mA	165 mA	76	DIP-24
EC3AW03	9-36 VDC	15 VDC	200 mA	15 mA	165 mA	76	DIP-24
EC3AW04	9-36 VDC	±5 VDC	±300 mA	25 mA	179 mA	70	DIP-24
EC3AW05	9-36 VDC	±12 VDC	±125 mA	25 mA	174 mA	72	DIP-24
EC3AW06	9-36 VDC	±15 VDC	±100 mA	25 mA	174 mA	72	DIP-24
EC3AW07	9-36 VDC	3.3 VDC	600 mA	15 mA	117 mA	70	DIP-24
EC3AW11	18-72 VDC	5 VDC	600 mA	7.5 mA	87 mA	72	DIP-24
EC3AW12	18-72 VDC	12 VDC	250 mA	7.5 mA	81 mA	77	DIP-24
EC3AW13	18-72 VDC	15 VDC	200 mA	7.5 mA	81 mA	77	DIP-24
EC3AW14	18-72 VDC	±5 VDC	±300 mA	12 mA	88 mA	71	DIP-24
EC3AW15	18-72 VDC	±12 VDC	±125 mA	12 mA	87 mA	72	DIP-24
EC3AW16	18-72 VDC	±15 VDC	±100 mA	12 mA	87 mA	72	DIP-24
EC3AW17	18-72 VDC	3.3 VDC	600 mA	7.5 mA	58 mA	70	DIP-24

NOTE: 1. Nominal Input Voltage 24 or 48 VDC

SPECIFICATIONS

All Specifications Typical At Nominal Line, Full Load, and 25°C Unless Otherwise Noted

INPUT SPECIFICATIONS:

Input Voltage Range	24V	9-36V
	48V	18-72V
Input Filter	Pi Type	

OUTPUT SPECIFICATIONS:


Voltage Accuracy	±2.0% max.
Voltage Balance (Dual)	±1.0% max.
Temperature Coefficient	±0.05%/°C
Ripple & Noise, 20MHz BW Single & ±5V	100mV pk-pk max.
	Dual 1% pk-pk max.
Short Circuit Protection	Continuous
Line Regulation Single/Dual (note1)	±0.5% max.
Load Regulation Single (note2)	±0.5% max.
	Dual (note3) ±1.0% max.

GENERAL SPECIFICATIONS:

Efficiency	See Table
Isolation Resistance	10 ⁹ ohm min.
Switching Frequency	100KHz min.
Operating Ambient Temperature Range	-25°C to +71°C
De-rating, Above 71°C (Plastic Case)	Linearly to Zero power at 95°C
De-rating, Above 71°C (Copper Case)	Linearly to Zero power at 100°C
Case Temperature (Plastic case note6)	95°C max.
	(Copper case note6) 100°C max.
Cooling	Natural Convection
Storage Temperature Range	-40°C to +100°C
Dimensions	DIP 1.25x0.80x0.40 inches(31.8x20.3x10.2 mm)
	SMD 1.25x0.80x0.45 inches(31.8x20.3x11.4 mm)
Weight	12.5g

Case A Dimensions:

NOTE: Pin Size is 0.02±0.002 Inch (0.5±0.05 mm) DIA
All Dimensions In Inches (mm)
Tolerances Inches: X.XX= ±0.02, X.XXX= ±0.010
Millimeters: X.X= ±0.5, X.XX= ±0.25



ISOLATION VOLTAGE:

500 VDC min.	Standard Models
3K VDC min. (note4)	Suffix "H" Models
1.5K VDC min.	Suffix "HM" Models


CASE MATERIAL:

Standard Models	Non-Conductive Black Plastic
Suffix "M" Models (note 5)	Black Coated Copper with Non-conductive Base

NOTE:

1. Measured from high line to low line.
2. Measured from full load to 10% load.
3. Measured from full load to 1/4 load.
4. Non-Conductive black plastic only.
5. Suffix "S" to the model number with SMD packages.
6. Maximum case temperature under any operating condition should not be exceeded 95°C (Plastic Case), 100°C (Copper Case).

Typical Derating curve for Natural Convection



PIN CONNECTION									
500 VDC					1.5K & 3K VDC				
Pin	Single Output		Dual Output		Pin	Single Output		Dual Output	
	DIP	SMD	DIP	SMD		DIP	SMD	DIP	SMD
1,24	+V Input		+V Input		1,24	NP	NC	NP	NC
2,23	NC		-V Output		2,3	-V Input		-V Input	
3,22	NC		Common		4,5	NP	NC	NP	NC
4	NP	NC	NP	NC	9	NC		Common	
5	NP	NC	NP	NC	10,15	NC		NC	
9	NP	NC	NP	NC	11	NC		-V Output	
10,15	-V Output		Common		12,13	NP	NC	NP	NC
11,14	+V Output		+V Output		14	+V Output		+V Output	
12,13	-V Input		-V Input		16	-V Output		Common	
16	NP	NC	NP	NC	20,21	NP	NC	NP	NC
20,21	NP	NC	NP	NC	22,23	+V Input		+V Input	

* NP-NO PIN

* NC-NO CONNECTION WITH PIN

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cincon:

[EC3AW14](#) [EC3AW01](#) [EC3AW02](#) [EC3AW03](#) [EC3AW04](#) [EC3AW05](#) [EC3AW06](#) [EC3AW07](#) [EC3AW11](#) [EC3AW12](#)
[EC3AW13](#) [EC3AW15](#) [EC3AW16](#) [EC3AW17](#) [EC3AW02HM](#) [EC3AW04M](#) [EC3AW02M](#) [EC3AW14HM](#) [EC3AW02H](#)
[EC3AW17M](#) [EC3AW12M](#) [EC3AW06H](#) [EC3AW05HM](#) [EC3AW05H](#) [EC3AW11HM](#) [EC3AW03M](#) [EC3AW04H](#)
[EC3AW11M](#) [EC3AW03H](#) [EC3AW15H](#) [EC3AW04HM](#) [EC3AW13M](#) [EC3AW16M](#) [EC3AW01M](#) [EC3AW14H](#)
[EC3AW07M](#) [EC3AW17HM](#) [EC3AW07H](#) [EC3AW12HM](#) [EC3AW16H](#) [EC3AW13H](#) [EC3AW06HM](#) [EC3AW11H](#)
[EC3AW01HM](#) [EC3AW15HM](#) [EC3AW01H](#) [EC3AW17H](#) [EC3AW13HM](#) [EC3AW03HM](#) [EC3AW05M](#) [EC3AW07HM](#)
[EC3AW16HM](#) [EC3AW12H](#) [EC3AW06M](#) [EC3AW15M](#) [EC3AW14M](#) [EC3AW01HMS](#) [EC3AW01MS](#) [EC3AW02HMS](#)
[EC3AW02MS](#) [EC3AW03HMS](#) [EC3AW03MS](#) [EC3AW04HMS](#) [EC3AW04MS](#) [EC3AW05HMS](#) [EC3AW05MS](#)
[EC3AW06HMS](#) [EC3AW06MS](#) [EC3AW07HMS](#) [EC3AW07MS](#) [EC3AW11HMS](#) [EC3AW11MS](#) [EC3AW12HMS](#)
[EC3AW12MS](#) [EC3AW13HMS](#) [EC3AW13MS](#) [EC3AW14HMS](#) [EC3AW14MS](#) [EC3AW15HMS](#) [EC3AW15MS](#)
[EC3AW16HMS](#) [EC3AW16MS](#) [EC3AW17HMS](#) [EC3AW17MS](#) [EC3AW12-NRH](#)