



CLC Series -G (RoHS Device)

Schematics:





Dimensions in (mm):

Package:



Package Code	Total Power	Number of Pins	L ± 0.2	W ± 0.2	p ± 0.1	e ± 0.1	Pkg. Height ± 0.2	d ± 0.1	c (ref.)
S14	225 mw	4	2.92	2.30	1.91	--	0.95	0.43	.038

Application:



Specifications: (Ta = 25°C)

5V0 Characteristic

Symbol	Characteristic	Min	Typ	Max	Units	Test Condition
V_{BD}	Diode breakdown voltage	6.0	-	11	V	$I_F = 1 \text{ ma}$
I_L	Leakage current		+0.1	+ 2.0	uA	5v
C_T	Capacitance		5		pF	@ 1Mhz
V_{ESD}	Channel clamp voltage			± 13	V	16kV event
V_{PV}	Peak ESD voltage capability			16	kV	IEC 61000-4-2
I_{pp}^*	Peak Pulse Current			5.1	A	8 / 20 us
T_o	Operating Temp. Range	-55		+155	°C	

* one diode conducting

Ordering Information:

CLC	S14	5V0	-G
Type	Package Code	Voltage	RoHS Compliance
CLC	S14 – SOT143	5V0	-G

- 3,000 units per reel

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Comchip Technology:](#)

[CLCS145V0-G](#)