


PROGRAMMABLE OSCILLATORS (SMD • Ceramic Package)

RoHS compliant / Pb free

SSX-750P SERIES


2000pcs/reel




FEATURES

- Wide range of output frequency by PLL technology.
- Quick sample delivery and short lead time in mass production.
- Low current consumption with output enable function (OE) or stand by function (STAND-BY).
- Suitable for various applications such as communication devices, AV devices and measuring instruments.

DIMENSION [mm]



SOLDER PAD LAYOUT [mm]



STANDARD SPECIFICATIONS * Model is determined by the selection for the output enable or stand-by function, the frequency stability and the supply voltage.

Item	Model	OE	SSX-750 PT (*)	SSX-750 PC (*)	SSX-750 PB (*)
		STAND-BY	SSX-750 PK (*)	SSX-750 PD (*)	SSX-750 PJ (*)
Frequency Range			1.000MHz ~ 125.000MHz		
Supply Voltage			Vdd : 5.0V±0.5V		Vdd : 3.3V±0.3V
Frequency Stability (*)			B : ±50ppm, C : ±100ppm, E : ±50ppm (− 40℃~+ 85℃), F : ±100ppm (− 40℃~+ 85℃)		
Operating Temperature Range			−20℃~+70℃ (− 40℃~+ 85℃)		
Storage Temperature Range			−55℃~+125℃		
Current consumption			45mA Max.		28mA Max.
Duty	TTL level (1.4V)		40~60%	—	
	CMOS level (1/2 Vdd)		—	40~60%	
Output Voltage	VOH		Vdd−4.0V Min.		
	VOL		0.4V Max.		
Output Load	TTL		5TTL Max.	—	
	CMOS		—	25pF Max.	15pF Max.
Rise and Fall Time			4 nsec Max.		
Start-up time			10 msec Max.		
Input Voltage	VIH		2.0V Min.		0.7Vdd Min.
	VIL		0.8V Max.		0.2Vdd Max.
Disable current			30mA Max.		16mA Max.
Stand-by current			50 μA Max.		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Citizen:

[SSX750PCC20.000MT-UT](#) [SSX750PCG-FREQ-UT](#) [SSX750PBB-FREQ-UT](#) [SSX750PCF-FREQ-UT](#) [SSX750PTG-FREQ-UT](#) [SSX750PBG-FREQ-UT](#) [SSX750PCB-FREQ-UT](#) [SSX750PBC-FREQ-UT](#) [SSX750PTF-FREQ-UT](#) [SSX750PCC-FREQ-UT](#) [SSX750PTC-FREQ-UT](#) [SSX750PBF-FREQ-UT](#) [SSX750PTB-FREQ-UT](#) [SSX750P1P-UT](#)