





# You make high bay and low bay lighting.

We'll make your high bay and low bay lighting shine – with long life times, outstanding efficacy and market leading performance.

Ecosystem	LED Spectrum Mixer	System Calculator	LM-80 Reports
			
Select pre-qualified, off-the-shelf components to aid in complete system design.	Calculate the color (white or color) that will be achieved by combining different LEDs into one application	Calculate the overall system performance based on design inputs.	Generate LM-80 reports for specific Lumileds LEDs.

Please check out our ecosystem support at [www.philipslumileds.com/designtools](http://www.philipslumileds.com/designtools)

## Who We Are

Philips Lumileds focuses on one goal: Creating the world's highest performing LEDs for lighting, flash, display and automotive applications. In partnership with its customers, Philips Lumileds matches application specific LEDs and uncompromising service with your end product design. Philips Lumileds

understands that solid-state lighting is not just about energy efficiency. It's about elegant design. Reinventing form. Pioneering markets and simplifying the supply chain. It's about a shared vision. Learn more about our comprehensive portfolio of LEDs at [www.philipslumileds.com](http://www.philipslumileds.com).




©2014 Philips Lumileds Lighting Company. All rights reserved. LUXEON is a registered trademark of the Philips Lumileds Lighting Company in the United States and other countries.

[www.philipslumileds.com](http://www.philipslumileds.com)  
[www.philipslumileds.cn.com](http://www.philipslumileds.cn.com)

AS 20140325

Philips Lumileds Lighting Company shall not be liable for any kind of loss of data or any other damages, direct, indirect or consequential, resulting from the use of the provided information and data. Although Philips Lumileds Lighting Company has attempted to provide the most accurate information and data, the materials and services information and data are provided "as is" and Philips Lumileds Lighting Company neither warranties, nor guarantees the contents and correctness of the provided information and data. Philips Lumileds Lighting Company reserves the right to make changes without notice. You as user agree to this disclaimer and user agreement with the download or use of the provided materials, information and data.





# High Bay and Low Bay Lighting

Energy saving LEDs for more productive environments



## Application requirements


- Increased optical control optimizes luminaire spacing and puts light where it is needed
- Accurate color rendering for productivity and safety
- Instant on without compromising reliability
- Ideal for dimming and occupancy based controls
- Provides uniform lighting









“My warehouse has never looked better. The electric bill has been cut in half and my workers are happier.”

### Philips Lumileds LEDs outperform conventional lighting

	System Efficacy	Reliability
HID	60 lm/W	15,000 hrs
Philips Lumileds LEDs	>120 lm/W	>60,000 hrs

### LUXEON Quality of Light



	Product/Type	Key Benefits	Flux (5700K Typical)	System Efficacy	Cost Efficient	CCT Accuracy
Arrays	 LUXEON M	<ul style="list-style-type: none"><li>• Flexibility to design for high efficiency or lower cost</li><li>• Assembly and manufacturing cost savings due to component count reduction</li></ul>	1,100 lm @ 700 mA, 85°C	+++	+++	3-Step/ 5-Step
	 NEW LUXEON MZ	<ul style="list-style-type: none"><li>• Small source size enables unique optical solutions</li><li>• Footprint compatible with LUXEON M allows for design flexibility</li></ul>	940 lm @ 700mA, 85°C	++	+++	3-Step/ 5-Step
	 NEW LUXEON CoB	<ul style="list-style-type: none"><li>• Easy to use, drop in, high flux solution</li><li>• Highest uniformity and efficiency in a small light emitting surface</li></ul>	500 to 10,000 lm 85°C, 70 CRI	++	+++	3-Step/ 5-Step
	 LUXEON K	<ul style="list-style-type: none"><li>• High lumen arrays ensuring bright light where needed</li><li>• Fully characterized light source resulting in ease of design and assembly</li><li>• Freedom from Binning – single V<sub>f</sub> Flux and CCT bin</li></ul>	4,400 lm (16-up) 6,600 lm (24-up) @ 700 mA, 85°C, 70 CRI	+++	+++	3-Step/ 5-Step
High-Power LEDs	 NEW LUXEON TX	<ul style="list-style-type: none"><li>• Best performance in a highly efficient package</li></ul>	275 lm @ 700 mA, 85°C	+++	+++	3-Step/ 5-Step
	 LUXEON Z ES	<ul style="list-style-type: none"><li>• Small optical source size enables unique optical solutions</li><li>• Footprint compatible with LUXEON T allows for design flexibility.</li></ul>	230 lm @ 700 mA, 85°C	++	+++	3-Step/ 5-Step
	 NEW LUXEON Q	<ul style="list-style-type: none"><li>• Industry standard 3535 footprint delivering market leading high flux</li></ul>	130 lm @ 350mA, 85°C	++	+++	3-Step 5-Step ANSI
Distributed Light Solutions	 NEW LUXEON 3020 LUXEON 3535L NEW LUXEON 3030 2D LUXEON 3535 2D	<ul style="list-style-type: none"><li>• High efficiency and cost effective mid-power LEDs</li></ul>	90 lm @ 100 mA, 25°C	+++	+++	ANSI